




Part Number : [755860010](#)
Product Description : 0.80mm Pitch, iPass I/O Surface Mount Receptacle, Right-Angle, External Application, 38 Circuit, 0.38µm Gold (Au), Supports QSFP14 / FDR
Series Number : 75586
Status : Not Recommended For New Design
Product Category : High-Speed I/O Connectors



Documents and Resources

Drawings

- [755860010 sd.pdf](#)
- [PK-75586-002-001.pdf](#)
- [PK-75586-101-001.pdf](#)

3D Models and Design Files

- [STEP AP242](#)
- [SOLIDWORKS](#)
- [Creo](#)
- [Symbol and Footprint \(Multi-Format\)](#)
- [EE-75586-001-001.pdf](#)
- [SI-75586-0001-001.pdf](#)
- [SP-75586-001-001.zip](#)

Specifications

- [AS-170432-0003-001.pdf](#)
- [AS-75586-001-001.pdf](#)
- [PS-75586-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 47; 34; 33
China RoHS	 per SJ/T 11365-2006

EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Not Recommended For New Design
Category	High-Speed I/O Connectors
Series	75586
Description	0.80mm Pitch, iPass I/O Surface Mount Receptacle, Right-Angle, External Application, 38 Circuit, 0.38µm Gold (Au), Supports QSFP14 / FDR
Application	Wire-to-Board
Comments	QSFP14 / FDR
Component Type	Receptacle
Product Name	iPass,Mini Multi-Lane,PCI Express
Type	Pluggable
UPC	822348852499

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	0.5A
Data Rate	10.0 Gbps
Grounding to Panel	N/A
Shielded	No
Voltage - Maximum	30V AC (RMS)/DC

Physical

Boot Color	N/A
Circuits (Loaded)	38
Circuits (maximum)	38
Color - Resin	Black
Durability (mating cycles max)	50
Flammability	94V-0
Gender	Female
Keying to Mating Part	No
Lock to Mating Part	No
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	0.977/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Embossed Tape on Reel
Panel Mount	No
PCB Locator	Yes
PCB Retention	No
PCB Thickness - Recommended	1.35mm
Pitch - Mating Interface	0.80mm
Pitch - Termination Interface	0.80mm

Plating min - Mating	0.381µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Temperature Range - Operating	-40° to +80°C
Termination Interface Style	Surface Mount
Waterproof / Dustproof	No
Wire Insulation Diameter	N/A
Wire Size (AWG)	N/A

Solder Process Data

Max-Duration	20
Lead-Free Process Capability	REFLOW
Max-Cycle	1
Max-Temp	260

Mates With / Use With

Use with Part(s)

Description	Part Number
External iPass Mini Multi-Lane SAS Guide Frames	<u>74548</u>

This document was generated on May 22, 2026