






PN: 09 45 545 0023  
PN: 09 45 545 0033




PN: 09 45 545 0030  
PN: 09 45 595 0030



X = 11.26 +/-0.15 for plastic version  
X = 11.3 +/-0.15 for metal version




PCB thickness: 1.6mm +/-0.1




(2) maxi PCB front side position if SMD led NOT used

Downloaded from Arrow.com.


# MOUNTING INSTRUCTION FOR HAN 3A RJ45 HOUSING WITH HAN 3A ADAPTER WITHOUT FIXING CLIPS 09 45 515 0022



D-D



PCB board Layout



PCB thickness: 1.6mm +/-0.1

Receptacle mating side according to  
IEC 61076-3-106 variant 5

|                                                                                     |  |                                              |  |                                                                 |  |                       |  |                             |  |                                                          |  |                        |  |
|-------------------------------------------------------------------------------------|--|----------------------------------------------|--|-----------------------------------------------------------------|--|-----------------------|--|-----------------------------|--|----------------------------------------------------------|--|------------------------|--|
|  |  | All Dimensions in mm<br>Original Size DIN A4 |  | Scale<br>2:1                                                    |  | Free size tol.        |  | Ref.                        |  |                                                          |  |                        |  |
|                                                                                     |  |                                              |  |                                                                 |  |                       |  | Sub.                        |  |                                                          |  |                        |  |
|  |  | All rights reserved                          |  | Created by<br>STOICA                                            |  | Inspected by<br>AVRAM |  | Standardisation<br>HOFFMANN |  | Date<br>2015-09-03                                       |  | State<br>Final Release |  |
| Department EC PD - RO                                                               |  |                                              |  | Title<br>HARTING RJ Industrial RJ45 jack 10/100Mbit PoE, 27.5mm |  |                       |  |                             |  | Doc-Key / ECM-Nr.<br>100635476/UGD/001/A<br>500000093968 |  |                        |  |
| HARTING Electronics GmbH<br>D-32339 Espelkamp                                       |  |                                              |  | Type TB                                                         |  | Number 09455511131    |  |                             |  | Rev. A                                                   |  | Page 3/4               |  |

