

SLF10145T-330M1R6-PF



Applications	Commercial Grade
Feature	Wire Wound
	Magnetic Shield
	Ferrite Core
Series   Type	SLF
Status	EOL announced
	Recommended Alternate Part No. : <a href="#">SPM10054T-330M-HZR</a> (Interchangeability is not guaranteed.)
	Discontinue Issue Date : May.14, 2024
	Last Purchase Order Date : Mar.31, 2026
Brand	Last Shipment Date : Dec.31, 2026
	TDK



Size	
Length(L)	10.10mm ±0.30mm
Width(W)	10.10mm ±0.30mm
Thickness   Height	4.50mm ±0.30mm
Recommended Land Pattern (A)	2.50mm Nom.
Recommended Land Pattern (B)	5.60mm Nom.
Recommended Land Pattern (C)	3.20mm Nom.

Electrical Characteristics	
Inductance	33μH ±20% at 1kHz
Rated Current (L Change) [Typ.]	
Rated Current (L Change) [Max.]	1.6A (10% Down)
Rated Current (Temperature Rise) [Typ.]	1.7A (30°C Rise)
Rated Current (Temperature Rise) [Max.]	
DC Resistance [Typ.]	81.5mΩ
DC Resistance [Max.]	97.8mΩ
Rated Voltage [Max.]	
Self Resonant Frequency [Min.]	
Self Resonant Frequency [Typ.]	
Q [Min.]	
Q [Typ.]	

Other	
Operating Temp. Range	-40 to 105°C (Including Self-Temp. Rise)

! Images are for reference only and show exemplary products.  
! This PDF document was created based on the data listed on the TDK Corporation website.  
! All specifications are subject to change without notice.

SLF10145T-330M1R6-PF









Soldering Method	Reflow Iron Soldering
AEC-Q200	NO
Packing	Embossed (Plastic)Taping [330mm Reel]
Package Quantity	500pcs
Weight	1.3g

SLF10145T-330M1R6-PF




## Characteristic Graphs(This is reference data, and does not guarantee the products characteristics.)



SLF10145T-330M1R6-PF



Characteristic Graphs(This is reference data, and does not guarantee the products characteristics.)





## Associated Images

