

Amphenol
FCi

© 2016 AFCi

10135286 - 10X LF



SEE NOTE 2

LEAD-FREE DESIGNATION
ONLY WITH APPLICABLE
PLATING CODES





MODULE DESCRIPTION	LETTER DESIGNATION REPRESENTED IN DASH NUMBER										BASE MODULE
LEFT POLARIZING GUIDANCE MODULE (SEE SHEET 3)	N	J (NO KEY)	A	B	C	D	E	F	G	H	
	NO KEY NO GUIDE PIN										
RIGHT POLARIZING GUIDANCE MODULE (SEE SHEET 2)	Z	Y (NO KEY)	P	Q	R	S	T	U	V	W	
	NO KEY NO GUIDE PIN										

PRELIMINARY

spec ref		---		dr		Tao Zhan		2015/05/19		projection		MM		size		scale							
tolerance std		TOLERANCES UNLESS OTHERWISE SPECIFIED		eng		Jackie Chen		2016/03/14						A2		8:1							
ASME Y14.5M				chr		-		-						ecn no		-							
				appr		-		-						rel level		Preliminary							
										product family		AirMax VS2											
surface		linear		0.X		±.3		Amphenol FCI		title		AIRMAX VS2 R.A. RECEPTACLE		dwg no		10135286		rev					
																				0.XX		±.15	
																				0.XXX		±.050	
		angular		0°		±°				cat. no.		-		Product - Customer Drw		sheet 1 of 4							



For information only. This is a preliminary customer document that is subject to change without notice.



PRELIMINARY

spec ref	---	dr	Tao Zhan	2015/09/19	projection	MM	size	A2	scale	8:1
tolerance std	ASME Y14.5M	eng	Jackie Chen	2016/03/14	chr	-	ecn no	-		
	TOLERANCES UNLESS OTHERWISE SPECIFIED	appr	-	-	product family	AIRMAX VS2	rel level	Preliminary		
surface	-	linear	0.X	±.3	Amphenol FCI	AIRMAX VS2 R.A. RECEPTACLE	10135286	1	Product - Customer Drw	sheet 3 of 4
			0.XX	±.15						
			0.XXX	±.050						
		angular	0°	±°	cat. no.	-				

