

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

2043650010

Status:

Active

Overview:

Coeur CST High-Current Interconnect System

Description:

Coeur CST High-Current Female Socket, 8.00mm Diameter, with 1.00mm Float, Surface Mount

Documents:

- Drawing (PDF)

RoHS Certificate of Compliance (PDF)
- Product Specification 2043130001-PS-000 (PDF)

Product Literature (PDF)
- Application Specification 2043130001-AS-000 (PDF)

General

Product Family

Series

Application

Comments

PCB Receptacles

204365

Power

Current and voltage performances are dependent upon application variables

Embossed Tape & Reel and Tray packaging available. Contact Molex for information.

Overview

Product Literature Order No

Product Name

UPC

Coeur CST High-Current Interconnect System

987651-8619

Coeur CST

191128468695

Physical

Circuits (Loaded)

Circuits (maximum)

Durability (mating cycles max)

Glow-Wire Capable

Material - Metal

Material - Plating Mating

Material - Plating Termination

Net Weight

Number of Rows

Orientation

PCB Retention

Packaging Type

Pitch - Mating Interface

Polarized to PCB

Temperature Range - Operating

Termination Interface: Style

1

1

200

No

Copper Alloy

Gold

Silver

7.700/g

1

Vertical

None

Carton

N/A

No

-40°C to +105°C

Surface Mount

Electrical

Current - Maximum per Contact

Voltage - Maximum

200.0A

600V

Material Info

Reference - Drawing Numbers

Application Specification

Product Specification

Sales Drawing

2043130001-AS-000

2043130001-PS-000

2043650010-SD-000



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[204365](#) Series

Mates With

Male Press-Fit Pin [203263](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION