

Detailed Specifications

Frame Width:	92[mm]
Frame Height:	92[mm]
Frame Depth:	25[mm]
Max. Air Flow:	45.2[CFM]
Max. Air Flow:	1.28[m3 per min]
Max. Static Pressure:	0.14[In H2O]
Max. Static Pressure:	36.2[Pa]
Fan Speed:	2750[RPM]
Noise:	29[dB]
Life Expectancy:	60 degree C 40,000 Hours AA/EA[L10]
Bearing Type:	Ball Bearing
Nominal Voltage:	24[V]
Operating Voltage - Lower:	12[V]
Operating Voltage - Upper:	27.6[V]
Current:	0.07[A]
Input Power:	1.7[W]
Mass:	95[g]
Tach / Locked Rotor Output:	Locked Rotor
Status:	Active

DC Axial Fans