


TWM/TWW Series

Ceramic Housed Radial Terminal Power



The TWM/TWW series radial terminal power resistors offer significant board space savings over axial terminal products. Generated heat is also kept away from the circuit board.

They are recommended for commercial applications requiring low cost.



FEATURES

- Economical Commercial Grade for general purpose use
- Wirewound and Metal Oxide construction
- Wide resistance range
- Flameproof inorganic construction


SERIES SPECIFICATIONS

Series	Wattage	Resistance	Voltage	Element
TWW3	3	0.01-39 Ω	250	Wire
TWW5	5	0.01-47 Ω	350	Wire
TWW10	10	0.04-990 Ω	750	Wire
TWW15	15	0.1 Ω -560 Ω	700	Wire
TWW20	20	0.1 Ω -560 Ω	750	Wire
TWM3	3	43-50K Ω	250	Metal oxide
TWM5	5	51-50K Ω	350	Metal oxide
TWM10	10	1000-50K Ω	750	Metal oxide
TWM15	15	561 Ω -200K Ω	700	Metal oxide
TWM20	20	561 Ω -200K Ω	750	Metal oxide

CHARACTERISTICS

Housing	Ceramic
Core	Fiberglass
Filling	Cement based
Tolerance	5% standard
Temperature coefficient	0.01-20 Ω $\pm$ 400ppm/ $^{\circ}$ C; >20-10 Ω $\pm$ 350ppm/ $^{\circ}$ C
Dielectric withstanding voltage	1,000VAC
Short time overload	TWW: 10x rated power for 5 sec.; TWM: 5x rated power for 5 sec. 15 & 20 watt: 2.5x RCWW for 5 sec.
Operating Temperature	-55 $^{\circ}$ C to 275 $^{\circ}$ C
Storage Temperature	15 $^{\circ}$ C-35 $^{\circ}$ C, humidity: 25%-75%

Derating




(continued)


TWM/TWW Series

Ceramic Housed Radial Terminal Power

DIMENSIONS



HOW TO ORDER



Standard part numbers for TWW series

Ohmic value	Part No. Prefix Suffix	Wattage 3 5 10 15 20
0.01	R01E	✓
0.02	R02E	✓
0.03	R03E	✓
0.04	R04E	✓
0.05	R05E	✓
0.10	R10E	✓
0.15	R15E	✓
0.20	R20E	✓
0.27	R27E	✓
0.30	R30E	✓
0.33	R33E	✓
0.39	R39E	✓
0.43	R43E	✓
0.47	R47E	✓
0.56	R56E	✓
0.68	R68E	✓
0.75	R75E	✓
0.82	R82E	✓
1.0	1R0E	✓
1.5	1R5E	✓
2.0	2R0E	✓
2.7	2R7E	✓
3.0	3R0E	✓
3.3	3R3E	✓
3.9	3R9E	✓
4.3	4R3E	✓
4.7	4R7E	✓
5.6	5R6E	✓
6.8	6R8E	✓
7.5	7R5E	✓
8.2	8R2E	✓
10	10RE	✓
15	15RE	✓
20	20RE	✓
22	22RE	✓
27	27RE	✓
30	30RE	✓
33	33RE	✓
39	39RE	✓
43	43RE	✓
47	47RE	✓
51	51RE	✓
56	56RE	✓
68	68RE	✓
75	75RE	✓
82	82RE	✓
100	100E	✓
150	150E	✓
200	200E	✓
270	270E	✓
300	300E	✓
330	330E	✓
390	390E	✓
430	430E	✓
470	470E	✓
500	500E	✓
560	560E	✓
680	680E	✓
750	750E	✓
820	820E	✓

Standard part numbers for TWM series

Ohmic value	Part No. Prefix Suffix	Wattage 3 5 10 15 20
43	43RE	✓
47	47RE	✓
56	56RE	✓
68	68RE	✓
75	75RE	✓
82	82RE	✓
100	100E	✓
150	150E	✓
200	200E	✓
270	270E	✓
300	300E	✓
330	330E	✓
390	390E	✓
430	430E	✓
470	470E	✓
560	560E	✓
680	680E	✓
750	750E	✓
820	820E	✓
1000	1K0	✓
1500	1K5	✓
2000	2K0	✓
2700	2K7	✓
3000	3K0	✓
3300	3K3	✓
3900	3K9	✓
4300	4K3	✓
4700	4K7	✓
5600	5K6	✓
5100	5K1	✓
6800	6K8	✓
7500	7K5	✓
8200	8K2	✓
10000	10K	✓
27000	27K	✓
47000	47K	✓
51000	51K	✓
75000	75K	✓