

This document is the property of Amphenol Corporation and is delivered on the express condition that is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, and that no right is granted to disclose or to use any information in this document.

The marking on this product doesn't contain environmental hazardous materials per Material Specification SS-00259 for Sony GP compliant or per directive 2011/65/EU for RoHS compliant.

ORIGINAL

REVISIONS				
SYM	ECN No.	DESCRIPTION	DATE	BY
A	NE-14070	NEW RELEASE	04/28/2014	HANK HSU
B	NE-14176	ADDED COLOR DESCRIPTION IN NOTES	10/02/2014	HANK HSU








TABLE 1

DIM A	APPLICABLE PCB THK
2.40	1.57~1.60
3.59	2.36~2.79
3.98	3.18

PART NUMBER SYSTEM

Mini SAS HD Integrated Connector	G40H B X X X X X XX - X	Verification Code X: OPTION BLANK: STANDARD
Connector Style B: V/T, 8512		Compliant Code XX: OPTION HR: Halogen-Free & RoHS
Number of Integration X: OPTION 1: 1X1 2: 1X2		BOARDLOCK CODE X: OPTION 1: 2.40 mm 2: 3.59 mm 3: 3.98 mm
Contact Finish X: OPTION 3: 30u" Gold		Variation Code X: OPTION 1: with Cap 2: without Cap
Terminal Style X: OPTION 2: SMT, 100u" MIN MATTE TIN PLATING		Packing Code X: OPTION 1: Tray 2: Tape & Reel 3: Narrow Tray



NOTES:

1. INSULATOR: HIGH TEMPERATURE UL94V-0.
COLOR: NC(BRACKET), BK(HOUSING)
2. TERMINAL: COPPER ALLOYBRASS
CONTACT AREA: OPTION
SOLDERING AREA: OPTION
UNDER PLTING.: NI 100u" MIN.
3. THIS PRODUCT DOESN'T CONTAIN ENVIRONMENTAL HAZARDOUS
PER DIRECTIVE 2011/65/EU for RoHS AND PER IEC 61249-2-21
FOR HALOGEN-FREE COMPLIANT.







TOLERANCE	DRAWN	APPROVALS	DATE	TITLE		Amphenol®			
X. X.X ±0.30 X.XX ±0.20 X.XXX ±0.10 ANGULAR ±2° UNLESS OTHERWISE SPECIFIED	DESIGNED	Hank Hsu	10/02/2014	MINI SAS HD INTEGRATED CONNECTOR 0.75 PITCH, V/T, SMT TYPE		Amphenol Corporation Amphenol Taiwan Corporation			
	CHECKED	Sondra Sang	10/02/2014						
	APPROVED	Hank Hsu	10/02/2014						
	DWG TYPE	CUST DWG	PROJECT CODE	1515		UNIT	mm	SIZE	A3
						SCALE	NA	SHEET	1 OF 3
								PART No.	G40HBXXXXXXHR-C
								DWG No.	G40HBXXXXXXHR-C
								REV.	B

This document is the property of Amphenol Corporation and is delivered on the express condition that it is not to be disclosed, reproduced or used, in whole or in part, for manufacture or sale by anyone other than Amphenol Corporation without its prior consent, and that no right is granted to disclose or to use any information in this document.

The marking on this product doesn't contain environmental hazardous materials per Material Specification SS-00259 for Sony GP compliant or per directive 2011/65/EU for RoHS compliant.

ORIGINAL


REVISIONS				
SYM	ECN No.	DESCRIPTION	DATE	BY
A	NE-14070	NEW RELEASE	04/28/2014	HANK HSU
B	NE-14176	ADDED COLOR DESCRIPTION IN NOTES	10/02/2014	HANK HSU




TOLERANCE	DRAWN	APPROVALS	DATE	TITLE	Amphenol® Amphenol Corporation Amphenol Taiwan Corporation			
X.	DESIGNED	Hank Hsu	10/02/2014	MINI SAS HD INTEGRATED CONNECTOR 0.75 PITCH, V/T, SMT TYPE	PART No. G40HBXXXXXXHR-C			
X.X ±0.30	CHECKED	Sondra Sang	10/02/2014		DWG No. G40HBXXXXXXHR-C			
X.XX ±0.20	APPROVED	Hank Hsu	10/02/2014		REV. B			
X.XXX ±0.10	DWG TYPE	CUST DWG	PROJECT CODE T515					
ANGULAR ±2°								
UNLESS OTHERWISE SPECIFIED								

ORIGINAL

REVISIONS				
SYM	ECN No.	DESCRIPTION	DATE	BY
A	NE-14070	NEW RELEASE	04/28/2014	HANK HSU
B	NE-14176	ADDED COLOR DESCRIPTION IN NOTES	10/02/2014	HANK HSU



1X1 RECOMMENDED PCB LAYOUT
(ALL TOLERANCES ARE ± 0.05)



1X2 RECOMMENDED PCB LAYOUT
(ALL TOLERANCES ARE ± 0.05)

NOTES:

1. RECOMMENDED PCB HOLE $\phi 1.20$ IS NPTH FOR ORIENTATION POST.
2. RECOMMENDED PCB ELLIPTICAL HOLE 0.5×1.45 IS PTH FOR BOARD-LOCK.
3. MINIMUM PCB THICKNESS: 1.57MM
4. PIN ASSIGNMENTS PLEASE REFER TO SERIAL ATTACHED SCSI-3 (SAS-3) STANDARD.

TOLERANCE		DRAWN APPROVALS		DATE	TITLE			Amphenol®					
X. X.X ±0.30 X.XX ±0.20 X.XXX ±0.10 ANGULAR ±2° UNLESS OTHERWISE SPECIFIED		DESIGNED	Hank Hsu	10/02/2014	MINI SAS HD INTEGRATED CONNECTOR 0.75 PITCH, V/T, SMT TYPE			Amphenol Corporation Amphenol Taiwan Corporation					
		CHECKED	Sondra Sang	10/02/2014									
		APPROVED	Hank Hsu	10/02/2014									
DWG TYPE		CUST DWG	PROJECT CODE	T515		UNIT	mm	SIZE	A3	PART No.	G40HBXXXXXXHR-C	REV.	B
						SCALE	NA	SHEET	3 OF 3	DWG No.	G40HBXXXXXXHR-C		



UNIT mm
SCALE NA
SHEET 3 OF 3

PART No. G40HBXXXXXXHR-C
DWG No. G40HBXXXXXXHR-C
REV. B