MP9361

High Performance Regulated Charge Pump

The Future of Analog IC Technology

DESCRIPTION

The MP9361 is a high performance, regulated charge pump converter. Its input voltage ranges from 2.8V to Vout. The output voltage is regulated to a fixed 5V. No external inductor is required for simplicity and compactness. Internal soft-start circuit effectively reduces the in-rush current both while start-up and mode change.

The MP9361 is available in a compact TSOT23-6 package

FEATURES


- Input Voltage Range: 2.8V to 5V
- Internal Soft-Start
- Output Maximum Current up to 110mA
- Fixed 5V Output Voltage with 30mV Ripple
- 2X Charge Pump
- Fixed 1.35MHz Switching Frequency
- Over Current Protection
- Short Circuit Protection
- In-rush Current limit
- TSOT23-6 package and Lead (pb)-Free

APPLICATIONS

- Cell phone, Smart phone, LED backlight
- PDA or hand Held Computer
- Camera Flash White LED
- LCD Display Supply
- TV-Remote Control

"MPS" and "The Future of Analog IC Technology" are Registered Trademarks of Monolithic Power Systems, Inc.


TYPICAL APPLICATION



MPS Proprietary Information. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

Downloaded from Arrow.com.

PACKAGE REFERENCE



Part Number*	Package	Temperature
MP9361DJ	TSOT23-6	-40°C to +85°C

* For Tape & Reel, add suffix –Z (e.g. MP9361DJ–Z)
For RoHS compliant packaging, add suffix –LF
(e.g. MP9361DJ–LF–Z)

ABSOLUTE MAXIMUM RATINGS (1)

Supply Input Voltage ..... –0.3V to +6.0V
All Other Pins ..... –0.3V to +6.0V
Storage Temperature ..... –65°C to +150°C
Junction Temperature ..... +150°C
Lead Temperature ..... +260°C

Recommended Operating Conditions (2)

Supply Voltage V_{IN} ..... 2.8V to 5.0V
Output Voltage V_{OUT} 5.0V
Operating Temperature ..... –40°C to +85°C

Thermal Resistance (3)

	θ_{JA}	θ_{JC}	
TSOT23-6	195	25	°C/W

Maximum Power Dissipation (4)

(T_A=25°C)

TSOT23-6 ..... P_D ..... 0.64 ..... W

Notes:
1) Exceeding these ratings may damage the device.
2) The device is not guaranteed to function outside of its operating conditions.
3) Measured on JESD51-7 4-layer board.
4) Reduce 0.05 watts every 10°C increasing.

ELECTRICAL CHARACTERISTICS

V_{IN}=3.7V, C_{IN}=C_{OUT}=2.2uF, C_P=0.22µF, T_A=25°C, Unless otherwise noted

Parameter	Symbol	Condition	Min	Typ	Max	Units
Input Supply Voltage	V_{IN}		2.8		5	V
Output Voltage	V_{OUT}	VIN>3.2V, I_{OUT}<110mA	4.8	5	5.2	V
Quiescent Current	I_Q	I_{OUT}=0		2	4	mA
Maximum Output Current	I_O	V_{IN}>3.2V	110			mA
Over Current Protection	I_{OCP}	V_{OUT}=5V	250	350	500	mA
Short Circuit Protection	I_{SHORT}			60	90	mA
Output Ripple		I_{OUT}=60mA		30		mV
Shut Down Current	I_{SHDN}	V_{IN}=4.5V, V_{EN}<0.4V		0.1	1	µA
Operation Frequency	F_{OSC}		1.1	1.35	1.6	MHz
Enable Voltage, High	V_{EN} (HIGH)			1.5		V
Enable Voltage, Low	V_{EN} (LOW)			0.4		V
Enable Pin Leakage	I_{EN}	V_{EN}=5V		0.2	1	µA

MPS Proprietary Information. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

Downloaded from Arrow.com.

PIN FUNCTIONS

Pin #	Name	Description
1	OUT	Output Voltage. Decoupled with a 2.2µF ceramic capacitor for a load current less than 60mA. For a load current greater than 60mA, use 10µF decoupling capacitor.
2	GND	Ground.
3	EN	Device Enable: A logic high input (V_{EN}>1.5V) turns on the regulator. A logic low input (V_{EN}<0.4V)
4	CN	Flying Capacitor Negative Terminal.
5	IN	Input.
6	CP	Flying Capacitor Positive Terminal.


MPS Proprietary Information. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

Downloaded from Arrow.com.


TYPICAL PERFORMANCE CHARACTERISTICS

V_{IN}=3.7V, V_{OUT}=5V, C1=C2=2.2µF, C3=0.47µF. T_A=25ºC, unless otherwise noted.


Efficiency vs. Load Current




Efficiency vs. Input Voltage




Load regulation




Line Regulation




Quiescent Current vs. Temperature




Output Voltage vs. Temperature




Frequency vs. Temperature



Line Regulation vs. Temperature



Shut Down Current vs. Temperature



MPS Proprietary Information. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.


Downloaded from Arrow.com.

TYPICAL PERFORMANCE CHARACTERISTICS

V_{IN}=3.7V, V_{OUT}=5V, C1=C2=2.2µF, C3=0.47µF. T_A=25ºC Unless otherwise noted. (*continued*)


Inrush Current

V_{IN}=2.8V, I_{OUT}=64mA
with resistor load




Inrush Current

V_{GN}=V_{IN}=3.6V, I_{OUT}=64mA
with resistor load




Load PWM Dimming Operation

V_{EN}=V_{IN}=2.8V, F_{PWM}=100HZ




Load PWM Dimming Operation

V_{EN}=V_{IN}=2.8V, F_{PWM}=2KHZ




Normal Load Ripple

V_{EN}=V_{IN}=2.8V, V_{OUT}=5V, I_{OUT}=60mA



Normal Load Ripple

V_{IN}=V_{EN}=4V, I_{OUT}=60mA



MPS Proprietary Information. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

Downloaded from Arrow.com.

OPERATION




Figure 1— Functional Block Diagram

The MP9361 uses a switched capacitor charge pump to boost an input voltage to a regulated output voltage. Regulation is achieved by sensing the charge pump output voltage through an internal resistor divider network. A switched doubling circuit is enabled when the divided output drops below a preset trip point controlled by an internal comparator.

The switching signal, which drives the charge pump, is created by an integrated oscillator within the control circuit block. The fixed charge pump switching frequency is approximately 1.35MHz.


The MP9361 has complete output short-circuit and thermal protection to safeguard the device under extreme operating conditions. An internal thermal protection circuit senses die temperature and will shut down the device if the internal junction temperature exceeds approximately 145°C. The charge pump will remain disabled until the fault condition is relieved.

MPS Proprietary Information. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.


Downloaded from Arrow.com.

PACKAGE INFORMATION


TSOT23-6




TOP VIEW




RECOMMENDED LAND PATTERN



FRONT VIEW



SIDE VIEW



DETAIL "A"

NOTE:

1) ALL DIMENSIONS ARE IN MILLIMETERS.
2) PACKAGE LENGTH DOES NOT INCLUDE MOLD FLASH, PROTRUSION OR GATE BURR.
3) PACKAGE WIDTH DOES NOT INCLUDE INTERLEAD FLASH OR PROTRUSION.
4) LEAD COPLANARITY (BOTTOM OF LEADS AFTER FORMING) SHALL BE 0.10 MILLIMETERS MAX.
5) DRAWING CONFORMS TO JEDEC MO-193, VARIATION AB.
6) DRAWING IS NOT TO SCALE.
7) PIN 1 IS LOWER LEFT PIN WHEN READING TOP MARK FROM LEFT TO RIGHT, (SEE EXAMPLE TOP MARK)

MPS Proprietary Information. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

Downloaded from Arrow.com.

REVISION HISTORY

Revision #	Revision Date	Description	Pages Updated
1.0	4/7/2021	Correct the description about EN logic.	Page 3

NOTICE: The information in this document is subject to change without notice. Users should warrant and guarantee that third party Intellectual Property rights are not infringed upon when integrating MPS products into any application. MPS will not assume any legal responsibility for any said applications.

MPS Proprietary Information. Unauthorized Photocopy and Duplication Prohibited.
© 2021 MPS. All Rights Reserved.

Downloaded from Arrow.com.