
Thyristor \ Diode Module

V_{RRM} = 2x 1200 V
I_{TAV} = 25 A
V_T = 1,2 V

Phase leg


Part number

MCMA25PD1200TB



Backside: isolated

E72873



Features / Advantages:

- Thyristor for line frequency
- Planar passivated chip
- Long-term stability
- Direct Copper Bonded Al2O3-ceramic

Applications:

- Line rectifying 50/60 Hz
- Softstart AC motor control
- DC Motor control
- Power converter
- AC power control
- Lighting and temperature control

Package: TO-240AA

- Isolation Voltage: 4800 V~
- Industry standard outline
- RoHS compliant
- Soldering pins for PCB mounting
- Base plate: DCB ceramic
- Reduced weight
- Advanced power cycling

Disclaimer Notice

Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/disclaimer-electronics.

© 2025 IXYS all rights reserved

Downloaded from Arrow.com.


Rectifier

Symbol	Definition	Conditions		Ratings min.	typ.	max.	Unit
$V_{RSM/DSM}$	*max. non-repetitive reverse/forward blocking voltage*		T_{VJ} = 25°C			1300	V
$V_{RRM/DRM}$	*max. repetitive reverse/forward blocking voltage*		T_{VJ} = 25°C			1200	V
$I_{R/D}$	*reverse current, drain current*	$V_{R/D}$ = 1200 V	T_{VJ} = 25°C			100	µA
		$V_{R/D}$ = 1200 V	T_{VJ} = 140°C			4	mA
V_T	*forward voltage drop*	I_T = 25 A	T_{VJ} = 25°C			1,22	V
		I_T = 50 A				1,47	V
		I_T = 25 A	T_{VJ} = 125°C			1,20	V
		I_T = 50 A				1,52	V
I_{TAV}	*average forward current*	T_C = 85°C	T_{VJ} = 140°C			25	A
$I_{T(RMS)}$	*RMS forward current*	180° sine				40	A
V_{T0}	*threshold voltage* } *for power loss calculation only*		T_{VJ} = 140°C			0,87	V
r_T	*slope resistance* }					13	mΩ
R_{thJC}	*thermal resistance junction to case*					1,2	K/W
R_{thCH}	*thermal resistance case to heatsink*				0,2		K/W
P_{tot}	*total power dissipation*		T_C = 25°C			90	W
I_{TSM}	*max. forward surge current*	t = 10 ms; (50 Hz), sine	T_{VJ} = 45°C			400	A
		t = 8,3 ms; (60 Hz), sine	V_R = 0 V			430	A
		t = 10 ms; (50 Hz), sine	T_{VJ} = 140°C			340	A
		t = 8,3 ms; (60 Hz), sine	V_R = 0 V			365	A
I^2t	*value for fusing*	t = 10 ms; (50 Hz), sine	T_{VJ} = 45°C			800	A^2s
		t = 8,3 ms; (60 Hz), sine	V_R = 0 V			770	A^2s
		t = 10 ms; (50 Hz), sine	T_{VJ} = 140°C			580	A^2s
		t = 8,3 ms; (60 Hz), sine	V_R = 0 V			555	A^2s
C_J	*junction capacitance*	V_R = 400V f = 1 MHz	T_{VJ} = 25°C		16		pF
P_{GM}	*max. gate power dissipation*	t_P = 30 µs	T_C = 140°C			10	W
		t_P = 300 µs				5	W
P_{GAV}	*average gate power dissipation*					0,5	W
$(di/dt)_{cr}$	*critical rate of rise of current*	T_{VJ} = 125°C; f = 50 Hz repetitive,	I_T = 75 A			150	A/µs
		t_P = 200 µs; di_G/dt = 0,45 A/µs;					
		I_G = 0,45A; V_D = ⅔ V_{DRM} non-repet.,	I_T = 25 A			500	A/µs
$(dv/dt)_{cr}$	*critical rate of rise of voltage*	V_D = ⅔ V_{DRM}	T_{VJ} = 125°C			1000	V/µs
		R_{GK} = ∞; method 1 (linear voltage rise)					
V_{GT}	*gate trigger voltage*	V_D = 6 V	T_{VJ} = 25°C			1,5	V
			T_{VJ} = -40°C			1,6	V
I_{GT}	*gate trigger current*	V_D = 6 V	T_{VJ} = 25°C			55	mA
			T_{VJ} = -40°C			80	mA
V_{GD}	*gate non-trigger voltage*	V_D = ⅔ V_{DRM}	T_{VJ} = 140°C			0,2	V
I_{GD}	*gate non-trigger current*					5	mA
I_L	*latching current*	t_p = 10 µs	T_{VJ} = 25°C			150	mA
		I_G = 0,45A; di_G/dt = 0,45 A/µs					
I_H	*holding current*	V_D = 6 V R_{GK} = ∞	T_{VJ} = 25°C			100	mA
t_{gd}	*gate controlled delay time*	V_D = ½ V_{DRM}	T_{VJ} = 25°C			2	µs
		I_G = 0,45A; di_G/dt = 0,45 A/µs					
t_q	*turn-off time*	V_R = 100 V; I_T = 25A; V_D = ⅔ V_{DRM}	T_{VJ} =125 °C		150		µs
		di/dt = 10 A/µs; dv/dt = 20 V/µs; t_p = 200 µs					

© 2025 IXYS all rights reserved

Downloaded from Arrow.com.

Package TO-240AA					Ratings			
Symbol	Definition	Conditions			min.	typ.	max.	Unit
I_{RMS}	*RMS current*	per terminal					60	A
T_{VJ}	*virtual junction temperature*				-40		140	°C
T_{op}	*operation temperature*				-40		125	°C
T_{stg}	*storage temperature*				-40		125	°C
Weight						81		g
M_D	*mounting torque*				2,5		4	Nm
M_T	*terminal torque*				2,5		4	Nm
$d_{Spp/App}$	*creepage distance on surface | striking distance through air*		*terminal to terminal*	13,0	9,7			mm
$d_{Spb/Apb}$			*terminal to backside*	16,0	16,0			mm
V_{ISOL}	*isolation voltage*	t = 1 second	50/60 Hz, RMS; I_{ISOL} ≤ 1 mA		4800			V
		t = 1 minute			4000			V




Part description

M = Module
C = Thyristor (SCR)
M = Thyristor
A = (up to 1800V)
25 = Current Rating [A]
PD = Phase leg
1200 = Reverse Voltage [V]
TB = TO-240AA-1B

Ordering	Ordering Number	Marking on Product	Delivery Mode	Quantity	Code No.
Standard	MCMA25PD1200TB	MCMA25PD1200TB	Box	36	515983

Equivalent Circuits for Simulation

** on die level* T_{VJ} = 140°C




Thyristor

$V_{0\ max}$	*threshold voltage*	0,87	V
$R_{0\ max}$	*slope resistance **	11,8	mΩ


© 2025 IXYS all rights reserved

Downloaded from Arrow.com.

Outlines TO-240AA



Optional accessories for modules
Keyed gate/cathode twin plugs with wire length = 350 mm, gate = white, cathode = red
Type ZY 200L (L = Left for pin pair 4/5) UL 758, style 3751



© 2025 IXYS all rights reserved

Downloaded from Arrow.com.

Thyristor




Fig. 1 Forward characteristics




Fig. 2 Surge overload current
I_{TSM}: crest value, t: duration




Fig. 3 I^2t versus time (1-10 s)




Fig. 4 Gate voltage & gate current




Fig. 5 Gate controlled delay time t_{gd}




Fig. 6 Max. forward current at case temperature





Fig. 7a Power dissipation versus direct output current
Fig. 7b and ambient temperature



i	R_{thi} (K/W)	t_i (s)
1	0.0200	0.0004
2	0.1300	0.0090
3	0.2400	0.0140
4	0.4700	0.0700
5	0.3400	0.4000

Fig. 8 Transient thermal impedance junction to case

© 2025 IXYS all rights reserved

Downloaded from Arrow.com.