





JKL PART NO.: 2910F-42



JKL PART NO.: 2910F-47

NOTES:

- TAB SIZE REFERENCE DIMENSIONS: .244" wide X .30" deep X .016 thick.
KEYSTONE P/N 4470 QUICK-FIT SOCKET MAY BE USED FOR CONTACT.
- LAMP SIZES FOR EACH HOLDER:
-42 HOLDER CAN HOLD LAMPS FROM 30mm TO 40mm LONG
-47 HOLDER CAN HOLD LAMPS FROM 37mm TO 44mm LONG
- MINIMUM CONTACT DIAMETER .30"
- LOCATION OF MOUNTING HOLE. HOLE DIA. : Ø3.5mm REF.
- BODY MATERIAL: DUPONT FR50
MAX. WITHSTAND TEMPERATURE 130C
MAX. INTERMITTENT TEMPERATURE 180C
MAX. WATTAGE: -42 10W
-47 18W

			METRIC  THIRD ANGLE PROJECTION	DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- REF. 2 PL +/- REF. ANGLE +/- 0	JKL COMPONENTS CORPORATION								
					TITLE								
E	CHANGE NOTE 2	3/9/10	DRAWN BY L. WENGSTROM	APPVD BY L. R.	DATE 3/9/10	FESTOON HOLDER							
D	ADDED NOTES	8/7/08											
C	CORR. MATERIAL DESCRIPTION	11/13/07											
B	ADD NOTES	8/18/06											
A	ADD PART NO. 2910F-47	6/30/06											
	RELEASED	6/12/06	- CAD DRAWING - MANUAL REVISIONS NOT PERMITTED		SCALE	NONE	RELEASED DATE	6/12/06	REVISION DATE	3/9/10	REV. NO.	E	SHEET 1 OF 1