



Part Number : [1727040155](#)

Product Description : FCT High Power Contact, Female, Straight, Solder Cup, 0.80µm Gold Mating Plating, 0.20µm Gold Termination Plating, Split Tine, 20.0A, 16-12 AWG

Series Number : 172704

Status : Active

Product Category : D-Sub Contacts

Engineering Part Number : FMP006S103

Documents and Resources

Drawings

[1727040155_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[1731120008-PK-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026) SCIP:d5ca3d76-6290-4794-890c-153e91127e83
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	D-Sub Contacts
Series	172704
Description	FCT High Power Contact, Female, Straight, Solder Cup, 0.80µm Gold Mating Plating, 0.20µm Gold Termination Plating, Split Tine, 20.0A, 16-12 AWG
Contact Type	High Power
Magnetic	Yes
Product Name	FCT Products
Type	Mixed Layout
UPC	889056020664

Electrical

Current - Maximum per Contact	20.0A
-------------------------------	-------

Physical

Durability (mating cycles min)	500
Gender	Female
Material - Contact	Copper Alloy

Material - Plating Mating	Gold over Nickel
Material - Plating Termination	Gold over Nickel
Material - Retaining Clip	Copper Alloy
Net Weight	2.000/g
Orientation	Straight
Packaging Type	Bag
Plating min - Mating	0.800µm
Plating min - Termination	0.200µm
Temperature Range - Operating	-55° to +155°C
Termination Style	Solder Cup
Wire Size (AWG)	12, 14, 16

Mates With / Use With

Mates with Part(s)

Description	Part Number
FCT High Power Contact, Male, Straight, Solder Cup, 0.80µm Gold Mating Plating, 0.20µm Gold Termination Plating, 20.0A, 16-12 AWG	<u>1727040147</u>

Use with Part(s)

Description	Part Number
FCT Mixed Layout D-Sub Connector, Female, Straight, Solder Cup, Gold Plating, Tin-plated Shell, 9 Circuits Max, 5 Signal Contacts Loaded, Green Insulator	<u>1731070062</u>
FCT Mixed Layout D-Sub Connector, Female, Straight, Solder Cup, Gold Plating, Tin-plated Shell, 24 Circuits Max, 17 Signal Contacts Loaded, Green Insulator	<u>1731070070</u>
FCT Mixed Layout D-Sub Connector, Female, Straight, Solder Cup, Gold Plating, Tin-	<u>1731070060</u>

plated Shell, 7 Circuits Max, 5 Signal Contacts Loaded, Green Insulator	
FCT Mixed Layout D-Sub Connector, Female, Straight, Solder Cup, Gold over Nickel Phosphorus Plating, Tin-plated Shell, 11 Circuits Max, 10 Signal Contacts Loaded, Green Insulator	<u>1727040012</u>
FCT Mixed Layout D-Sub Connector, Female, Straight, Solder Cup, Gold Plating, Tin-plated Shell, 13 Circuits Max, 10 Signal Contacts Loaded, Green Insulator	<u>1731070064</u>
FCT Mixed Layout D-Sub Connector, Female, Straight, Solder Cup, Gold Plating, Tin-plated Shell, 17 Circuits Max, 15 Signal Contacts Loaded, Green Insulator	<u>1731070066</u>
FCT Mixed Layout D-Sub Connector, Female, Straight, Solder Cup, Gold Plating, Tin-plated Shell without Dimples, 9 Circuits Max, 5 Signal Contacts Loaded	<u>1731070240</u>
FCT Mixed Layout D-Sub Connector, Female, Straight, Solder Cup, Gold over Nickel Phosphorus Plating, Tin-plated Shell, 27 Circuits Max, 25 Signal Contacts Loaded, Green Insulator	<u>1727040030</u>

Application Tooling

Global

Description	Part Number
FCT Removal Tool for Size 8 Contacts	<u>1731121747</u>

This document was generated on May 26, 2026