



REVISONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
A	PROPOSAL	OCT27/17	L.CHAN




RECOMMENDED P.C.B. LAYOUT
(COMPONENT SIDE OF BOARD)



- MATERIALS:**
PLASTIC HOUSING: HIGH TEMPERATURE THERMOPLASTIC
FLAMMABILITY RATING UL 94V-0, COLOUR: BLACK

CONTACTS: PHOSPHOR BRONZE
PLATING: SELECTIVE GOLD PLATING ON MATING SURFACES,
SEE AMPHENOL PART NUMBER FOR DETAIL.
50 μ " [1.27 MICRONS] MIN. NICKEL UNDERPLATE
100 μ " [2.54 MICRONS] MIN. MATTE TIN ON CONTACT TAILS

SHIELD: STAINLESS STEEL WITH TIN DIPPED ON PCB TAILS.
- RECOMMENDED SOLDERING TEMPERATURE:**
WAVE SOLDERING AT 260° C MAXIMUM FOR 5 SEC MAXIMUM.
- PART NUMBER:** RJE39-888-1X00
GOLD PLATING OPTION
0=GOLD FLASH
1=6u" GOLD PLATING
2=15u" GOLD PLATING
3=30u" GOLD PLATING
4=50u" GOLD PLATING



RECOMMENDED PANEL CUTOUT

UNLESS SPECIFIED OTHERWISE		DRAWN	AMY.Z	DATE	OCT27/15	Amphenol Canada Corp. www.amphenolcanada.com	
PRIMARY UNITS	INCH	CHECKED	L.CHAN	DATE	OCT27/15		
SECONDARY	MILLIMETER	M.E. APP'D				TITLE	
REFERENCE IN PARENTHESES		Q.A. APP'D				8 PORT HIGH SPEED MODULAR JACK, 8 POSITIONS, 8 CONTACTS, SHIELDED, WITHOUT LEDs - RoHS COMPLIANT	
GENERAL TOLERANCES		DWG APPR.				DWG. NO.	
1 DECIMAL PLACE	±0.025	ENG. REL. NO.				P-RJE39-888-1X00	
2 DECIMAL PLACES	±0.020	REF.				REV	
3 DECIMAL PLACES	±0.015	THIRD ANGLE PROJECTION		DO NOT SCALE DRAWING		A	
ANGULAR DEGREES	±1.0°					CODE ID NO. 03554 DWG SIZE: C SCALE: N/A SHEET 1 OF 1	