







- ① MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- ② FINISH:
30μ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL.
3. SCREWS PACKAGED IN END OF PACKAGING TUBE.
- ④ FOR GROUNDED GUIDE PIN USE $\varnothing 3.56 \pm 0.08$ PTH,
 $\varnothing 3.66$ DRILL, AND $\varnothing 6.5$ PAD.
5. KEYING PIN SHOWN IN POSITION A, SEE KEYING CHART
ON SHEET 2 FOR OTHER POSITIONS.




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 22DEC2010 J. K. SHOBER		 TE Connectivity	
DIMENSIONS:		CH, EARY 22DEC2010			
mm		APVD J. EARY 22DEC2010		NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		IMPACT, 4 PAIR, 10 COLUMN, HEADER	
0 P/LC ± 1 P/LC ±0.25 2 P/LC ±0.13 3 P/LC ± 4 P/LC ± ANGLES ± FINISH		APPLICATION SPEC		LEFT GUIDED, OPEN END WALL	
		WEIGHT -		SIGNAL MODULE, 0.46 PTH	
MATERIAL		A		SIZE CAGE CODE DRAWING NO	
		SEE TABLE		00779C=2007808	
		CUSTOMER DRAWING		RESTRICTED TO	
				SCALE 6:1 SHEET 1 OF 2 REV. A2	


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-


OBSOLETE		H	5.5	8-2007808-3
		H	4.9	8-2007808-2
		H	4.5	8-2007808-1
		G	5.5	7-2007808-3
		G	4.9	7-2007808-2
		G	4.5	7-2007808-1
		F	5.5	6-2007808-3
		F	4.9	6-2007808-2
		F	4.5	6-2007808-1
		E	5.5	5-2007808-3
		E	4.9	5-2007808-2
		E	4.5	5-2007808-1
		D	5.5	4-2007808-3
		D	4.9	4-2007808-2
		D	4.5	4-2007808-1
		C	5.5	3-2007808-3
		C	4.9	3-2007808-2
		C	4.5	3-2007808-1
		B	5.5	2-2007808-3
		B	4.9	2-2007808-2
		B	4.5	2-2007808-1
		A	5.5	1-2007808-3
		A	4.9	1-2007808-2
		A	4.5	1-2007808-1
OBSOLETE		-	5.5	2007808-3
		-	4.9	2007808-2
		-	4.5	2007808-1
FINISH		KEY POSITION	DIM M	PART NUMBER


REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY


KEY POSITION
CHART


NONE


A


E

B

F

C

G

D

H