

	1	2	3	4	5	6	7																																																																													
A	RoHS compliant General Tolerances to DIN ISO 2768 <table border="1"> <tr> <th>Permissible deviations in mm for ranges in nominal lengths</th> <th>Tolerance class designation (description)</th> </tr> <tr> <td></td> <td>m (medium)</td> </tr> <tr> <td>0.5 up to 3</td> <td>±0.1</td> </tr> <tr> <td>over 3 up to 6</td> <td>±0.1</td> </tr> <tr> <td>over 6 up to 30</td> <td>±0.2</td> </tr> </table>							Permissible deviations in mm for ranges in nominal lengths	Tolerance class designation (description)		m (medium)	0.5 up to 3	±0.1	over 3 up to 6	±0.1	over 6 up to 30	±0.2	A																																																																		
Permissible deviations in mm for ranges in nominal lengths	Tolerance class designation (description)																																																																																			
	m (medium)																																																																																			
0.5 up to 3	±0.1																																																																																			
over 3 up to 6	±0.1																																																																																			
over 6 up to 30	±0.2																																																																																			
B								B																																																																												
C								C																																																																												
D								D																																																																												
E	Width across flat(SW)5 Thread M2.5 nickel plated <table border="1"> <tr> <th>Option</th> <th colspan="3">Dimensions</th> </tr> <tr> <td></td> <td>L</td> <td>B</td> <td>C min</td> </tr> <tr> <td>A</td> <td>5</td> <td>6</td> <td>2.5</td> </tr> <tr> <td>B</td> <td>8</td> <td>6</td> <td>5</td> </tr> <tr> <td>C</td> <td>10</td> <td>6</td> <td>6</td> </tr> <tr> <td>D</td> <td>12</td> <td>6</td> <td>6</td> </tr> <tr> <td>E</td> <td>15</td> <td>6</td> <td>6</td> </tr> <tr> <td>F</td> <td>18</td> <td>6</td> <td>6</td> </tr> <tr> <td>G</td> <td>20</td> <td>6</td> <td>6</td> </tr> <tr> <td>H</td> <td>25</td> <td>6</td> <td>6</td> </tr> <tr> <td>K</td> <td>30</td> <td>6</td> <td>6</td> </tr> </table>							Option	Dimensions				L	B	C min	A	5	6	2.5	B	8	6	5	C	10	6	6	D	12	6	6	E	15	6	6	F	18	6	6	G	20	6	6	H	25	6	6	K	30	6	6	E																																
Option	Dimensions																																																																																			
	L	B	C min																																																																																	
A	5	6	2.5																																																																																	
B	8	6	5																																																																																	
C	10	6	6																																																																																	
D	12	6	6																																																																																	
E	15	6	6																																																																																	
F	18	6	6																																																																																	
G	20	6	6																																																																																	
H	25	6	6																																																																																	
K	30	6	6																																																																																	
F								F																																																																												
G	<table border="1"> <tr> <td>Scale</td> <td>1:1</td> <td></td> <td></td> <td></td> <td></td> <td>Date</td> <td>Name</td> <td>Customer-No.</td> </tr> <tr> <td>TOLERANCE</td> <td></td> <td></td> <td></td> <td></td> <td>Drawn</td> <td>20.08.2009</td> <td>Dean</td> <td rowspan="4">ASSMANN WSW-No. V6622x</td> </tr> <tr> <td>X.</td> <td>±X</td> <td></td> <td></td> <td></td> <td>Approved</td> <td>20.08.2009</td> <td>Andy</td> </tr> <tr> <td>X.X</td> <td>±X</td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td>X.XX</td> <td>±X</td> <td></td> <td></td> <td></td> <td></td> <td></td> <td></td> </tr> <tr> <td>DIM</td> <td>TOL</td> <td>②</td> <td>Add tolerance</td> <td>09.10.2018</td> <td>F.Lübke</td> <td colspan="2" rowspan="3"> </td> <td>Drawing-No.</td> </tr> <tr> <td>X.°</td> <td>±X°</td> <td>①</td> <td>Drawn</td> <td>20.08.2009</td> <td>Dean</td> <td>ASS 0493 HS</td> <td>rev02</td> </tr> <tr> <td>X.X°</td> <td>±X°</td> <td></td> <td></td> <td></td> <td></td> <td>Replace</td> <td>Sheet</td> </tr> <tr> <td>Angle</td> <td>TOL</td> <td>Id.</td> <td>Modification</td> <td>Date</td> <td>Name</td> <td colspan="3"></td> </tr> </table>							Scale	1:1					Date	Name	Customer-No.	TOLERANCE					Drawn	20.08.2009	Dean	ASSMANN WSW-No. V6622x	X.	±X				Approved	20.08.2009	Andy	X.X	±X							X.XX	±X							DIM	TOL	②	Add tolerance	09.10.2018	F.Lübke			Drawing-No.	X.°	±X°	①	Drawn	20.08.2009	Dean	ASS 0493 HS	rev02	X.X°	±X°					Replace	Sheet	Angle	TOL	Id.	Modification	Date	Name				G
Scale	1:1					Date	Name	Customer-No.																																																																												
TOLERANCE					Drawn	20.08.2009	Dean	ASSMANN WSW-No. V6622x																																																																												
X.	±X				Approved	20.08.2009	Andy																																																																													
X.X	±X																																																																																			
X.XX	±X																																																																																			
DIM	TOL	②	Add tolerance	09.10.2018	F.Lübke			Drawing-No.																																																																												
X.°	±X°	①	Drawn	20.08.2009	Dean			ASS 0493 HS	rev02																																																																											
X.X°	±X°							Replace	Sheet																																																																											
Angle	TOL	Id.	Modification	Date	Name																																																																															
H								H																																																																												
	1	2	3	4	5	6	7																																																																													