

Part Number : 1200700258
Product Description : M12 Signal, A-Coded, Receptacle, 5 Poles, Male, Front Panel Mount, 1/2"-14 NPT Mounting Threads, 22 AWG, PVC Leads, 2.0m (6.56') Length
Series Number : 120070
Status : Active
Product Category : Industrial Connectors
Engineering Part Number : 8R5006A18M020

Documents and Resources

Drawings

1200700258_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Triphenyl-phosphate; Lead per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Industrial Connectors
Series	120070
Description	M12 Signal, A-Coded, Receptacle, 5 Poles, Male, Front Panel Mount, 1/2"-14 NPT Mounting Threads, 22 AWG, PVC Leads, 2.0m (6.56') Length
IP Rating	IP67
NEMA Rating	NEMA 6
Product Name	M12 Signal,Micro-Change (M12)
Type	Single Ended (pigtail)
UPC	78678831574

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

Physical

Coupling Type	External Thread
Gender	Male
Keyway	A-Coded
Length	2.0m
Material - Component	Black Annodized Aluminum
Mounting Thread Size	1/2" - 14 NPT
Net Weight	74.545/g

Downloaded from Arrow.com.

Orientation	Straight
Panel Mount	Front
Poles	5
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	UL 1061
Wire Size (AWG)	22

Downloaded from Arrow.com.