


HEAT SHRINK TUBING

TE CONNECTIVITY
RT-780-3/8-0-SPRT-780-3/8-0-SP
TE Internal Number: F48748-000
Alias ID: 1201739-3

Always EU RoHS/ELV Compliant

Wall Type **Single**Resistant To **Fluids, Hydrocarbons, Radiation, Strain**Low Outgassing **No**Product Source **US**Packaging Method **Piece**

> See All Features

✓ Active

> See All Documentation

North America ▾

Contact us to request pricing, availability and customization options.

REQUEST ADDITIONAL INFORMATION



GET SAMPLE



SAVE TO LIST



CHECK FOR TOOLING



FIND SIMILAR PRODUCTS

DOCUMENTATION **FEATURES**Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features

Wall Type

Single

Body Features

Material Systems Code

780 NBC

Shrink Ratio

2:1

Color

Black

Flexibility

Semi-Rigid

Material

Crosslinked Fluoroelastomer

Fluid Type

Aviation Fuel, Brake Fluid, Chemicals/Solvents, De-Icing Fluid, Diesel Fuel, Hydraulic Fluid, Lubricating Oil, Military Decontaminating Agents, Water

Dimensions

Recovered Wall Thickness (Nominal)

.003mm[.08in]

Recovered Inside Diameter (Max)

4.75mm[.187in]

Expanded Inside Diameter (Min)

9.53mm[.375in]

Usage Conditions

Resistant To

Fluids, Hydrocarbons, Radiation, Strain

Recovery Temperature(°C)

200

Operating Temperature Range(°C)

-55 – 175

Flammability

Flame-Retardant

Fluid Resistance

Immersion Protection, Splash Protection

Shrink Temperature (Min)(°C)

175

Product Availability

Applicable Region

Worldwide

Packaging Features

Packaging Method

Piece

Other

Low Outgassing

No

Product Source

US

Product Compliance

[Statement of Compliance](#)

PDF

[VIEW ALL PRODUCT COMPLIANCE](#)Download from [Arrow.com](#)

Feedback

Feedback

COMPATIBLE

No compatible products found for RT-780-3/8-0-SP