
Cool MOS™ Power Transistor

V_{DS} @ T_{jmax}	650	V
$R_{DS(on)}$	1.4	Ω
I_D	3.2	A


PG-TO251-3-11



Feature

- New revolutionary high voltage technology
- Ultra low gate charge
- Periodic avalanche rated
- Extreme d*v*/d*t* rated
- High peak current capability
- Improved transconductance
- Pb-free lead plating; RoHS compliant
- Qualified according to JEDEC[0)] for target applications

Type	Package	Ordering Code	Marking
SPS03N60C3	PG-TO251-3-11		03N60C3



Maximum Ratings

Parameter	Symbol	Value	Unit
Continuous drain current T_C = 25 °C T_C = 100 °C	I_D	 3.2 2	A
Pulsed drain current, t_p limited by T_{jmax}	$I_{D\ puls}$	9.6	
Avalanche energy, single pulse I_D = 2.4 A, V_{DD} = 50 V	E_{AS}	100	mJ
Avalanche energy, repetitive t_{AR} limited by T_{jmax}[1] I_D = 3.2 A, V_{DD} = 50 V	E_{AR}	0.2	
Avalanche current, repetitive t_{AR} limited by T_{jmax}	I_{AR}	3.2	A
Gate source voltage static	V_{GS}	±20	V
Gate source voltage AC (f >1Hz)	V_{GS}	±30	
Power dissipation, T_C = 25°C	P_{tot}	38	W
Operating and storage temperature	T_j, T_{stg}	-55... +150	°C
Reverse diode dv/dt [5)]	dv/dt	15	V/ns

Downloaded from Arrow.com.

Maximum Ratings

Parameter	Symbol	Value	Unit
Drain Source voltage slope V_{DS} = 480 V, I_D = 3.2 A, T_j = 125 °C	dv/dt	50	V/ns

Thermal Characteristics

Parameter	Symbol	Values			Unit
		min.	typ.	max.	
Thermal resistance, junction - case	R_{thJC}	-	-	3.3	K/W
Thermal resistance, junction - ambient, leaded	R_{thJA}	-	-	75	
SMD version, device on PCB: @ min. footprint @ 6 cm^2 cooling area [2)]	R_{thJA}	 - -	 - -	 75 50	
Soldering temperature, *) 1.6 mm (0.063 in.) from case for 10s	T_{sold}	-	-	260	°C

Electrical Characteristics, at T_j=25°C unless otherwise specified

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
Drain-source breakdown voltage	$V_{(BR)DSS}$	V_{GS}=0V, I_D=0.25mA	600	-	-	V
Drain-Source avalanche breakdown voltage	$V_{(BR)DS}$	V_{GS}=0V, I_D=3.2A	-	700	-	
Gate threshold voltage	$V_{GS(th)}$	I_D=135µA, V_{GS}=V_{DS}	2.1	3	3.9	
Zero gate voltage drain current	I_{DSS}	V_{DS}=600V, V_{GS}=0V, T_j=25°C, T_j=150°C	 - -	 0.5 -	 1 70	µA
Gate-source leakage current	I_{GSS}	V_{GS}=30V, V_{DS}=0V	-	-	100	nA
Drain-source on-state resistance	$R_{DS(on)}$	V_{GS}=10V, I_D=2A, T_j=25°C T_j=150°C	 - -	 1.26 3.8	 1.4 -	Ω
Gate input resistance	R_G	f=1MHz, open Drain	-	10	-	

*) TO252: reflow soldering, MSL3; TO251: wavesoldering

Downloaded from Arrow.com.

Electrical Characteristics , at T_j = 25 °C, unless otherwise specified

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
Transconductance	g_{fs}	$V_{DS}\geq 2*I_D*R_{DS(on)max}$, I_D=2A	-	3.4	-	S
Input capacitance	C_{iss}	V_{GS}=0V, V_{DS}=25V, f=1MHz	-	400	-	pF
Output capacitance	C_{oss}		-	150	-	
Reverse transfer capacitance	C_{rss}		-	5	-	
Effective output capacitance,[3] energy related	$C_{o(er)}$	V_{GS}=0V, V_{DS}=0V to 480V	-	12	-	pF
Effective output capacitance,[4] time related	$C_{o(tr)}$		-	26	-	
Turn-on delay time	$t_{d(on)}$	V_{DD}=350V, V_{GS}=0/10V, I_D=3.2A, R_G=20Ω	-	7	-	ns
Rise time	t_r		-	3	-	
Turn-off delay time	$t_{d(off)}$		-	64	100	
Fall time	t_f		-	12	20	

Gate Charge Characteristics

Gate to source charge	Q_{gs}	V_{DD}=420V, I_D=3.2A	-	2	-	nC
Gate to drain charge	Q_{gd}		-	6	-	
Gate charge total	Q_g	V_{DD}=420V, I_D=3.2A, V_{GS}=0 to 10V	-	13	17	
Gate plateau voltage	$V_{(plateau)}$	V_{DD}=420V, I_D=3.2A	-	5.5	-	V

[0] J-STD20 and JESD22

[1] Repetitve avalanche causes additional power losses that can be calculated as $P_{AV}=E_{AR}*f$.

[2] Device on 40mm*40mm*1.5mm epoxy PCB FR4 with 6cm² (one layer, 70 µm thick) copper area for drain connection. PCB is vertical without blown air.

[3] $C_{o(er)}$ is a fixed capacitance that gives the same stored energy as C_{oss} while V_{DS} is rising from 0 to 80% V_{DSS}.

[4] $C_{o(tr)}$ is a fixed capacitance that gives the same charging time as C_{oss} while V_{DS} is rising from 0 to 80% V_{DSS}.

[5] I_{SD}<=I_D, di/dt<=400A/us, V_{DClink}=400V, V_{peak}<$V_{BR, DSS}$, T_j<$T_{j,max}$.
Identical low-side and high-side switch.


Downloaded from Arrow.com.

Electrical Characteristics, at T_j = 25 °C, unless otherwise specified

Parameter	Symbol	Conditions	Values			Unit
			min.	typ.	max.	
Inverse diode continuous forward current	I_S	T_C=25°C	-	-	3.2	A
Inverse diode direct current, pulsed	I_{SM}		-	-	9.6	
Inverse diode forward voltage	V_{SD}	V_{GS}=0V, I_F=I_S	-	1	1.2	V
Reverse recovery time	t_{rr}	V_R=420V, I_F=I_S , di_F/dt=100A/µs	-	250	400	ns
Reverse recovery charge	Q_{rr}		-	1.8	-	µC
Peak reverse recovery current	I_{rrm}		-	15	-	A
Peak rate of fall of reverse recovery current	di_{rr}/dt		-	-	540	A/µs

Typical Transient Thermal Characteristics


Symbol	Value	Unit	Symbol	Value	Unit
	typ.			typ.	
Thermal resistance			Thermal capacitance		
R_{th1}	0.054	K/W	C_{th1}	0.00005232	Ws/K
R_{th2}	0.103		C_{th2}	0.0002034	
R_{th3}	0.178		C_{th3}	0.0002963	
R_{th4}	0.757		C_{th4}	0.0009103	
R_{th5}	0.682		C_{th5}	0.002084	
R_{th6}	0.202		C_{th6}	0.024	



Downloaded from Arrow.com.

1 Power dissipation


$P_{tot} = f(T_C)$



2 Safe operating area

$I_D = f(V_{DS})$


parameter : $D = 0$, T_C=25°C



3 Transient thermal impedance

$Z_{thJC} = f(t_p)$


parameter: $D = t_p/T$



4 Typ. output characteristic

$I_D = f(V_{DS})$; T_j=25°C

parameter: t_p = 10 µs, V_{GS}




Downloaded from Arrow.com.

5 Typ. output characteristic

$I_D = f(V_{DS})$; T_j=150°C


parameter: t_p = 10 µs, V_{GS}



6 Typ. drain-source on resistance

$R_{DS(on)}=f(I_D)$


parameter: T_j=150°C, V_{GS}



7 Drain-source on-state resistance

$R_{DS(on)} = f(T_j)$


parameter : I_D = 2 A, V_{GS} = 10 V



8 Typ. transfer characteristics

$I_D = f(V_{GS})$; $V_{DS} \geq 2 \times I_D \times R_{DS(on)max}$

parameter: t_p = 10 µs




Downloaded from Arrow.com.

9 Typ. gate charge

$V_{GS} = f\ (Q_{Gate})$


parameter: I_D = 3.2 A pulsed



10 Forward characteristics of body diode

$I_F = f\ (V_{SD})$


parameter: T_j , tp = 10 µs



11 Typ. drain current slope

d*i*/d*t* = f(R_G), inductive load, T_j = 125°C


par.: V_{DS}=380V, V_{GS}=0/+13V, I_D=3.2A



12 Typ. switching time

$t = f\ (R_G)$, inductive load, T_j=125°C

par.: V_{DS}=380V, V_{GS}=0/+13V, I_D=3.2 A




Downloaded from Arrow.com.

13 Typ. switching time

$t = f(I_D)$, inductive load, T_j=125°C


par.: V_{DS}=380V, V_{GS}=0/+13V, R_G=20Ω



14 Typ. drain source voltage slope

dv/dt = f(R_G), inductive load, T_j = 125°C


par.: V_{DS}=380V, V_{GS}=0/+13V, I_D=3.2A



15 Typ. switching losses

$E = f(I_D)$, inductive load, T_j=125°C


par.: V_{DS}=380V, V_{GS}=0/+13V, R_G=20Ω



16 Typ. switching losses

$E = f(R_G)$, inductive load, T_j=125°C

par.: V_{DS}=380V, V_{GS}=0/+13V, I_D=3.2A




Downloaded from Arrow.com.

17 Avalanche SOA

$I_{AR} = f(t_{AR})$


par.: $T_j \leq 150$ °C



18 Avalanche energy


$E_{AS} = f(T_j)$

par.: I_D = 2.4 A, V_{DD} = 50 V



19 Drain-source breakdown voltage


$V_{(BR)DSS} = f(T_j)$



20 Avalanche power losses

$P_{AR} = f(f)$

parameter: E_{AR}=0.2mJ




Downloaded from Arrow.com.

21 Typ. capacitances


$C = f(V_{DS})$

parameter: V_{GS}=0V, f=1 MHz




22 Typ. C_{oss} stored energy

$E_{oss}=f(V_{DS})$




Definition of diodes switching characteristics



Downloaded from Arrow.com.

PG-TO-251-3-11



DIM	MILLIMETERS		INCHES	
	MIN	MAX	MIN	MAX
A	2.18	2.39	0.086	0.094
A1	0.80	1.14	0.031	0.045
b	0.64	0.89	0.025	0.035
b2	0.65	1.15	0.026	0.045
b4	4.95	5.50	0.195	0.217
c	0.46	0.58	0.018	0.023
c2	0.46	0.89	0.018	0.035
D	5.97	6.22	0.235	0.245
D1	5.04	5.44	0.198	0.214
E	6.35	6.73	0.250	0.265
E1	4.90	5.10	0.193	0.201
e	2.29		0.090	
e1	4.57		0.180	
N	3		3	
L	3.40	3.60	0.134	0.142
L1	0.90	1.10	0.035	0.043
L2	0.90	1.10	0.035	0.043

DOCUMENT NO.
Z8B00003329

SCALE 0 2.0 0 2.0 4mm

EUROPEAN PROJECTION

ISSUE DATE
17-01-2008

REVISION
03

Dimensions in mm/ inches

Downloaded from Arrow.com.

Published by
Infineon Technologies AG
81726 Munich, Germany
© 2008 Infineon Technologies AG
All Rights Reserved.

Legal Disclaimer
The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. With respect to any examples or hints given herein, any typical values stated herein and/or any information regarding the application of the device, Infineon Technologies hereby disclaims any and all warranties and liabilities of any kind, including without limitation, warranties of non-infringement of intellectual property rights of any third party.

Information
For further information on technology, delivery terms and conditions and prices, please contact the nearest Infineon Technologies Office (www.infineon.com).

Warnings
Due to technical requirements, components may contain dangerous substances. For information on the types in question, please contact the nearest Infineon Technologies Office.
Infineon Technologies components may be used in life-support devices or systems only with the express written approval of Infineon Technologies, if a failure of such components can reasonably be expected to cause the failure of that life-support device or system or to affect the safety or effectiveness of that device or system. Life support devices or systems are intended to be implanted in the human body or to support and/or maintain and sustain and/or protect human life. If they fail, it is reasonable to assume that the health of the user or other persons may be endangered.

Downloaded from Arrow.com.