

Control cabinet feed-through - VS-BH-M12FSD-RJ45/90 - 1657261

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Control cabinet feed-through, M12, 4-pos., D-coded on RJ45 socket, socket input 90°, IP65/67



Ethernet

Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	36.500 g
Custom tariff number	85366990
Country of origin	Germany

Technical data

Mechanical characteristics

Thread type	M12
Weight	35.4 g
Flammability rating according to UL 94	V0

Ambient conditions

Ambient temperature (operation)	-25 °C ... 85 °C
Degree of protection	IP65
	IP67

Material data

Contact material	Copper alloy
Housing material	PA
Mounting type	Rear mounting

Electrical characteristics

Number of positions	4
---------------------	---

Control cabinet feed-through - VS-BH-M12FSD-RJ45/90 - 1657261

Technical data

Electrical characteristics


Nominal voltage U_N	48 V
Nominal current I_N	1 A
Transmission characteristics (category)	CAT5 (IEC 11801:2002)
GRP transmission properties	CAT5 (IEC 11801:2002)
Transmission speed	100 Mbps
Rated current	1 A
Rated voltage (III/3)	50 V

Standards and Regulations


Flammability rating according to UL 94	V0
--	----

Drawings

Dimensional drawing




Dimensional drawing




Mounting cutout

Exploded view



Circuit diagram



Circuit diagram

Exploded drawing

Control cabinet feed-through - VS-BH-M12FSD-RJ45/90 - 1657261

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27060307
eCl@ss 6.0	27279220
eCl@ss 7.0	27440103

ETIM

ETIM 3.0	EC002061
ETIM 4.0	EC002535

UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501