



Part Number : [348033212](#)
Product Description : CTX64 Female Terminal, Tin,
L-Grip, D-Wind, Left Payoff, SAE 20
Series Number : 34803
Status : Active
Product Category : Crimp Terminals



Documents and Resources

Drawings

- [348033212 sd.pdf](#)
- [PK-31301-053-001.pdf](#)
- [313025040-000.pdf](#)
- [STEP AP242](#)
- [SOLIDWORKS](#)
- [Creo](#)

Specifications

- [AS-502306-002-001.pdf](#)
- [AS-560065-001-001.pdf](#)
- [AS-560065-001-CH-001.pdf](#)
- [AS-502306-002-FR-001.pdf](#)
- [AS-560065-001-FR-001.pdf](#)
- [AS-502306-002-CH-001.pdf](#)
- [PS-502306-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-

	DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	34803
Description	CTX64 Female Terminal, Tin, L-Grip, D-Wind, Left Payoff, SAE 20
Application	Signal, Wire-to-Board
Product Name	CTX64
UPC	887191519296

Electrical

Current - Maximum per Contact	See Receptacle Product Spec.
Voltage - Maximum	14V DC

Physical

Gender	Female
Grip Code	L
Material - Metal	Copper Alloy

Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.124/g
Packaging Type	Reel
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.40-1.90mm
Wire Size (AWG)	20
Wire Size mm ²	0.50-0.85

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Mates With / Use With

Use with Part(s)

Description	Part Number
Stac64 Receptacle Housings	<u>34729</u>

Application Tooling

Global

Description	Part Number
Hand Crimp Tool for CTX64 Receptacle Terminal, 0.50, 0.75, 0.85mm ² and 20 AWG	<u>638193800</u>
FineAdjust Applicator for CTX64 Mat Seal Receptacle Terminals, for Wire Process Use Only	<u>639032700</u>

This document was generated on May 28, 2026