
TE Connectivity: Every Connection Counts
© 2017 TE Connectivity Ltd. family of companies. All Rights Reserved

TERMINALS & SPLICES

QUICK DISCONNECTS



✔ Active

TE CONNECTIVITY (TE)

B-106-3631CS100

Raychem

CC2628-000
TE Internal Number: CC2628-000
Alias ID: B-106-3631CS100

Not Yet Reviewed for EU RoHS
Not Yet Reviewed for EU ELV

Wire Size (AWG) 22 – 18

Wire Size (mm²) .3 – .9

Wire Size (CMA) 509 – 1900

Mating Tab Width 6.35 mm [.25 in]

Mating Tab Thickness .81 mm [.032 in]

PRODUCT DRAWING
English

DOCUMENTATION

Product Drawings

Duraseal Push-On Receptacle
PDF
English

Catalog Pages/Data Sheets

1654025_Sec8_B-106
PDF
English

Product Specifications

Product Specification

Installation Procedure For Duraseal Splices And Terminals

Downloaded from Arrow.com.

PDF

English

FEATURES

Please review product documents or contact us for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Terminates To Wire & Cable
FASTON No
Insulated Wire Support No
Disconnect Type Quick Disconnect Pin
Insertion Force Normal
Insulated Yes
Wire Stop No
Wire/Cable Composition Stranded

Configuration Features

Connection Capacity Single

Body Features

Fully Insulated No
Plating Material Tin
Insulation Material Polyamide

Contact Features

Terminal Orientation Straight

Dimensions

Wire Size (AWG) 22 – 18
Wire Size (mm^2) .3 – .9
Wire Size (CMA) 509 – 1900
Mating Tab Width 6.35 mm [.25 in]
Mating Tab Thickness .81 mm [.032 in]
Wire Insulation Diameter (Max) 4.06 mm [.16 in]
Overall Length 30 mm [1.181 in]

Usage Conditions

Operating Temperature Range (°C) 125

Industry Standards

UL Rating Listed

Packaging Features

Packaging Method Bag
Packaging Quantity 100

Downloaded from Arrow.com.

Other

Barrel Color Red

PRODUCT COMPLIANCE

Statement of Compliance

Statement of Compliance

PDF

Downloaded from Arrow.com.