





REV.	DATE	ECR NO.	DESCRIPTION
NC	09/09/10	XXXXXX	INITIAL RELEASE



1. FREQUENCY RANGE: DC – 3 GHz
2. VSWR (RETURN LOSS): 1.15, MAX.
3. CRIMPED FERRULE
HEX CRIMP SIZE .213"
4. CRIMPED CONTACT PIN
HEX CRIMP SIZE .043"

8	FERRULE	COPPER	NICKEL	1	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex								
7	CONTACT PIN	BRASS	GOLD	1		DRAWN	M.ZHANG						09/09/10			
6	BARREL	BRASS	NICKEL	1		CHECKED										
5	OUT CONTACT	BER. COPPER	GOLD	1		ISSUED			PART DESCRIPTION							
4	INSULATOR	PTFE	NATURAL	1		SHEET	1 OF 1		1.0/2.3 PUSH-PULL CRIMP PLUG (FOR BELDEN 1855A CABLE)							
3	SPRING	SUS 301H	PASSIVATED	1					PART NO.							
2	BODY	BRASS	NICKEL	1					282138-75							
1	SHELL	BRASS	NICKEL	1					DWG. NO.		282138-75.DWG	REV.	NC	SIZE	A	SCALE
DESCRIPTION		MATERIAL		FINISH	QTY	C:/CONNEX/282125-75.DWG										