



**HSB100FR, Heat Shrink Tubing, 1" ID Min.(Exp.), 0.5" ID Max.(Rec.), 1/0-4/0 Flex, PVC, Thin Wall, Flame Retardant, Black, 600V.**

By Burndy  
Catalog # [HSB100FR](#)

Heat Shrink Tubing, 1" ID Min.(Exp.), 0.5" ID Max.(Rec.), 1/0-4/0 Flex, PVC, Thin Wall, Flame Retardant, Black, 600V.

**Features**

- Flame Retardant
- Flexible Polyvinylchloride
- 2:1 Shrink Ratio
- 600 Volts

**Application**

For Terminations And Splices

**General**

Catalog Number	HSB100FR
Connector Type	THIN WALL TUBES/REELS
EU RoHS Indicator	Yes
Material	Polyvinyl chloride
Sub Brand	HEAT SHRINK
Type	HS-FR, Thin Wall, Flexible, Fire Retardant
UPC	781810265741

**Conductor Related**

Conductor Range	#1/0 AWG to #4/0 AWG
Conductor Size	4/0AWG - 300kcmil

**Certifications And Compliance**

Buy American Compliant	Yes
Certification - CSA Approved	Yes
Certification - ETL	No
Certified Listed	TAA Compliant (All status valid till December 2024)
Standards - RoHS Compliance	CM
Status	
UL Listed	No

**Logistics**

Minimum Pack Quantity	1
-----------------------	---

**Product Assets**

- [Catalogs - BURNDY Master Catalog - Full Line BURNDY Catalog](#)
- [Interactive Catalog - BURNDY Full-Line Digital Catalog](#)
- [Literature - Polyolefin Thin Wall Heat Shrink Cross Reference Guide](#)
- [Product Cross Section Image\(s\) - BUR\\_HSC100FR\\_LineArt](#)
- [Sales Drawings - 50015598](#)
- [Specifications - HSB100FR](#)

