

Stamped contacts Crimp male contacts diameter 1,5 mm for wire gauge AWG 28 - 24 gold plated

Part No. HN01 015 0052 2

Series Contacts

Subseries Contact Stamped contacts



COMMON CHARACTERISTICS		
Contact diameter		1,5 mm
Insulation diameter		0,7 - 1,6 mm
Wire gauge from		0,09
Wire gauge to		0,25
Wire gauge (AWG) from		28
Wire gauge (AWG) to		24
Packaging / supplied as		Contacts on reel for crimp machines-right hand side
No. of pieces		2.000
Sex of Contact		Pin
Type of contact		Stamped/rolled crimp contact
ELECTRICAL CHARACTERISTICS		
Contact resistance	DIN EN 60512-2-1, Test 2a / IEC 60512-2-1, Test 2a	< 5 mΩ

