


HONEYWELL PART NUMBER
22SM25-T
PRODUCT CODE TXP2460

REV	DOCUMENT	CHANGED BY	CHECK
4	0038111	PK 20MAY08	ASD



NOTE -


1 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375 ± .002 CENTERS

2- TERMINALS ARE PLATED FOR SOLDERING

3- SWITCH WILL WITHSTAND TEMPERATURE OF 250°F

RELEASE NO. PR - 6253

REPLACES -

CHARACTERISTICS		ELECTRICAL DATA			DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± TWO PLACE .XX ± THREE PLACE .XXX ± FOUR PLACE .XXXX ± ANGLES ± 0.030 0.015 0.005		DRAWN	VK	19 OCT 07	Honeywell				
OPERATING FORCE — — — — 3 - 5 OZ		CONTACT ARRANGEMENT SPDT					CHECK	RJ	19 OCT 07					
RELEASE FORCE — — — — 1 OZ MIN		30 VOLTS DC RATING			0.030 0.015 0.005		THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH - BASIC				
DIFFERENTIAL TRAVEL — — — .004 MAX			SEA LEVEL	50,000 FT										
OVERTRAVEL — — — — — .005 MIN		MAXIMUM INRUSH 24 AMP					INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	DRAWING NAME		REV
		INDUCTIVE	3 AMP	2.5 AMP						B	I	22SM25-T		4
		RESISTIVE	5 AMP	5 AMP	THIRD ANGLE PROJECTION 		RASTER			SCALE	-	WEIGHT .006 LB MAX	SHEET 1 OF 1	
		APPROVALS								KEMA, CE		5A, 250V ~ T85 1E4		UL, CSA