



HB-2X2-W

~50° wide beam

SPECIFICATION:

Dimensions 50.0 x 50.0 Height 8.5 mm Fastening glue, pin, screw ROHS compliant yes 1



MATERIALS:

ComponentTypeMaterialColourFinishLength (mm)HB-2X2-WMulti-lensPMMAclear

ORDERING INFORMATION:

Component


» Box size: 480 x 280 x 300 mm

C12361_HB-2X2-W

Qty in box MOQ MPQ Box weight (kg) 800 160 160 9.1



PRODUCT DATASHEET C12361_HB-2X2-W



See also our general installation guide: www.ledil.com/installation_guide






LED Bridgelux SMD 5050

FWHM / FWTM 55.0° / 93.0° Efficiency 94 % Peak intensity 0.9 cd/lm LEDs/each optic

Light colour/type White Required components:




Light distribution files



QUICK FLUX XTP 2x4 xxx LS G5

FWHM / FWTM 52.0° / 85.0° Efficiency 94 % Peak intensity 1 cd/lm LEDs/each optic Light colour/type White Required components:




Light distribution files



LED QUICK FLUX XTP 2x6 xxx LS G5

 $\mathsf{FWHM}\,/\,\mathsf{FWTM}$ 52.0° / 86.0° Efficiency 94 % Peak intensity 1 cd/lm LEDs/each optic Light colour/type White Required components:




Light distribution files



CREE \$

J Series 5050C 6V E Class LED


54.0° / 86.0° FWHM / FWTM Efficiency 94 % Peak intensity 1 cd/lm LEDs/each optic White Light colour/type Required components:



Light distribution files

CREE \$


FWHM / FWTM 48.0° / 85.0° Efficiency 86 % Peak intensity 1 cd/lm LEDs/each optic Light colour/type White Required components:



Light distribution files

CREE \$

LED XD16 FWHM / FWTM 48.0° / 89.0° Efficiency 91 % Peak intensity 0.9 cd/lm LEDs/each optic 1 Light colour/type White Required components:




Light distribution files



CREE \$


LED XD16 FWHM / FWTM 54.0° / 94.0° Efficiency 91 % Peak intensity 0.9 cd/lm LEDs/each optic Light colour/type White Required components:



Light distribution files

CREE \$


XHP35 HD FWHM / FWTM 57.0° / 92.0° Efficiency 85 % Peak intensity 0.8 cd/lm LEDs/each optic Light colour/type White Required components:



Light distribution files

CREE \$

LED XM-L FWHM / FWTM 57.0° / 90.0° Efficiency 89 % Peak intensity 0.9 cd/lm LEDs/each optic 1 Light colour/type White Required components:




Light distribution files



CREE +


LED XM-L2
FWHM / FWTM 56.0° / 85.0°
Efficiency 87 %
Peak intensity 0.9 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

CREE \$


LED XM-L3
FWHM / FWTM 56.0° / 87.0°
Efficiency 95 %
Peak intensity 0.9 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

CREE -

LED XP-G
FWHM / FWTM 52.0°
Efficiency 88 %
Peak intensity 0.9 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files



CREE \$ XP-G2 LED 51.0° / 84.0° FWHM / FWTM Efficiency 94 % Peak intensity 1 cd/lm LEDs/each optic

White




Light distribution files

CREE \$


Light colour/type Required components:

XP-L HD FWHM / FWTM 56.0° / 90.0° Efficiency 87 % Peak intensity 0.8 cd/lm LEDs/each optic Light colour/type White Required components:



CREE \$

LED XP-L HI FWHM / FWTM 50.0° / 83.0° Efficiency 93 % Peak intensity 1 cd/lm LEDs/each optic 1 Light colour/type White Required components:



Light distribution files



CREE \$

 LED
 XP-L2

 FWHM / FWTM
 56.0° / 96.0°


 Efficiency
 92 %

 Peak intensity
 0.8 cd/lm

 LEDs/each optic
 1

 Light colour/type
 White


 Required components:



Light distribution files

CREE \$

LED XT-E
FWHM / FWTM 50.0° / 88.0°
Efficiency 87 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

inventronics

LED PL-BRICK HP 3800 2x8 SSG

FWHM / FWTM 52.0° / 75.0°
Efficiency 98 %
Peak intensity 1.1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files



DIVIDITY LUMILEDS

LED LUXEON 5050 Round LES

FWHM / FWTM 55.0° / 91.0°
Efficiency 94 %
Peak intensity 0.9 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

UMILEDS

LED LUXEON 5050 Square LES


FWHM / FWTM 55.0° / 91.0°
Efficiency 94 %
Peak intensity 0.9 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

MILEDS

LED LUXEON MZ
FWHM / FWTM 53.0° / 86.0°
Efficiency 92 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files



LUMILEDS


LUXEON Q 50.0° / 86.0° FWHM / FWTM Efficiency 86 % Peak intensity 0.9 cd/lm LEDs/each optic Light colour/type White Required components:



Light distribution files

LUMILEDS


LUXEON Rebel ES FWHM / FWTM 51.0° / 82.0° Efficiency 87 % Peak intensity 0.9 cd/lm LEDs/each optic Light colour/type White Required components:



Light distribution files

LUMILEDS

LED LUXEON T FWHM / FWTM 55.0° Efficiency 87 % Peak intensity 0.9 cd/lm LEDs/each optic Light colour/type White Required components:




Light distribution files






LED LUXEON TX
FWHM / FWTM 50.0° / 80.0°
Efficiency 88 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

UMILEDS


LED LUXEON V
FWHM / FWTM 55.0° / 91.0°
Efficiency 93 %
Peak intensity 0.9 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

MUMILEDS

LED LUXEON V2
FWHM / FWTM 51.0° / 86.0°
Efficiency 94 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files





LUXEON Z ES FWHM / FWTM 46.0° / 76.0° Efficiency 87 % Peak intensity 1.2 cd/lm LEDs/each optic White Light colour/type Required components:




Light distribution files



SST-10-B130 FWHM / FWTM 51.0° / 80.0° Efficiency 99 % Peak intensity 1 cd/lm LEDs/each optic

Light colour/type Deep Red

Required components:




Light distribution files



LED RecLED 122x50mm 1900lm 730 2x4 Opt G1

FWHM / FWTM 50.0° / 75.0° Efficiency 98 % Peak intensity 1.1 cd/lm LEDs/each optic Light colour/type White Required components:




Light distribution files



WNICHIA


NCSxx19A 48.0° / 77.0° FWHM / FWTM Efficiency 85 % Peak intensity 1.1 cd/lm LEDs/each optic Light colour/type White Required components:



Light distribution files

WNICHIA


NCSxx19B FWHM / FWTM 50.0° / 83.0° Efficiency 85 % Peak intensity 1 cd/lm LEDs/each optic Light colour/type White Required components:



Light distribution files

WNICHIA

LED NS9x383 $\mathsf{FWHM}\,/\,\mathsf{FWTM}$ 54.0° / 93.0° Efficiency 86 % Peak intensity 0.9 cd/lm LEDs/each optic 1 Light colour/type White Required components:




Light distribution files



WNICHIA


LED NVSW219D
FWHM / FWTM 53.0° / 83.0°
Efficiency 94 %
Peak intensity 0.9 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

WNICHIA


LED NVSW219F
FWHM / FWTM 54.0° / 81.0°
Efficiency 97 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

WNICHIA

LED NVSW319B
FWHM / FWTM 56.0° / 93.0°
Efficiency 93 %
Peak intensity 0.9 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files



WNICHIA


NVSW3x9A 53.0° / 88.0° FWHM / FWTM Efficiency 92 % Peak intensity 0.9 cd/lm LEDs/each optic Light colour/type White Required components:



Light distribution files

WNICHIA

NVSxE21A FWHM / FWTM 43.0° / 80.0° Efficiency 86 % Peak intensity 1.1 cd/lm LEDs/each optic Light colour/type White Required components:




Light distribution files

WNICHIA

LED NVSxx19B/NVSxx19C

 $\mathsf{FWHM}\,/\,\mathsf{FWTM}$ 51.0° / 82.0° Efficiency 85 % Peak intensity 1 cd/lm LEDs/each optic 1 Light colour/type White Required components:



Light distribution files



WNICHIA

 LED
 NWSx229A

 FWHM / FWTM
 57.0° / 90.0°


 Efficiency
 86 %

 Peak intensity
 0.9 cd/lm

 LEDs/each optic
 1

 Light colour/type
 White

 Required components:



Light distribution files




LED OLP-5065F6L-06A
FWHM / FWTM 56.0° / 90.0°
Efficiency 88 %
Peak intensity 0.9 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:

Light distribution files

OSRAM

LED Duris S8
FWHM / FWTM 55.0° / 91.0°
Efficiency 93 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files



OSRAM Opto Semiconductors

OSCONIQ C 3030 LED FWHM / FWTM 47.0° / 76.0° Efficiency 96 % Peak intensity 1.2 cd/lm LEDs/each optic

White Light colour/type Required components:




Light distribution files

OSRAM Opto Semiconductore

OSCONIQ C 3030 FWHM / FWTM 47.0° / 76.0° Efficiency 96 % Peak intensity 1.2 cd/lm

LEDs/each optic Light colour/type White Required components:




Light distribution files

OSRAM

LED OSLON Square PC

FWHM / FWTM 54.0° / 85.0° Efficiency 87 %

Peak intensity 0.9 cd/lm LEDs/each optic 1 Light colour/type White Required components:




Light distribution files



OSRAM Opto Semiconductors

LED OSLON SSL 80
FWHM / FWTM 43.0° / 70.0°
Efficiency 89 %
Peak intensity 1.3 cd/lm
LEDs/each optic 1
Light colour/type White




Light distribution files

PHILIPS

Required components:

LED Fortimo FastFlex LED 2x8 DA (U)HE

FWHM / FWTM 54.0° / 87.0°
Efficiency 97 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

PHILIPS

LED Fortimo FastFlex LED 2x8 DA G4

FWHM / FWTM 52.0° / 82.0°
Efficiency 94 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files



PHILIPS

LED Fortimo FastFlex LED 2x8 DA G4+

FWHM / FWTM 55.0° / 88.0°
Efficiency 97 %
Peak intensity 0.9 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

PHILIPS

LED Fortimo FastFlex LED 2x8 DA G5

FWHM / FWTM 50.0° / 77.0°
Efficiency 97 %
Peak intensity 1.1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

SAMSUNG

LED HILOM RC12 Z (LH181B)

FWHM / FWTM 46.0° / 84.0°
Efficiency 97 %
Peak intensity 1.1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files



SAMSUNG

LED HiLOM RH12 Z (LH351C)

FWHM / FWTM 54.0° / 84.0°
Efficiency 96 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

SAMSUNG

LED HILOM RH16 (LH351C)

FWHM / FWTM 53.0° / 83.0°
Efficiency 94 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

SAMSUNG

LED HILOM RM12 Z (LH502C)

FWHM / FWTM 55.0° / 94.0°
Efficiency 94 %
Peak intensity 0.9 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files



SAMSUNG

HiLOM RM16 Z (LH502C)

FWHM / FWTM 55.0° / 95.0° Efficiency 96 % Peak intensity 0.9 cd/lm LEDs/each optic White Light colour/type Required components:




Light distribution files

SAMSUNG

HiLOM RM8 Z (LH502C)


FWHM / FWTM 56.0° / 95.0° Efficiency 96 % Peak intensity 0.9 cd/lm LEDs/each optic Light colour/type White Required components:



Light distribution files

SAMSUNG

LED LH351A FWHM / FWTM 49.0° / 81.0° Efficiency 89 % Peak intensity 1 cd/lm LEDs/each optic Light colour/type White Required components:



Light distribution files



SAMSUNG

 LED
 LH351B

 FWHM / FWTM
 55.0° / 85.0°


 Efficiency
 86 %

 Peak intensity
 0.9 cd/lm

 LEDs/each optic
 1

 Light colour/type
 White


 Required components:



Light distribution files

SAMSUNG


LED LH351C
FWHM / FWTM 53.0° / 85.0°
Efficiency 93 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

SAMSUNG

LED LH351D
FWHM / FWTM 56.0° / 90.0°
Efficiency 91 %
Peak intensity 0.9 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files



SAMSUNG


LED LH351Z
FWHM / FWTM 50.0° / 77.0°
Efficiency 87 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:



Light distribution files

SAMSUNG

LED LH508A
FWHM / FWTM 56.0° / 92.0°
Efficiency 93 %
Peak intensity 0.9 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files




LED LED-Pa-L15c2W11c2-xxx-C050-01


FWHM / FWTM 50.0° / 78.0°
Efficiency 96 %
Peak intensity 1.1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files













































TRIDONIC

LED RLE 2x8 4000lm HP EXC2 OTD

FWHM / FWTM 51.0° / 84.0°
Efficiency 94 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

TRIDONIC

LED RLE 2x8 6000lm HP HE EXC3 OTD

FWHM / FWTM 54.0° / 92.0°
Efficiency 95 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files

TRIDONIC

LED RLE G1 49x121mm 2000lm xxx EXC OTD

FWHM / FWTM 52.0° / 83.0°
Efficiency 94 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:




Light distribution files



TRIDONIC

LED RLE G1 49x133mm 2000lm xxx EXC OTD

FWHM / FWTM 52.0° / 83.0° Efficiency 94 % Peak intensity 1 cd/lm LEDs/each optic White Light colour/type Required components:




Light distribution files

TRIDONIC

RLE G1 49x223mm 4000lm xxx EXC OTD

FWHM / FWTM 52.0° / 83.0° Efficiency 94 % Peak intensity 1 cd/lm LEDs/each optic Light colour/type White Required components:




Light distribution files

TRIDONIC

RLE G1 49x245mm 4000lm xxx EXC OTD LED

FWHM / FWTM 52.0° / 83.0° Efficiency 94 % Peak intensity 1 cd/lm LEDs/each optic 1 Light colour/type White Required components:



Light distribution files






J Series 5050 Round LES LED

57.0° / 84.0° FWHM / FWTM Efficiency 94 % Peak intensity 1 cd/lm LEDs/each optic 1 Light colour/type White

Required components:




Light distribution files

CREE \$

J Series 5050B 6V K Class LFD

FWHM / FWTM 56.0° / 86.0° Efficiency 89 % Peak intensity 1 cd/lm LEDs/each optic Light colour/type White

Required components:




Light distribution files

Protective plate, glass



J Series 5050B 6V K Class LED

FWHM / FWTM 56.0° / 85.0° 94 % Efficiency Peak intensity 1 cd/lm LEDs/each optic Light colour/type White Required components:








LED MHB-A/B FWHM / FWTM 58.0° / 93.0° Efficiency 94 % Peak intensity 1 cd/lm LEDs/each optic Light colour/type White

Required components:




Light distribution files

CREE \$

XHP35 HI LED FWHM / FWTM 52.0° / 73.0° Efficiency 93 % Peak intensity 1.2 cd/lm LEDs/each optic 1 Light colour/type White

Required components:




Light distribution files

CREE \$

XM-L RGBW (XMLDCL HI) LED

FWHM / FWTM 52.0° / 78.0° Efficiency 95 % Peak intensity 1.2 cd/lm LEDs/each optic Light colour/type **RGBW**

Required components:



Light distribution files



CREE \$


LED XP-E FWHM / FWTM 50.0° / 68.0° Efficiency 94 % Peak intensity 1.2 cd/lm LEDs/each optic 1 Light colour/type White Required components:

Light distribution files

CREE \$

XP-E2 LED FWHM / FWTM 48.0° / 70.0° Efficiency 96 % Peak intensity 1.2 cd/lm LEDs/each optic 1 Light colour/type White

Required components:



Light distribution files

CREE \$

XP-G2 HE LED FWHM / FWTM 57.0° / 82.0° Efficiency 95 % Peak intensity 0.9 cd/lm LEDs/each optic Light colour/type White Required components:





LED XP-G3
FWHM / FWTM 54.0° / 79.0°
Efficiency 94 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:

Light distribution files

CREE -

LED XP-G3
FWHM / FWTM 55.0° / 81.0°
Efficiency 88 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:


Light distribution files

Protective plate, glass

CREE \$

LED XP-G4
FWHM / FWTM 54.0° / 70.0°
Efficiency 88 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:


Protective plate, glass





CREE \$

LED XP-G4 FWHM / FWTM 52.0° / 69.0° Efficiency 96 % Peak intensity 1.1 cd/lm LEDs/each optic 1 Light colour/type White Required components:




Light distribution files

CREE \$

XP-G4 HI LED FWHM / FWTM 52.0° / 72.0° Efficiency 96 % Peak intensity 1.1 cd/lm LEDs/each optic 1 Light colour/type White

Required components:




Light distribution files

CREE \$

XP-L HD LED FWHM / FWTM 58.0° / 80.0° Efficiency 87 % Peak intensity 0.9 cd/lm LEDs/each optic Light colour/type White Required components:

Protective plate, glass








LED XP-L HD FWHM / FWTM 56.0° / 79.0° Efficiency 95 % Peak intensity 1 cd/lm LEDs/each optic Light colour/type White Required components:

Light distribution files

CREE \$

XP-L HI LED FWHM / FWTM 52.0° / 72.0° Efficiency 88 % Peak intensity 1.1 cd/lm LEDs/each optic 1 Light colour/type White

Required components:




Light distribution files

Protective plate, glass

CREE \$

XP-L2 LED FWHM / FWTM 58.0° / 84.0° Efficiency 95 % Peak intensity 0.9 cd/lm LEDs/each optic Light colour/type White Required components:





CREE \$

LED XP-L2 FWHM / FWTM 58.0° / 86.0° Efficiency 89 % Peak intensity 0.9 cd/lm LEDs/each optic 1 Light colour/type White

Protective plate, glass


Required components:

Light distribution files

CREE \$

LED XQ-E HI FWHM / FWTM 42.0° / 68.0° Efficiency 93 % Peak intensity 1.4 cd/lm LEDs/each optic 1 Light colour/type White

Required components:




Light distribution files

LUMILEDS

LUXEON 3030 2D (Round LES)

FWHM / FWTM 49.0° / 73.0° Efficiency 94 % Peak intensity 1.2 cd/lm LEDs/each optic Light colour/type White Required components:








Required components:

LFD LUXEON 3535L $\mathsf{FWHM}\,/\,\mathsf{FWTM}$ 49.0° / 73.0° Efficiency 94 % Peak intensity 1.2 cd/lm LEDs/each optic 1 Light colour/type White

Light distribution files




LUMILEDS

LUXEON 5050 HE LFD FWHM / FWTM 56.0° / 84.0° Efficiency 94 % Peak intensity 1 cd/lm LEDs/each optic

White

Required components:

Light colour/type



Light distribution files



LUXEON 5050 HE FWHM / FWTM 54.0° / 84.0° Efficiency 89 % Peak intensity 1 cd/lm LEDs/each optic

White

Light colour/type Required components:

Light distribution files

Protective plate, glass






LED LUXEON 5050 HE Plus

FWHM / FWTM 56.0° / 87.0°
Efficiency 94 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour/type White

Required components:




Light distribution files



LED LUXEON 5050 Square LES

FWHM / FWTM 54.0° / 84.0°
Efficiency 89 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour/type White

Required components:



Light distribution files

Protective plate, glass

MILEDS

LED LUXEON A
FWHM / FWTM 52.0°

Efficiency %

LEDs/each optic 1

Light colour/type White

Required components:






LED LUXEON C
FWHM / FWTM 50.0° / 75.0°
Efficiency 94 %
Peak intensity 1.1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:

Light distribution files



LED LUXEON H50-2
FWHM / FWTM 52.0° / 68.0°
Efficiency 91 %
Peak intensity 4.7 cd/lm
LEDs/each optic 1
Light colour/type White

Required components:



Light distribution files



LED LUXEON HL2X
FWHM / FWTM 56.0° / 76.0°


Efficiency 93 %

Peak intensity 1 cd/lm

LEDs/each optic 1

Light colour/type White

Required components:








LFD LUXEON HL2X-D $\mathsf{FWHM}\,/\,\mathsf{FWTM}$ 58.0° / 78.0° Efficiency 96 % Peak intensity 1 cd/lm

LEDs/each optic Light colour/type White

Required components:



Light distribution files




LUXEON HL2X-D LFD FWHM / FWTM 58.0° / 80.0°

Efficiency 88 % Peak intensity 0.9 cd/lm

LEDs/each optic 1 Light colour/type White

Required components:




Light distribution files

Protective plate, glass

LUMILEDS

LUXEON HL2X-E FWHM / FWTM 56.0° / 78.0 + 77.0°

Efficiency 96 % Peak intensity 1 cd/lm LEDs/each optic Light colour/type White



Light distribution files





LFD LUXEON HL2X-E $\mathsf{FWHM}\,/\,\mathsf{FWTM}$ 56.0° / 78.0° Efficiency 89 %

Peak intensity 1 cd/lm LEDs/each optic Light colour/type White

Protective plate, glass

Required components:


Light distribution files



LUXEON HL2X-P LFD FWHM / FWTM 56.0° / 80.0°

Efficiency 95 % Peak intensity 1 cd/lm LEDs/each optic Light colour/type White

Required components:




Light distribution files



LUXEON HL4X FWHM / FWTM 57.0° / 82.0° Efficiency 95 % Peak intensity 1 cd/lm LEDs/each optic Light colour/type White

Required components:







Required components:

LED LUXEON HL4Z
FWHM / FWTM 50.0° / 74.0°
Efficiency 95 %
Peak intensity 1.2 cd/lm
LEDs/each optic 1
Light colour/type White

Light distribution files



LED LUXEON Rebel

FWHM / FWTM 52.0°
Efficiency %
LEDs/each optic 1
Light colour/type White


Required components:

Light distribution files



LED LUXEON XR-HL2X (L2H2-xxxxxxxMLU010)

FWHM / FWTM 56.0° / 77.0°
Efficiency 96 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:







LFD LUXEON XR-HL2X (L2H2-xxxxxxMLU010)

 $\mathsf{FWHM}\,/\,\mathsf{FWTM}$ 57.0° / 78.0° Efficiency 87 % Peak intensity 0.9 cd/lm LEDs/each optic 1 Light colour/type White

Required components:

Light distribution files


Protective plate, glass

ELUMINUS

SFT-12R-W-A LFD FWHM / FWTM 44.0° / 70.0° Efficiency 92 % Peak intensity 1.2 cd/lm

LEDs/each optic 1 Light colour/type White

Required components:




Light distribution files

Protective plate, glass



SFT-12R-W-A FWHM / FWTM 44.0° / 70.0° Efficiency 97 % Peak intensity 1.3 cd/lm LEDs/each optic Light colour/type White

Required components:








Required components:

LED SFT-40 Gen2
FWHM / FWTM 52.0° / 72.0°
Efficiency 96 %
Peak intensity 1.2 cd/lm
LEDs/each optic 1
Light colour/type White

Similated from photometric dota




Light distribution files



LED SFT-40 Gen2
FWHM / FWTM 52.0° / 72.0°
Efficiency 89 %
Peak intensity 1.1 cd/lm
LEDs/each optic 1

Light colour/type White Required components:




Light distribution files

Protective plate, glass



LED SST-20 Gen2
FWHM / FWTM 50.0° / 72.0°
Efficiency 96 %
Peak intensity 1.1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:

Simulated from photometric data




Light distribution files





LED SST-20F-W FWHM / FWTM 54.0° / 74.0° Efficiency 96 % Peak intensity 1.1 cd/lm LEDs/each optic Light colour/type White Required components:




Light distribution files



SST-25-W LFD FWHM / FWTM 52.0° / 74.0° Efficiency 96 % Peak intensity 1.1 cd/lm LEDs/each optic 1 Light colour/type White

Required components:



Light distribution files



SST-36F-W FWHM / FWTM 56.0° / 80.0° Efficiency 96 % Peak intensity 1 cd/lm LEDs/each optic Light colour/type White



Light distribution files



WNICHIA

Required components:


LED NFMW48xA
FWHM / FWTM 57.0° / 86.0°
Efficiency 94 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour/type White

Light distribution files



LED NV4WB35AM
FWHM / FWTM 54.0° / 78.0°
Efficiency 95 %
Peak intensity 1.2 cd/lm
LEDs/each optic 1
Light colour/type White

Required components:



Light distribution files



LED NVSxx19A
FWHM / FWTM 50.0°
Efficiency %
LEDs/each optic 1
Light colour/type White
Required components:




OSRAM Opto Semiconductors

Duris S8 LED FWHM / FWTM 57.0° / 88.0° Efficiency 90 % Peak intensity 1 cd/lm LEDs/each optic Light colour/type White

Protective plate, glass

Required components:

Light distribution files




OSRAM Opto Semiconductore

OSCONIQ C 2424 Gen1 LFD

FWHM / FWTM 48.0° / 70.0° Efficiency 96 % Peak intensity 1.3 cd/lm LEDs/each optic 1 Light colour/type White

Required components:



Light distribution files

OSRAM

OSCONIQ C 3030 LED FWHM / FWTM 50.0° / 72.0° Efficiency 88 % Peak intensity 1.1 cd/lm

LEDs/each optic Light colour/type White Required components:


Protective plate, glass



OSRAM Opto Semiconductors

LED OSCONIQ C 3030 FWHM / FWTM 50.0° / 71.0° Efficiency 96 % Peak intensity 1.2 cd/lm LEDs/each optic 1 Light colour/type White

Required components:




Light distribution files

OSRAM Opto Semiconductore

OSCONIQ P 3737 (2W version) LFD

FWHM / FWTM 48.0° / 70.0° Efficiency 93 % Peak intensity 1.2 cd/lm LEDs/each optic 1 Light colour/type White

Required components:



Light distribution files

OSRAM

OSCONIQ P 3737 (3W version)

FWHM / FWTM 54.0° / 77.0° Efficiency 94 % Peak intensity 1.1 cd/lm LEDs/each optic Light colour/type White Required components:

Light distribution files




OSRAM Opto Semiconductors

LED OSCONIQ P 3737 Flat

FWHM / FWTM 50.0° / 73.0°
Efficiency 96 %
Peak intensity 1.2 cd/lm
LEDs/each optic 1
Light colour/type White

Required components:




Light distribution files

OSRAM Opto Semiconductore

LED OSCONIQ S 5050 (Q9LR32)

FWHM / FWTM 56.0° / 84.0°
Efficiency 87 %
Peak intensity 1 cd/lm
LEDs/each optic 1
Light colour/type White

Required components:




Light distribution files

Protective plate, glass

OSRAM

LED OSCONIQ S 5050 (Q9LR32)

FWHM / FWTM 56.0° / 83.0°
Efficiency 95 %
Peak intensity 1.1 cd/lm
LEDs/each optic 1
Light colour/type White
Required components:






OSRAM Opto Semiconductors

LED OSCONIQ S 5050 SFC

FWHM / FWTM 55.0° / 82.0° Efficiency 94 % Peak intensity 1.1 cd/lm LEDs/each optic 1 Light colour/type White

Required components:




Light distribution files

OSRAM Opto Semiconductore

OSLON Square CSSRM2/CSSRM3 LFD

FWHM / FWTM 54.0° / 76.0° 87 % Efficiency Peak intensity 1 cd/lm LEDs/each optic Light colour/type White Required components:

Protective plate, glass




Light distribution files

OSRAM

OSLON Square CSSRM2/CSSRM3

FWHM / FWTM 52.0° / 74.0° Efficiency 96 % Peak intensity 1.1 cd/lm LEDs/each optic Light colour/type White Required components:

Light distribution files



50/55




PHILIPS

LFD Fortimo FastFlex LED 2x8 DAX G4

 $\mathsf{FWHM}\,/\,\mathsf{FWTM}$ 54.0° / 79.0° Efficiency 94 % Peak intensity 1 cd/lm LEDs/each optic Light colour/type White

Required components:




Light distribution files

SAMSUNG

LFD LH502D 55.0° / 86.0° FWHM / FWTM Efficiency 97 % Peak intensity 1.1 cd/lm LEDs/each optic 1

White


Light colour/type Required components:



Light distribution files



Acrich MJT 4040 LED FWHM / FWTM 52.0° / 77.0° Efficiency 94 % Peak intensity 1.1 cd/lm LEDs/each optic Light colour/type White



Light distribution files





LED MJT 5050 FWHM / FWTM 57.0° / 88.0° Efficiency 94 % Peak intensity 1 cd/lm LEDs/each optic Light colour/type White Required components:


Light distribution files



SEOUL DC 5050 6V LED

FWHM / FWTM 54.0° / 84.0° Efficiency 94 % Peak intensity 1.1 cd/lm LEDs/each optic 1 White Light colour/type

Required components:




Light distribution files



Z5M1/Z5M2 LED FWHM / FWTM 52.0° / 73.0° Efficiency 94 % Peak intensity 1.1 cd/lm


LEDs/each optic Light colour/type White Required components:







LED Z5M3-E1 FWHM / FWTM 54.0° / 74.0° Efficiency 96 % Peak intensity 1.1 cd/lm LEDs/each optic Light colour/type White Required components:




Light distribution files



LED Z5M4-E1 56.0° / 78.0° FWHM / FWTM Efficiency 96 % Peak intensity 1.1 cd/lm LEDs/each optic 1 White Light colour/type


Required components:



Light distribution files





Z5M4-E2 LED FWHM / FWTM 56.0° / 80.0° Efficiency 96 % Peak intensity 1 cd/lm LEDs/each optic Light colour/type White




Light distribution files











PRODUCT DATASHEET C12361_HB-2X2-W

GENERAL INFORMATION:

NOTE: The typical beam angle will be changed by different color, chip size and chip position tolerance. The typical total beam angle is the full angle measured where the luminous intensity is half of the peak value.

MATERIALS:

As part of our continuous research and improvement processes, and to ensure the best possible quality and availability of our products, LEDiL reserves the right to change material grades without notice.

PRODUCT DATA USER AGREEMENT AND DISCLAIMER:

The measured data in the provided downloadable LEDiL Product Datasheets and Mechanical 2D-Drawings is rounded and provided as reference for planning. LEDiL Oy's optical specifications have been verified by conducting performance testing of the products in accordance with the company's quality system. The reported data are averaged results of multiple measurements with typical variation. LEDiL Oy reserves the right to without prior notification make changes and improvements to its products.

LEDiL Oy assumes neither warranty, nor guarantee nor any other liability of any kind for the contents and correctness of the provided data. The provided data has been generated with highest diligence but the provided data may in reality not represent the complete possible variation range of all intrinsic parameters. Therefore, in certain cases a deviation from the provided data could occur.

LEDiL Oy reserves the right to undertake technical changes of its products without further notification which could lead to changes in the provided data. LEDiL Oy assumes no liability of any kind for the possible deviation from any provided data or any other damage resulting from the usage of the provided data.

The user agrees to this disclaimer and user agreement with the download or usage of the provided files.

LEDIL Oy

Joensuunkatu 7 FI-24100 SALO Finland

LEDiL Inc.

228 West Page Street Suite D Sycamore IL 60178 USA

Ledil Optics Technology (Shenzhen) Co., Ltd.

405 , Block B Casic Motor Building Shenzhen 518057 P.R.CHINA

Local sales and technical support

www.ledil.com/ where_to_buy

Shipping locations

Poznan, Poland Hong Kong, China

Distribution Partners

www.ledil.com/ where_to_buy