

Data Sheet

LL01CR-ANWxxL06

CREE 
 ▶ LED Solution Provider


MC-E(RGBW)


■ Features & Typical Applications

- High efficiency
- Available with 3 beam angles
- Optimized Uniformity
- Lens without Holder
- Spotlight
- Architectural Lighting
- Stage Lighting

■ Table of Contents


General Information & Product Nomenclature.....	P.2
Optical Specifications	P.3
Mechanical Specifications	P.4
Package Specifications.....	P.5

LL01CR-ANWxxL06

General Information

- Lens Material : PMMA 8N
- Operating Temperature range $-40^{\circ}\text{C} \sim +70^{\circ}\text{C}$ (upper limit $+80^{\circ}\text{C}$).
- Storage Temperature range $-40^{\circ}\text{C} \sim +70^{\circ}\text{C}$ (upper limit $+80^{\circ}\text{C}$).
 * Average transmittance in visible spectrum $400\text{nm} \sim 700\text{nm} > 90\%$.
- Usage and Maintenance:
 1. If necessary, clean lenses with mild soap, water and soft cloth.
 2. Never use any commercial cleaning solvents on lenses, like alcohol.
 3. Please handle or install lenses with wearing gloves, skin oils may damage lens or its optical characteristic.

Product Nomenclature



LL01CR-ANWxxL06




Optical Specifications

CREE
 LED Solution Provider



MC-E(RGBW)

Note: (1) All the results of analysis are based on 0 degrees of elevation.
 (2) Tolerance: $\pm 10\%$.
 (3) Led Luminous Flux(lm): 201($\pm 5\%$).



*The Field Angle is the angle between the two directions opposed to each other over the beam axis for which the luminous intensity is 10% that of the maximum luminous intensity.
 *This testing result is obtained through testing the popular rank LED samples which provided by the original manufacturer. Hence, the testing results would be varied as the users choose same LED model but different rank.

LL01CR-ANWxxL06

Mechanical Specification

1. Fixing method

☐ Glue

☐ Screw


☐ Tape

☒ Fixing-ring


☒ Frame

Note: (1) All dimensions are in mm.
 (2) All tolerance are ± 0.15 mm unless otherwise specified.

2. Lens dimension




3. Lens + Leds assembly instruction



4. Holder dimension




5. View assembly lens with LED:



LL01CR-ANWxxL06

Package Specifications

Item	Quantity	Total	Size(L*W*H)	G.W
plastic box	30 pcs/plastic box	30 pcs	32*29*3.15 cm	23.5g
outer box	6 plastic box/outer box	180 pcs	35*31*21 cm	



180 pcs/outer box



Note: