

BMME000505304R7MX1

Search by :

Part Number

Characteristics

Cross reference



MP



Closed Magnetic Circuit Type
Molding Processing & for Ultra High Current

Series Pdf

Product detail	
L(mm) ±	4.7±0.2
W(mm) ±	5.3Max.
T(mm) ±	3.0Max.
Inductance(uH)	4.7
Tolerance(±%)	20
Test Frequency	100kHz,0.25V
RDC(Ω)Max	0.053
RDC(Ω)Typ	0.0477
Isat(A)Typ	6
Irms(A)Typ	4.8
Operating Temperature	−55℃~125℃(Including self - temperature rise)


Part Numbering

Dimensions

Packing

Recommended Pattern

Electrical Characteristics



Products

Power Inductor
EMI-Common Mode Choke
EMI-Bead
RF-Signal Inductor
RF-Passives/Antennas
LAN Transformer
Resistor & Current Sensor

Applications

Automotive
Industrial
Server/DataCenter
Communication
Mobile and Tablet
Computer/Laptop
Consumer

Design Tools

Simulation Tool
Product Search Engine
E-Catalogue

About Us

Corporate Overview
Corporate Milestones
Core Technology
Certificates & Awards
Quality and Social Responsibility

Investor

Financial Information
Corporate governance
Stakeholder Contacts

[Media Center](#)

[New Products](#)

[Events](#)

[Product Notices](#)

Contact Us

[Contact Info](#)

[Contact Form](#)

[Join Chilisín](#)

[Terms of Use](#)

[Privacy policy](#)

[Sitemap](#)



Inductor



Resistor



Powder

Copyrights © 2018. Chilisín. All rights reserved.