




NOTE:

ONLY SUITABLE FOR RT360 SERIES 1804 and 1802 LAYOUT CONNECTOR



NOTES: (UNLESS OTHERWISE SPECIFIED)

1. MATERIAL:

- 1.1. CONTACT BODY: COPPER ALLOY.
- 1.2. POSITIONING CLIP: COPPER ALLOY.
- 1.3 CONTACT CAP: THERMOPLASTIC.

2. SPECIFICATIONS:

- 2.1 CURRENT RATING: 65A(MAX).
- 2.2 TERMINATION TYPE: CRIMPING.
- 2.3 WIRE RANGE: 8 AWG.

3. SUITABLE CONTACT : MS10A25x-8A.

4. RoHS COMPLIANT.

5. ALL DIMENSIONS ARE FOR REFERENCE USE ONLY.

REVISIONS					
REV	ECO	DESCRIPTION	DATE	BY	APPR
A1	-	PRELIMINARY DESIGN	26/Jul/23	RONALD	TOMMY

P/N	CONTACT PLATING(MATING AREA)
MP10A25F-8A	GOLD FLASH PLATING OVER NICKEL.
MP10A25S-8A	SILVER PLATING OVER NICKEL.

		SEE PART NUMBER CHART					
QUANTITY	PART NUMBER		DESCRIPTION			ITEM	
MATERIALS LIST							
UNLESS OTHERWISE SPECIFIED 1) All dimensions are in metric(mm). 2) Tolerances are as follows: 1 PL DEC ±0.30 2 PL DEC ±0.15 3 PL DEC ±0.08 3) Note reference = X		SIGNATURES DRAWN: RONALD CHECKED: JOE ENGINEER: APPROVAL: TOMMY CUSTOMER:		DATE 26/Jul/23 27/Jul/23 28/Jul/23		Amphenol Sine Systems - www.amphenol-sine.com 44724 Morley Drive Clinton Township, MI 48036	
MATERIAL SPECIFICATIONS:				EcoMate RM,PIN CONTACT, Ø3.6mm, CRIMP 8 AWG			
PROCESS SPECIFICATIONS:		THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.		SIZE B TYPE C- DWG NO: MP10A25x-8A		REVISION A1	
NEXT ASSY:				SCALE: NONE		SHEET 1 OF 1	

TITLE: EcoMate RM,PIN CONTACT,Ø3.6mm, CRIMP 8 AWG DWG NO: MP10A25x-8A REV: A1 SH: 1 OF: 1