

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A I	REVISED FOR ET00-0081-01	07MAR01	H. Y.	C. T.
	B I	3.8+/-0.1 CHANGED TO 3.75+/-0.19	06AUG2021	MB	TD

R1.8
REF.SPESSORE BANDELLA
(MAT. THK.)
.040±0.025DIM. MASSIMA
DI TAGLIO
(MAX. DUE TO
APPLICATION CUT-OFF)


0.3

1.8
REF.SENSO DI USCITA DEL CONTATTO
DALLA BOBINA
(DIRECTION OFF
TOP OF REEL)


SECTION E-E




SECTION A-A



SECTION B-B



SECTION C-C



NOTES:

1 TRADE MARK LOCATED AS SHOWN.

2) SUPPLIED IN STRIP ON REEL
FORNITO IN STRIP SU BOBINA3) CONTACT AS SHOWN IS SUITABLE FOR HSG. TE AMP P/N 284406-1
IL CONTATTO IN OGGETTO E' UTILIZZABILE
CON IL CONNETTORE TE AMP P/N 284406-14 LA SEZIONE E LE RELATIVE DIMENSIONI SONO VALIDE PER UNA LUNGHEZZA
DI 1.8mm A PARTIRE DAL FRONTE DEL CONTATTO
THIS SECTION AND RELEVANT DIM. ARE APPLICABLE FROM THE FRONT
OF THE CONTACT FOR 1.8mm LENGTH

18-16

1.50-2.62

COPPER ALLOY

284633-1

WIRE RANGE (AWG)

INSULATION DIA. RANGE

MATERIAL


PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN C.CORDOLA 27LUG2000

CHK G.TURCO 27LUG2000

APVD G.TURCO 27LUG2000

DIMENSIONS:
mmTOLERANCES UNLESS
OTHERWISE SPECIFIED:0 PLC ± .5
1 PLC ± .3
2 PLC ± .3
3 PLC ±
4 PLC ±
ANGLES ± 2°

MATERIAL

SEE TABLE

FINISH

STAGNATO
TIN PLATED

PRODUCT SPEC

108-20033

APPLICATION SPEC

114-20107

WEIGHT

CUSTOMER DRAWING

NAME

SPECIAL REC. CONTACT CLUSTER
FOR PIN 2.29 dia .090 DIA

SIZE

CAGE CODE

DRAWING NO

A3

C-

284633

RESTRICTED TO

SCALE 8:1

SHEET 1

OF 1

REV B1