



Part Number : [190270034](#)
Product Description : ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press
Series Number : 207126
Status : Active
Product Category : Applicators and Crimp Modules
Engineering Number : ATP-AA-110



Documents & Resources

Tooling Specifications

- [ATS-190270034-001.pdf](#)
- [ATS-TOOLING-ID-ATP-001.pdf](#)
- [TM-640160065-001.pdf](#)
- [TM-640160065CN-001.pdf](#)
- [TM-640160065DE-001.pdf](#)
- [TM-640160065SP-001.pdf](#)
- [TM-640160065FR-001.pdf](#)
- [TM-640160065IT-001.pdf](#)
- [TM-640160065JP-001.pdf](#)
- [TM-640160065KR-001.pdf](#)
- [TM-640160065MY-001.pdf](#)
- [TM-640160065PL-001.pdf](#)
- [TM-640160065RU-001.pdf](#)
- [TM-640160065SK-001.pdf](#)
- [TM-640160065TH-001.pdf](#)
- [TM-640160065VN-001.pdf](#)
- [TM-640160065TW-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	

	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Applicators and Crimp Modules
Series	207126
Description	ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press
Comments	The Crimp Tape Module 640162000 is a base unit that will work like an applicator in a Molex TM-3000 638017200, 638017300 industry standard crimp press or the Molex TM-4000 638017600 industry standard crimp press. The Crimp Tape Module will accept all ATP-301 and ATP-201 style crimp dies. This Crimp Tape Module will allow

	customers to process most of Molex's Mylar Tape product from 2 AWG uninsulated and 4 AWG insulated products and up. The Crimp Tape Module will NOT work in any other industry standard crimp press or wire process machine. These ATP-301 style die sets can be used in the older style suitcase presses.
Function	Crimp
Geographic Area	Global
Level of Automation	Semi-Automatic
More Detailed Tech Information	toolingsupport@molex.com
Product Name	N/A
Tool Type	Crimp Module
UPC	800753040953
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical

Net Weight	1.000/g
------------	---------

Mates With / Use With

Use with Part(s)

Description	Part Number
Taped Terminal Crimp Module used with TM-3000 and TM-4000 presses with ATP-201 and ATP-301 die sets.	<u>640162000</u>
Use With	Molex ATP-101 style presses

Applicable Parts

Description	Part Number
Krimptite Ring Tongue Terminal for 22-18 AWG Wire	<u>190690028</u>
Krimptite Ring Tongue Terminal for 22-18 AWG Wire	<u>190690030</u>
Krimptite Ring Tongue Terminal for 22-18 AWG Wire	<u>190690032</u>
Krimptite Ring Tongue Terminal for 22-18 AWG Wire	<u>190690034</u>
Krimptite Ring Tongue Terminal for 22-18 AWG Wire	<u>190690036</u>
Krimptite Ring Tongue Terminal for 22-18 AWG Wire	<u>190690038</u>
Krimptite Ring Tongue Terminal for 22-18 AWG Wire	<u>190690044</u>
Krimptite Ring Tongue Terminal for 22-18 AWG Wire	<u>190690046</u>
Krimptite Ring Tongue Terminal for 22-18 AWG Wire	<u>190690050</u>
Krimptite Ring Tongue Terminal for 22-18 AWG Wire	<u>190690055</u>
Krimptite Ring Tongue Terminal for 22-18 AWG Wire	<u>190690057</u>
Krimptite Ring Tongue Terminal for 22-18 AWG Wire	<u>190690062</u>
Krimptite Snap Spade Tap for 22-18 AWG Wire, Stud Size 5-6 (M3-3.5), Mylar Tape Carrier	<u>190980019</u>
Krimptite Snap Spade Tap for 22-18	<u>190980080</u>

AWG Wire, Stud Size 8 (M4), Mylar Tape Carrier	
Krimptite Snap Spade Tap for 22-18 AWG Wire, Stud Size 10 (M5), Mylar Tape Carrier	<u>190980081</u>
Krimptite Flanged Spade Tongue Terminal for 22-18 AWG Wire, Stud Size 6 (M3.5), Length 14.12mm, Mylar Tape Carrier	<u>191180022</u>
Krimptite Flanged Spade Tongue Terminal for 22-18 AWG Wire, Stud Size 8 (M4), Mylar Tape Carrier	<u>191180024</u>
Krimptite Spade Tongue Terminal for 22-18 AWG Wire, Stud Size 6 (M3.5), Mylar Tape Carrier	<u>191410021</u>
Krimptite Spade Tongue Terminal for 22-18 AWG Wire, Stud Size 8 (M4), Mylar Tape Carrier	<u>191410023</u>
Krimptite Spade Tongue Terminal for 22-18 AWG Wire, Stud Size 10 (M5), Mylar Tape Carrier	<u>191410025</u>
VersaKrimp Spade Tongue Terminal for 22-18 AWG Wire, Tape and Reel	<u>191470007</u>
VersaKrimp Ring Tongue Terminal for 22-18 AWG Wire, Closed-Brazed Barrel, Stud Size 3-4 (M2.6), Mylar Tape Carrier	<u>191930008</u>
VersaKrimp Ring Tongue Terminal for 22-18 AWG Wire, Closed-Brazed Barrel, Stud Size 5-6 (M3-3.5), Mylar Tape Carrier	<u>191930011</u>
VersaKrimp Ring Tongue Terminal for 22-18 AWG Wire, Closed-Brazed Barrel, Stud Size 5-6 (M3-3.5), Mylar Tape Carrier	<u>191930013</u>
VersaKrimp Ring Tongue Terminal for 22-18 AWG Wire, Closed-Brazed Barrel, Stud Size 8 (M4), Mylar Tape Carrier	<u>191930015</u>
VersaKrimp Ring Tongue Terminal for 22-18 AWG Wire, Closed-Brazed	<u>191930017</u>

Barrel, Stud Size 10 (M5), Mylar Tape Carrier	
VersaKrimp Ring Tongue Terminal for 22-18 AWG Wire, Closed-Brazed Barrel, Stud Size 1/4" (M6), Mylar Tape Carrier	<u>191930022</u>
VersaKrimp Ring Tongue Terminal for 22-18 AWG Wire, Closed-Brazed Barrel, Stud Size 5/16" (M8), Mylar Tape Carrier	<u>191930024</u>
VersaKrimp Ring Tongue Terminal for 22-18 AWG Wire, Closed-Brazed Barrel, Stud Size 5-6 (M3-3.5), Mylar Tape Carrier	<u>191930035</u>
VersaKrimp Ring Tongue Terminal for 22-18 AWG Wire, Closed-Brazed Barrel, Stud Size 8 (M4), Mylar Tape Carrier	<u>191930037</u>
VersaKrimp Ring Tongue Terminal for 22-18 AWG Wire, Closed-Brazed Barrel, Stud Size 10 (M5), Mylar Tape Carrier	<u>191930042</u>
Krimptite Wire Pin Terminal for 22-18 AWG Wire, Mylar Tape Carrier	<u>192110004</u>
VersaKrimp Metric Ring Terminal for M2.5 Stud Size (#4), Un-insulated, Adhesive Tape on Reel	<u>193230207</u>
VersaKrimp Metric Ring Terminal for M3 Stud Size (#5), Un-insulated, Adhesive Tape on Reel	<u>193230208</u>
VersaKrimp Metric Ring Terminal for M3-3.5 Stud Size (#5-#6), Un-insulated, Adhesive Tape on Reel	<u>193230209</u>
VersaKrimp Metric Ring Terminal for M4 Stud Size (#8), Un-insulated, Adhesive Tape on Reel	<u>193230210</u>
VersaKrimp Metric Ring Terminal for M5 Stud Size (#10), Un-insulated, Adhesive Tape on Reel	<u>193230211</u>