


CGHV40320D

320 W, 4.0 GHz, GaN HEMT Die

Description

Wolfspeed's CGHV40320D is a gallium nitride (GaN) High Electron Mobility Transistor (HEMT). GaN has superior properties compared to silicon or gallium arsenide, including higher breakdown voltage, higher saturated electron drift velocity, and higher thermal conductivity. GaN HEMTs offer greater power density and wider bandwidths compared to Si and GaAs transistors.



Features

- 19 dB Typical Small Signal Gain at 4 GHz
- 65% Typical Power Added Efficiency
- 320 W Typical P_{SAT}
- 50 V Operation
- High Breakdown Voltage
- Up to 4 GHz Operation

Applications

- Broadband amplifiers
- Tactical communications
- Satellite communications
- Industrial, Scientific, and Medical amplifiers
- Class A, AB, Linear amplifiers suitable for OFDM, W-CDMA, EDGE, CDMA waveforms

Packaging Information



- Bare die are shipped in Gel-Pak® containers
- Non-adhesive tacky membrane immobilizes die during shipment

 Large Signal Models Available for ADS and MWO





Absolute Maximum Ratings (not simultaneous)

Parameter	Symbol	Rating	Units	Conditions
Drain-Source Voltage	V_{DS}	150	V_{DC}	25°C
Gate-to-Source Voltage	V_{GS}	-10, +2		
Storage Temperature	T_{STG}	-65, +150	°C	
Operating Junction Temperature	T_J	225		
Maximum Drain Current ¹	I_{DMAX}	12	A	25°C
Maximum Forward Gate Current	I_{GMAX}	41.8	mA	
Thermal Resistance, Junction to Case (packaged) ²	$R_{\theta JC}$	0.44	°C/W	85°C, 167.2 W Dissipation
Thermal Resistance, Junction to Case (die only)		0.35		
Mounting Temperature	T_s	320	°C	30 seconds

Notes:

¹ Current limit for long term, reliable operation

² Eutectic die attach using 80/20 AuSn mounted to a 10 mil thick Cu15Mo85 carrier

Electrical Characteristics (Frequency = 4 GHz unless otherwise stated; $T_c = 25^\circ\text{C}$)

Characteristics	Symbol	Min.	Typ.	Max.	Units	Conditions
DC Characteristics						
Gate Pinch-Off Voltage	V_P	-3.8	-3.0	-2.3	V	$V_{DS} = 10\text{ V}$, $I_D = 41.8\text{ mA}$
Drain Current ¹	I_{DSS}	33	41.8	—	A	$V_{DS} = 6\text{ V}$, $V_{GS} = 2.0\text{ V}$
Drain-Source Breakdown Voltage	V_{BR}	125	—	—	V	$V_{GS} = -8\text{ V}$, $I_D = 41.8\text{ mA}$
On Resistance	R_{ON}	—	0.07	—	Ω	$V_{DS} = 0.1\text{ V}$
Gate Forward Voltage	V_{G-ON}	—	1.9	—	V	$I_{GS} = 41.8\text{ mA}$
RF Characteristics						
Small Signal Gain	G_{SS}	—	19	—	dB	$V_{DD} = 50\text{ V}$, $I_{DQ} = 500\text{ mA}$
Saturated Power Output ¹	P_{SAT}	—	320	—	W	
Drain Efficiency ²	η	—	65	—	%	$V_{DD} = 50\text{ V}$, $I_{DQ} = 500\text{ mA}$, $P_{SAT} = 320\text{ W}$
Intermodulation Distortion	IM3	—	-30	—	dBc	$V_{DD} = 50\text{ V}$, $I_{DQ} = 500\text{ mA}$, $P_{OUT} = 320\text{ W PEP}$
Output Mismatch Stress	VSWR	—	—	10 : 1	Ψ	No damage at all phase angles, $V_{DD} = 50\text{ V}$, $I_{DQ} = 500\text{ mA}$, $P_{OUT} = 320\text{ W Pulse}$
Dynamic Characteristics						
Input Capacitance	C_{GS}	—	55.6	—	pF	$V_{DS} = 50\text{ V}$, $V_{GS} = -8\text{ V}$, $f = 1\text{ MHz}$
Output Capacitance	C_{DS}	—	11.56	—		
Feedback Capacitance	C_{GD}	—	1.23	—		

Notes:


¹ Scaled from PCM data

² P_{SAT} is defined as $I_G = 4.0\text{ mA}$

³ Drain Efficiency = P_{OUT} / P_{DC}



DIE Dimensions (units in microns)



Overall die size 6100 x 1110 (+0/-50) microns, die thickness 100 microns.
All Gate and Drain pads must be wire bonded for electrical connection.

Assembly Notes:

- Recommended solder is AuSn (80/20) solder. Refer to Wolfspeed’s website for the Eutectic Die Bond Procedure application note at <https://www.wolfspeed.com/rf/document-library>
- Vacuum collet is the preferred method of pick-up.
- The backside of the die is the Source (ground) contact.
- Die back side gold plating is 5 microns thick minimum.
- Thermosonic ball or wedge bonding are the preferred connection methods.
- Gold wire must be used for connections.
- Use the die label (XX-YY) for correct orientation.

Electrostatic Discharge (ESD) Classifications

Parameter	Symbol	Class	Classification Level	Test Methodology
Human Body Model	HBM	TBD	ANSI/ESDA/JEDEC JS-001 Table 3	JEDEC JESD22 A114-D

Typical Performance




Figure 1. CGHV40320D Output Power, Gain and Efficiency vs. Input Power at $T_{CASE} = 25^{\circ}\text{C}$
 $V_{DD} = 50\text{V}$, $I_{DQ} = 500\text{ mA}$, Frequency = 2.7 GHz




Figure 2. CGHV40320D G_{MAX} and K Factor vs. Frequency at $T_{CASE} = 25^{\circ}\text{C}$
 $V_{DD} = 50\text{ V}$, $I_{DQ} = 500\text{ mA}$



Typical Die S-Parameters
(Small Signal, $V_{DS} = 50\text{ V}$, $I_{DQ} = 500\text{ mA}$, magnitude/angle)

Frequency	Mag S11	Ang S11	Mag S21	Ang S21	Mag S12	Ang S12	Mag S22	Ang S22
0.5	0.964	-175.19	5.49	73.16	0.005	-15.49	0.719	-171.16
0.6	0.966	-175.83	4.48	69.32	0.005	-19.04	0.732	-170.45
0.7	0.967	-176.28	3.75	65.72	0.005	-22.35	0.746	-169.86
0.8	0.969	-176.62	3.20	62.34	0.005	-25.45	0.761	-169.41
0.9	0.970	-176.88	2.77	59.16	0.005	-28.35	0.776	-169.08
1	0.972	-177.10	2.42	56.17	0.005	-31.06	0.790	-168.88
1.1	0.973	-177.28	2.14	53.35	0.005	-33.59	0.804	-168.78
1.2	0.974	-177.44	1.90	50.70	0.004	-35.96	0.817	-168.76
1.3	0.976	-177.59	1.70	48.21	0.004	-38.16	0.829	-168.81
1.4	0.977	-177.71	1.53	45.87	0.004	-40.22	0.841	-168.91
1.5	0.978	-177.83	1.38	43.66	0.004	-42.13	0.852	-169.06
1.6	0.979	-177.95	1.25	41.59	0.004	-43.91	0.862	-169.24
1.7	0.980	-178.05	1.14	39.65	0.004	-45.56	0.871	-169.44
1.8	0.981	-178.15	1.04	37.81	0.004	-47.11	0.879	-169.66
1.9	0.982	-178.24	0.96	36.08	0.003	-48.54	0.887	-169.89
2	0.983	-178.33	0.88	34.45	0.003	-49.88	0.895	-170.12
2.1	0.984	-178.42	0.81	32.90	0.003	-51.12	0.901	-170.36
2.2	0.985	-178.50	0.75	31.44	0.003	-52.28	0.907	-170.61
2.3	0.985	-178.58	0.70	30.06	0.003	-53.36	0.913	-170.85
2.4	0.986	-178.65	0.65	28.75	0.003	-54.37	0.918	-171.08
2.5	0.987	-178.73	0.61	27.50	0.003	-55.30	0.923	-171.32
2.6	0.987	-178.80	0.57	26.32	0.003	-56.17	0.927	-171.55
2.7	0.988	-178.86	0.53	25.19	0.003	-56.99	0.931	-171.77
2.8	0.988	-178.93	0.50	24.11	0.002	-57.74	0.935	-171.99
2.9	0.989	-178.99	0.47	23.08	0.002	-58.45	0.938	-172.20
3	0.989	-179.05	0.44	22.10	0.002	-59.10	0.942	-172.41
3.2	0.990	-179.17	0.39	20.26	0.002	-60.28	0.947	-172.80
3.4	0.990	-179.28	0.35	18.56	0.002	-61.29	0.952	-173.17
3.6	0.991	-179.39	0.32	16.99	0.002	-62.15	0.957	-173.52
3.8	0.991	-179.49	0.29	15.54	0.002	-62.87	0.960	-173.84
4	0.992	-179.58	0.26	14.18	0.002	-63.47	0.964	-174.15
4.2	0.992	-179.68	0.24	12.90	0.002	-63.94	0.967	-174.43
4.4	0.992	-179.76	0.22	11.71	0.001	-64.30	0.969	-174.70
4.6	0.993	-179.85	0.20	10.58	0.001	-64.55	0.971	-174.96
4.8	0.993	-179.93	0.19	9.51	0.001	-64.68	0.973	-175.20
5	0.993	179.99	0.17	8.50	0.001	-64.70	0.975	-175.42
5.2	0.993	179.92	0.16	7.54	0.001	-64.59	0.977	-175.64
5.4	0.993	179.84	0.15	6.62	0.001	-64.35	0.978	-175.84
5.6	0.994	179.77	0.14	5.75	0.001	-63.96	0.980	-176.03
5.8	0.994	179.70	0.13	4.91	0.001	-63.41	0.981	-176.22
6	0.994	179.63	0.12	4.10	0.001	-62.68	0.982	-176.39

To download the s-parameters in s2p format, go to the [CGHV40320D](#) Product page and click on the documentation tab.



Part Number System

CGHV40320D




Table 1.

Parameter	Value	Units
Upper Frequency ¹	4.0	GHz
Power Output	320	W
Package	Bare Die	—

Note:
¹ Alpha characters used in frequency code indicate a value greater than 9.9 GHz. See Table 2 for value.

Table 2.

Character Code	Code Value
A	0
B	1
C	2
D	3
E	4
F	5
G	6
H	7
J	8
K	9
Examples:	1A = 10.0 GHz 2H = 27.0 GHz



Product Ordering Information

Order Number	Description	Unit of Measure	Image
CGHV40320D	GaN HEMT Bare Die	Each	

**For more information, please contact:**

4600 Silicon Drive
Durham, NC 27703 USA
Tel: +1.919.313.5300
www.wolfsspeed.com/RF

Sales Contact
RFSales@wolfsspeed.com

RF Product Marketing Contact
RFMarketing@wolfsspeed.com

Notes & Disclaimer

Specifications are subject to change without notice. “Typical” parameters are the average values expected by Wolfsspeed in large quantities and are provided for information purposes only. Wolfsspeed products are not warranted or authorized for use as critical components in medical, life-saving, or life-sustaining applications, or other applications where a failure would reasonably be expected to cause severe personal injury or death. No responsibility is assumed by Wolfsspeed for any infringement of patents or other rights of third parties which may result from use of the information contained herein. No license is granted by implication or otherwise under any patent or patent rights of Wolfsspeed.

© 2014-2022 Wolfsspeed, Inc. All rights reserved. Wolfsspeed® and the Wolfstreak logo are registered trademarks and the Wolfsspeed logo is a trademark of Wolfsspeed, Inc.
PATENT: <https://www.wolfsspeed.com/legal/patents>

The information in this document is subject to change without notice.