

Part Number : [1205030010](#)

Product Description : Micro-Change (M12) Field Attachable Connector, 5 Poles, L-Coded, Angled, Male, Unshielded, Screw Termination, Cable Diameter 8.00-13.00mm

Series Number : 120503

Status : Active

Product Category : Circular Industrial Connectors

Engineering Part Number : LAP5007-44




Documents and Resources

Drawings

[1205030010_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	120503
Description	Micro-Change (M12) Field Attachable Connector, 5 Poles, L-Coded, Angled, Male, Unshielded, Screw Termination, Cable Diameter 8.00-13.00mm
Approvals	UKCA, CE certified
IP Rating	IP67
Product Name	Micro-Change (M12)
Type	Field Attachable Connector
UPC	193264730193

Electrical

Current - Maximum per Contact	12.0A, 16.0A
Voltage - Maximum	63V

Physical

Cable Diameter	8.00-13.00mm (.315-.512")
Coupling Type	External Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male
Keyway	L-Coded
Material - Connector Body	Polyamide
Material - Contact	Brass
Material - Coupling Nut	Aluminum Die-Cast

Material - Plating Mating	Gold
Orientation	Angled
Poles	5
Temperature Range - Operating	-40° to +85°C
Wire Size (AWG)	14, 16

This document was generated on Jun 07, 2026