



Part Number : [39000048](#)
Product Description : Mini-Fit Male Crimp Terminal, Tin (Sn) over Plated Brass Contact, 22-28 AWG, Reel
Series Number : 5558
Status : Active
Product Category : Crimp Terminals
Engineering Number : 5558T2
Packaging Alternative : [0039000049](#) (Bag)



Documents & Resources

Drawings

[Drawing 039000048_sd.pdf](#)
[Packaging Design Drawing 55580001-PK-000.pdf](#)

Specifications


[Application Specification 55560001-AS-000.pdf](#)
[Product Specification 55560002-PS-CH-000.pdf](#)
[Product Specification 55560002-PS-ES-000.pdf](#)
[Product Specification 55560002-PS-SK-000.pdf](#)
[Product Specification 55560008-TS-000.pdf](#)
[Product Specification PS-5556-001-001.pdf](#)
[Product Specification PS-5556-002-001.pdf](#)
[Test Summary 55560000-TS-000.pdf](#)
[Test Summary 55560010-TS-000.pdf](#)
[Test Summary TS-5556-002-001.pdf](#)

Tooling Specifications

[Crimp Specification CS-5556X2_5558X2-031.pdf](#)
[Crimp Specification CS-5556X2_5558X2-032.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21

REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Crimp Terminals
Series	5558
Description	Mini-Fit Male Crimp Terminal, Tin (Sn) over Plated Brass Contact, 22-28 AWG, Reel
Application	Power, Wire-to-Wire
Product Family	Mini-Fit Family Power Connectors
Product Name	Mini-Fit
UPC	800753584617

Electrical

Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

Physical

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin

Material - Plating Termination	Tin
Net Weight	0.164/g
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.889µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	0.90-1.80mm
Wire Size (AWG)	22, 24, 26, 28
Wire Size mm ²	N/A

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

Use with Part(s)

Description	Part Number
Mini-Fit Jr. Plug Housings	<u>5559</u>
Mini-Fit BMI Dual Row Plug Housings	<u>42475</u>
Mini-Fit Jr. Dual Row Plug Housings	<u>46993</u>

Application Tooling

Global

Description	Part Number
Extraction Tool for Mini-Fit Jr. Terminals	<u>0011030044</u>
PremiumGrade Hand Crimp Tool for Mini-Fit Jr. Male and Female Terminals, 22-28 AWG	<u>0638191000</u>
FineAdjust Applicator for Insulation Diameter 1.30-1.50mm, 22-28 AWG Wire	<u>0639002700</u>
FineAdjust Applicator for Insulation OD 1.10-1.30mm - 22-28 AWG	<u>0639020200</u>
FineAdjust Applicator for Insulation OD 0.95-1.08mm - 22-28 AWG	<u>0639023800</u>
T2 Terminator for Insulation OD 1.30-1.50mm, 22-28 AWG	<u>0639102700</u>

T2 Terminator for insulation OD 1.10-1.30mm - 22-28 AWG	<u>0639120200</u>
T2 Terminator for Insulation Diameter 0.95-1.08mm, 22-28 AWG	<u>0639123800</u>

Application Tooling

Japan

Description	Part Number
S-1 Applicator for Mini-Fit Plug and Receptacle Terminals, 22-28 AWG	<u>0570223720</u>
Hand Extraction Tool	<u>0570316000</u>

This document was generated on Feb 26, 2024