



Part Number : [2121320003](#)

Product Description : 1.00mm Pitch Pico-EZmate Plus Receptacle Housing, Single Row, 3 Circuits, Black

Series Number : 212132

Status : Active

Product Category : Connector Housings



Documents and Resources

Drawings

[2121320003_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[2121320003.dxf](#)

Specifications


[2121329200-SPK-200.pdf](#)

[2121320000-PS-000.pdf](#)

[2121321000-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

[Compliance Statements](#)

- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	212132
Description	1.00mm Pitch Pico-EZmate Plus Receptacle Housing, Single Row, 3 Circuits, Black
Application	Signal, Wire-to-Board
Keyword	Pico-EZmate 1.0
Product Name	Pico-EZmate Plus
UPC	193264124633

Agency

UL	E29179
----	--------

Physical

Circuits (maximum)	3
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Resin	Polyamide (PA)

Net Weight	9.500/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.00mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
Pico-EZmate Plus Single Row Surface Mount Headers	<u>212134</u>

This document was generated on Apr 29, 2026