

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY

FED. MFR. CODE 91929

SWITCH - BASIC

CATALOG LISTING
BZ-2RW80288-A2

APS1528

X115400-BZ

BZ-2RW80288-A2

PAGE 1 OF 1

M

DRAWING
NUMBER

C

ISSUE

REPLACES

ECO-0005270

RELEASE NO.

29 AUG 05

RJ

CHECK

JUL 04

AK

CHECK


05/05/04

AK

CHECK

05/05/04

DVM



NOTE
△ - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000 ± .002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS		ELECTRICAL DATA		SCALE FULL
OPERATING FORCE -----	3 OZ MAX	CONTACT ARRANGEMENT		DO NOT SCALE PRINT
RELEASE FORCE -----	1/4 OZ MIN	S P D T		
DIFFERENTIAL TRAVEL -----	.001 - .020	15A-125, 250 OR 480 VAC, 2A-600 VAC -L74- 1/8HP-125 VAC; 1/4HP-250 VAC 1/2A-125 VDC; 1/4A-250 VDC		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES
OVERTRAVEL -----	.100 MIN			TOLERANCES ARE:
		-L288-	CE EN05	ONE PLACE (.0) ±.030
		-L306-	EC	TWO PLACE (.00) ±.015
		-L315-	SP	THREE PLACE (.000) ±.005
			16A 250V ~ T85 5E4	ANGLES ±
				WEIGHT .073 LB

FORMTEK

FO-50378