








used for: D-SUB COMBINATION

P.C.B. HOLE DRILLINGS



METAL BRACKET

PRESS FOR FIXING ON PCB



NOTES:

1. METAL SHELLS: STEEL; min. 320µin TIN
2. INSULATORS: PBT GF UL 94 V-0, GREEN
3. HIGH POWER CONTACTS 30A: COPPER ALLOY
4. PLATING: min. 30µin HARD GOLD OVER min. 50µin NICKEL
5. METAL BRACKET: STEEL; min. 320µin TIN over 80µin NICKEL
6. THREADED INSERT: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
7. PCB-SNAP: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
PCB-HOLE: 3.1±0.1; PCB THICKNESS 1.6mm
8. MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
9. CONNECTOR IS PART MARKED: 3005W5PXX57N40X CONEC ABC

Directive 2002/95 EC
„RoHS“
Compliant

APPROVAL # FREIGABE # DEBLOCAGE # AUTOR/ZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTOR/ZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name

tolerance		
2002	date	name
drawn	05.06.	Parei
appd.	05.06.	Schrader
norm		
d-old		

scale:	2:1 (5:1)	
material:	SEE NOTES	
title:		
D-SUB COMBINATION MALE 90°		
5W5P		
with threaded insert, metal bracket and clip		
dwg no:	AutoCAD 2000	DIN-A
13K1A585		3
part no: 3005W5PXX57N40X		sh: 1/1