SIEMENS

Data sheet 3SK1111-1AB30



SIRIUS safety relay Basic unit Standard series Relay enabling circuits 3 NO contacts plus Relay signaling circuit 1 NC contact Us = 24 V AC/DC screw terminal

product brand name	SIRIUS
product category	Safety relays
product designation	safety relays
design of the product	Relay enabling circuits
product type designation	3SK1
product line	Standard basic unit
Product Function	
product function parameterizable	sensor floating / sensor non-floating, monitored start-up / automatic start
product function	
● automatic start	Yes
● light barrier monitoring	Yes
● protective door monitoring	Yes
● magnetically operated switch monitoring NC-NO	No
● magnetically operated switch monitoring NC-NC	Yes
● laser scanner monitoring	Yes
● light array monitoring	Yes
● EMERGENCY OFF function	Yes
● monitored start-up	Yes
● pressure-sensitive mat monitoring	No
product feature cross-circuit-proof	Yes
suitability for interaction press control	No
suitability for operation device connector 3ZY12	No
suitability for use	
● monitoring of floating sensors	Yes
● monitoring of non-floating sensors	Yes
● position switch monitoring	Yes
● EMERGENCY-OFF circuit monitoring	Yes
● opto-electronic protection device monitoring	Yes
● magnetically operated switch monitoring	Yes
● safety-related circuits	Yes
General technical data	
certificate of suitability UL approval	Yes
product feature protective coating on printed-circuit board	No
power loss [W] maximum	2 W
insulation voltage rated value	300 V
degree of pollution	3
overvoltage category	3
surge voltage resistance rated value	4 000 V
protection class IP of the enclosure	IP20

Subject to change without notice
© Copyright Siemens
Downloaded from Arrow.com.

shock resistance	10 g / 11 ms
vibration resistance according to IEC 60068-2-6	5 ... 500 Hz: 0.75 mm
operating frequency maximum	360 1/h
reference code according to IEC 81346-2	F
Substance Prohibitance (day/month/year)	11/05/2012
SVHC substance name	Lead CAS-No. 7439-92-1 Lead monoxide (lead oxide) CAS-No. 1317-36-8 2-methyl-1-(4-methylthiophenyl)-2-morpholinopropan-1-one CAS-No. 71868-10-5 Melamine CAS-No. 108-78-1 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol CAS-No. 119-47-1 4,4'-isopropylidenediphenol (Bisphenol A, BPA) CAS-No. 80-05-7
Net Weight	0.226 kg
Ambient conditions	
installation altitude at height above sea level maximum	4 000 m
● note	Derating, see Product Notification 109792701
ambient temperature	
● during operation	-25 ... +60 °C
● during storage	-40 ... +80 °C
relative humidity during operation	10 ... 95 %
air pressure according to SN 31205	900 ... 1 060 hPa
Electromagnetic compatibility	
installation environment regarding EMC	This product is suitable for Class B environments and can also be used in domestic environments.
EMC emitted interference	IEC 60947-5-1, Class B
Safety related data	
product function suitable for safety function	Yes
safe state	Safety outputs switched off
test wear-related service life necessary	Yes
function test interval maximum	1 a
stop category according to IEC 60204-1	0
IEC 62061	
SIL Claim Limit (subsystem) according to EN 62061	3
Safety Integrity Level (SIL)	
● **according to IEC 62061**	SIL 3
● at single-channel evaluation according to IEC 62061	1
● at 2-channel evaluation according to IEC 62061	3
PFHD with high demand rate according to IEC 62061	0.0000000017
ISO 13849	
category according to EN ISO 13849-1	4
performance level (PL)	
● **according to ISO 13849-1**	PL e
● at single-channel evaluation according to ISO 13849-1	c
● at 2-channel evaluation according to ISO 13849-1	e
category	
● **according to ISO 13849-1**	4
● at 2-channel evaluation according to ISO 13849-1	4
overdimensioning according to ISO 13849-2 necessary	No
IEC 61508	
Safety Integrity Level (SIL)	
● according to IEC 61508	3
● at single-channel evaluation according to IEC 61508	1
● at 2-channel evaluation according to IEC 61508	3
safety device type according to IEC 61508-2	Type A
PFHD with high demand rate according to IEC 61508	0.0000000017
PFDavg with low demand rate according to IEC 61508	0.000001
Safe failure fraction (SFF)	99 %
hardware fault tolerance	
● according to IEC 61508	1
● at single-channel evaluation according to IEC 61508	0
● at 2-channel evaluation according to IEC 61508	1

© Copyright Siemens
Downloaded from Arrow.com.

T1 value	
● of service life according to IEC 61508	20 a
● for proof test interval or service life according to IEC 61508	20 a
Electrical Safety	
touch protection against electrical shock	finger-safe
Short-circuit protection	
design of the fuse link	
● for short-circuit protection of the NO contacts of the relay outputs required	gL/gG: 6A or circuit breaker type A: 3A or circuit breaker type B: 2A or circuit breaker type C: 1A
● for short circuit protection of the NC contacts of the relay outputs required	Diazed or Neozed fuses, operating class gL/gG: 6 A or MCB type A: 2 A or MCB type B: 2 A or MCB type C: 1 A
Inputs	
design of input	
● cascading input/functional switching	No
● feedback input	Yes
● start input	Yes
pulse duration of the sensor input minimum	150 ms
number of sensor inputs 1-channel or 2-channel	1
Outputs	
number of outputs as contact-affected switching element	
● as NC contact	
— for signaling function instantaneous contact	1
● as NO contact	
— safety-related instantaneous contact	3
— safety-related delayed switching	0
mechanical service life (operating cycles) typical	10 000 000
thermal current of the switching element with contacts maximum	5 A
switching capacity current of the NO contacts of the relay outputs at DC-13	
● at 24 V	5 A
● at 115 V	0.2 A
● at 230 V	0.1 A
switching capacity current of the NO contacts of the relay outputs at AC-15	
● at 115 V	5 A
● at 230 V	5 A
switching capacity current of the NC contacts of the relay outputs at DC-13	
● at 24 V	1 A
● at 115 V	0.2 A
● at 230 V	0.1 A
switching capacity current of the NC contacts of the relay outputs at AC-15	
● at 24 V	2 A
● at 115 V	1.5 A
● at 230 V	1.5 A
total current maximum	12 A
operational current at 17 V minimum	5 mA
Times	
make time with automatic start	
● typical	200 ms
● at DC maximum	320 ms
● at AC maximum	320 ms
make time with automatic start after power failure	
● typical	200 ms
● maximum	320 ms
make time with monitored start	
● typical	15 ms
● maximum	20 ms

© Copyright Siemens
Downloaded from Arrow.com.

backslide delay time after opening of the safety circuits typical	10 ms
backslide delay time in the event of power failure	
● typical	65 ms
● maximum	75 ms
recovery time after opening of the safety circuits typical	10 ms
recovery time after power failure typical	0.09 s
pulse duration	
● of the ON pushbutton input minimum	0.015 s
Control circuit/ Control	
type of voltage of the control supply voltage	AC/DC
control supply voltage at AC	
● at 50 Hz rated value	24 V
● at 60 Hz rated value	24 V
control supply voltage frequency	
● 1 rated value	50 Hz
● 2 rated value	60 Hz
control supply voltage at DC rated value	24 V
operating range factor control supply voltage rated value of magnet coil at DC	
● initial value	0.85
● full-scale value	1.2
operating range factor control supply voltage rated value of magnet coil at AC	
● at 50 Hz	0.85 ... 1.1
● at 60 Hz	0.85 ... 1.1
Installation/ mounting/ dimensions	
mounting position	any
fastening method	screw and snap-on mounting
height	100 mm
width	22.5 mm
depth	121.6 mm
required spacing	
● for grounded parts at the side	5 mm
Connections/ Terminals	
type of electrical connection	screw terminal
wire length	
● for total of all sensor circuits with Cu 1.5 mm² and 150 nF/km maximum	2 000 m
type of connectable conductor cross-sections	
● solid	1x (0.5 ... 2.5 mm²), 2x (1.0 ... 1.5 mm²)
● finely stranded with core end processing	1x (0.5 ... 2.5 mm²), 2x (0.5 ... 1.0 mm²)
● for AWG cables solid	1x (20 ... 14), 2x (18 ... 16)
● for AWG cables stranded	1x (20 ... 16), 2x (20 ... 16)
type of electrical connection plug-in socket	No

Approvals Certificates

Environment	General Product Approval				
Environmental Confirmations	EPD	CCC	cULus	EAC	CE EG-Konf.


General Product Approval	EMV		Functional Saftey	Test Certificates	Maritime application
UKCA	KC	RCM	Type Examination Certificate	Type Test Certificates/Test Report	DNV

© Copyright Siemens
Downloaded from Arrow.com.


Maritime application	other	Railway
LRS RINA	Confirmation 产品合格 QC PASS	Confirmation


Further information


Information on the packaging
https://support.industry.siemens.com/cs/ww/en/view/109813875
Information for data generation and storage
https://support.industry.siemens.com/cs/ww/en/view/109995012
Information- and Downloadcenter (Catalogs, Brochures,…)
https://www.siemens.com/ic10
Industry Mall (Online ordering system)
https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3SK1111-1AB30
Cax online generator
https://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SK1111-1AB30
Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
https://support.industry.siemens.com/cs/ww/en/ps/3SK1111-1AB30
Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)
https://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3SK1111-1AB30&lang=en




© Copyright Siemens
Downloaded from Arrow.com.









last modified: 8/28/2026

Subject to change without notice
© Copyright Siemens
Downloaded from Arrow.com.