




PRODUCT NUMBER: 867-10-005-70-502011

www.mill-max.com
DATA SHEET



General Info

Description¹: Wire Termination Target Pad Header
Pre-Wired Target with 8" 24 AWG
Black Stranded Wires

Target Face Type: Flat Face

Type: Spring-Loaded

Category: Crimped Wire Cable Assembly

Mounting Style: Wire Termination - Crimp Type

Pins: 5

Packaging²: Packaged in Box or Tube

Rows: Single Row

ECCN: Contact Factory

HTSUS: 8536.90.4040

Product Lifecycle: Active

Country Of Origin: USA

867-10-005-70-502011- SPECIFICATIONS

Environmental Specs		Materials	
Temperature Range ³ :	-55/+125° C	Shell Plating:	10 μ " Gold over 100 μ " Nickel
Shock ⁴ :	No Elect. Discontinuity > 1 μ s @ 50g	Inner Plating:	
Vibration ⁵ :	No Elect. Discontinuity > 1 μ s @ 10-2000HZ, 15 G	Insulator Material:	Nylon 4/6
RoHS ⁶ :	Yes	Technical Specs	
Moisture Sensitivity Level (MSL):	1 (Unlimited)	Pitch:	.100" (2,540mm)
REACH Status:	REACH Unaffected	Electrical Specs	
		Rated Voltage:	100 VRMS/150 VDC
		Insulation Resistance:	10,000 M Ω min.
		Dielectric Withstanding Voltage:	1,000 VRMS min.

NOTES:

1. Standard Tolerances

Assembly tolerance: +/- .010" (.25mm)

Connector Length "L"

Connector Length "L"	Tolerance
$L \leq 2"$ ($L \leq 50.8$ mm)	+/- .005" (+/- .127 mm)
$2 < L \leq 3"$ (50.8 < $L \leq 76.2$ mm)	+ .007 / - .006" (+ .178 / -.152 mm)
$3 < L \leq 4"$ (76.2 < $L \leq 101.6$ mm)	+ .009 / - .007" (+ .229 / -.178 mm)
$4 < L \leq 5"$ (101.6 < $L \leq 127$ mm)	+ .011 / - .008" (+ .279 / -.203 mm)
$5 < L \leq 6.4"$ (127 < $L \leq 162.56$ mm)	+ .013 / - .009" (+ .330 / -.229 mm)

Insulator width: +/- .005 (.13mm)

Insulator height: +/- .005 (.13mm)

Co-planarity of SMT connectors: .005" (.13mm) up to 1" (25.4mm) in connector length

Insulator Flatness: .005" (.13mm) up to 1" (25.4mm) in connector length

Pin Length: +/- .005 (.13mm)

Pin Diameter: +/- .002 (.051mm)

Pin Angle: +/- 2°

2. Not all part numbers in the series may be packaged in tubes. Some specific part numbers may be packaged in a box.

3. Per IEC 60512-11-(4,-9,-10,-12)

4. For discrete pin only. Per IEC 60512-6-3: Test 6c: Shock

5. For discrete pin only. Per IEC 60512-6-4: Test 6d: Vibration (sinusoidal)

6. Mill-Max products labeled with the RoHS symbol are compliant with all three ROHS Directives. All of our products previously described as RoHS (2002/95/EC) and RoHS-2 (2011/65/EC) are also compliant with RoHS-3 (2015/863/EU).

ADDITIONAL NOTES AND SPECIFICATIONS

In the interest of improved design, quality and performance, Mill-Max reserves the right to make changes in its specifications without prior notice. Specifications and tolerances are provided wherever possible. The tolerance on dimensions of critical to function features is typically held tighter than the stated standard tolerances, such as press-fits, holes and lengths affecting the coplanarity of SMT products. Due to the wide variety of interconnects Mill-Max offers, the specific tolerances vary from product to product. If you need information regarding the tolerance of a particular part, please contact Technical Services.

RELATED LINKS AND DOCUMENTS

- Engineering Notebook: [Introduction to Spring Loaded Pogo Pins & Connectors](#)
- Engineering Notebook: [Pre-Wired Crimp Termination Cable Assemblies](#)
- Environmental Compliance: <https://www.mill-max.com/rohs>