

Product Summary


BV_{DSS}	$R_{DS(ON)}$	Package	I_D $T_A = +25^\circ C$ (Notes 5 & 6)
20V	130m Ω @ $V_{GS} = 4.5V$	MSOP-8	2.5A
	150m Ω @ $V_{GS} = 2.7V$		2.3A

Description

This MOSFET is designed to minimize the on-state resistance ($R_{DS(ON)}$), yet maintain superior switching performance, making it ideal for high efficiency power management applications.

Applications

- DC-DC Converters
- Power Management Functions
- Motor Control
- Disconnect Switches




Ordering Information (Note 4)

Part Number	Marking	Reel Size (inches)	Tape Width (mm)	Quantity per Reel
ZXMD63N02XTA	ZXM63N02	7	12	1,000
ZXMD63N02XTC	ZXM63N02	13	12	4,000

Notes:

- No purposely added lead. Fully EU Directive 2002/95/EC (RoHS), 2011/65/EU (RoHS 2) & 2015/863/EU (RoHS 3) compliant.
- See <https://www.diodes.com/quality/lead-free/> for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.
- Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- For packaging details, go to our website at <https://www.diodes.com/design/support/packaging/diodes-packaging/>.

Marking Information



ZXM63N02 = Product Type Marking Code

Maximum Ratings (@ $T_A = +25^\circ\text{C}$, unless otherwise specified.)

Characteristic			Symbol	Value	Unit
Drain-Source Voltage			V_{DSS}	20	V
Gate-Source Voltage			V_{GSS}	± 12	V
Continuous Drain Current	Steady State	@ $V_{GS} = 10\text{V}$; $T_A = +25^\circ\text{C}$ (Notes 5 & 6) @ $V_{GS} = 10\text{V}$; $T_A = +70^\circ\text{C}$ (Notes 5 & 6) @ $V_{GS} = 10\text{V}$; $T_A = +100^\circ\text{C}$ (Notes 5 & 6)	I_D	2.5 1.9 0.78	A
Pulsed Drain Current			I_{DM}	19	A
Continuous Source Current (Body Diode)			I_S	1.5	A
Pulsed Source Current (Body Diode)			I_{SM}	19	A





Thermal Characteristics

Characteristic		Symbol	Value	Unit
Power Dissipation	(Notes 6 & 8)	P_D	0.87	W
	(Notes 5 & 6)		1.25	
	(Notes 8 & 9)		1.04	
Thermal Resistance, Junction to Ambient	(Notes 6 & 8)	$R_{\theta JA}$	143	°C/W
	(Notes 5 & 6)		100	
	(Notes 8 & 9)		120	
Thermal Resistance, Junction to Leads	(Note 10)	$R_{\theta JL}$	84.9	°C/W
Operating and Storage Temperature Range	T_J, T_{STG}		-55 to +150	°C

Notes:

- 5. For a device surface mounted on FR-4 PCB measured at $t \leq 10$ sec.
- 6. For device with one active die.
- 7. Repetitive rating – 25mm x 25mm FR-4 PCB, $D = 0.02$, pulse width 300 μs – pulse width limited by maximum junction temperature.
- 8. For a device surface mounted on 25mm x 25mm FR-4 PCB with high coverage of single sided 1oz copper, in still air conditions.
- 9. For device with two active die running at equal power.
- 10. Thermal resistance from junction to solder-point (at the end of the drain lead).

Thermal Characteristics









Electrical Characteristics (@ $T_A = +25^\circ\text{C}$, unless otherwise specified.)

Characteristic	Symbol	Min	Typ	Max	Unit	Test Condition
OFF CHARACTERISTICS						
Drain-Source Breakdown Voltage	BV_{DSS}	20	—	—	V	$\text{V}_{\text{GS}} = 0\text{V}$, $\text{I}_D = 250\mu\text{A}$
Zero Gate Voltage Drain Current $T_J = +25^\circ\text{C}$	I_{DSS}	—	—	1.0	μA	$\text{V}_{\text{DS}} = 20\text{V}$, $\text{V}_{\text{GS}} = 0\text{V}$
Gate-Source Leakage	I_{GSS}	—	—	100	nA	$\text{V}_{\text{GS}} = \pm 12\text{V}$, $\text{V}_{\text{DS}} = 0\text{V}$
ON CHARACTERISTICS						
Gate Threshold Voltage	$\text{V}_{\text{GS}(\text{TH})}$	0.7	—	3	V	$\text{V}_{\text{DS}} = \text{V}_{\text{GS}}$, $\text{I}_D = 250\mu\text{A}$
Static Drain-Source On-Resistance (Note 11)	$\text{R}_{\text{DS}(\text{ON})}$	—	65 90	130 150	$\text{m}\Omega$	$\text{V}_{\text{GS}} = 4.5\text{V}$, $\text{I}_D = 1.7\text{A}$ $\text{V}_{\text{GS}} = 2.7\text{V}$, $\text{I}_D = 0.85\text{A}$
Forward Transconductance (Notes 11 & 13)	g_{fs}	2.6	—	—	S	$\text{V}_{\text{DS}} = 10\text{V}$, $\text{I}_D = 0.85\text{A}$
Diodes Forward Voltage (Note 11)	V_{SD}	—	0.85	0.95	V	$T_J = +25^\circ\text{C}$, $\text{I}_s = 1.7\text{A}$, $\text{V}_{\text{GS}} = 0\text{V}$
DYNAMIC CHARACTERISTICS						
Input Capacitance (Notes 12 & 13)	C_{iss}	—	350	700	pF	$\text{V}_{\text{DS}} = 15\text{V}$, $\text{V}_{\text{GS}} = 0\text{V}$, $f = 1\text{MHz}$
Output Capacitance (Notes 12 & 13)	C_{oss}	—	120	250		
Reverse Transfer Capacitance (Notes 12 & 13)	C_{rss}	—	50	100	Ω	$f = 1\text{MHz}$, $\text{V}_{\text{GS}} = 0\text{V}$, $\text{V}_{\text{DS}} = 0\text{V}$
Gate Resistance (Notes 12 & 13)	R_{g}	—	3.8	7.6		
Total Gate Charge (Notes 12 & 13)	Q_{g}	—	4.5	6	nC	$\text{V}_{\text{GS}} = 4.5\text{V}$, $\text{V}_{\text{DS}} = 16\text{V}$, $\text{I}_D = 1.7\text{A}$
Gate-Source Charge (Notes 12 & 13)	Q_{gs}	—	0.5	0.65		
Gate-Drain Charge (Notes 12 & 13)	Q_{gd}	—	2	2.5	ns	$\text{T}_J = +25^\circ\text{C}$, $\text{I}_F = 1.7\text{A}$, $\text{dI}/\text{dt} = 100\text{A}/\mu\text{s}$
Reverse Recovery Time (Note 13)	t_{RR}	—	15	30		
Reverse Recovery Charge (Note 13)	Q_{RR}	—	5.9	—	ns	$\text{V}_{\text{DD}} = 10\text{V}$, $\text{I}_D = 1.7\text{A}$, $\text{R}_G = 6\Omega$, $\text{R}_D = 5.7\Omega$
Turn-On Delay Time (Notes 12 & 13)	$\text{t}_{\text{D}(\text{ON})}$	—	3.4	—		
Turn-On Rise Time (Notes 12 & 13)	t_{R}	—	8.1	—	ns	
Turn-Off Delay Time (Notes 12 & 13)	$\text{t}_{\text{D}(\text{OFF})}$	—	13.5	—		
Turn-Off Fall Time (Notes 12 & 13)	t_{F}	—	9.1	—		



Notes:

11. Measured under pulsed conditions. Pulse width $\leq 300\mu\text{s}$; duty cycle $\leq 2\%$.
12. Switching characteristics are independent of operating junction temperature.
13. For design aid only, not subject to production testing.


Typical Characteristics




Typical Characteristics (Cont.)




Test Circuits




Basic gate charge waveform



Gate charge test circuit



Switching time waveforms




Switching time test circuit

Package Outline Dimensions

Please see <http://www.diodes.com/package-outlines.html> for the latest version.

MSOP-8




MSOP-8			
Dim	Min	Max	Typ
A	—	1.10	—
A1	0.05	0.15	0.10
A2	0.75	0.95	0.86
A3	0.29	0.49	0.39
b	0.22	0.38	0.30
c	0.08	0.23	0.15
D	2.90	3.10	3.00
E	4.70	5.10	4.90
E1	2.90	3.10	3.00
E3	2.85	3.05	2.95
e	—	—	0.65
L	0.40	0.80	0.60
a	0°	8°	4°
x	—	—	0.750
y	—	—	0.750

All Dimensions in mm

Suggested Pad Layout

Please see <http://www.diodes.com/package-outlines.html> for the latest version.

MSOP-8



Dimensions	Value (in mm)
C	0.650
X	0.450
Y	1.350
Y1	5.300

IMPORTANT NOTICE

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes Incorporated.

LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

A. Life support devices or systems are devices or systems which:

1. are intended to implant into the body, or
2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.

B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical, life support devices or systems.

Copyright © 2018, Diodes Incorporated

www.diodes.com