

APPROVED: _____


DATE: _____ TITLE: _____


Rev	AWO #	Description	Date	Appr
-		RELEASED	11/26/18	
A		UPDATE SPEC.	2/18/23	WX/LL1





RECOMMENDED PCB LAYOUT





Poles: 01 thru 15

SPECIFICATIONS:

Material:

Insulator: PBT, rated UL 94V-0

Insulator color: Black

Cover: PC, rated UL 94V-2

Contacts: Copper Alloy, Tin plated

Screw: M5 Steel, Zinc plated (A)

Electrical:

Voltage rating: 600 V

Current rating: 65 A

Contact resistance: 20 mohms

Insulation resistance: 1000 Mohms / DC500V

Dielectric withstanding voltage: 2,200 VAC for 1 minute

Mechanical:

Wire Range: 14~6 AWG

Torque: 2.5Nm/25.0lb.in

Temperature Rating:

-40°C to +130°C

Environmental:

Lead free, RoHS compliant. RoHS COMPLIANT

linear dimension(Tolerances Standard)								—	⏥	⊥
variable range	to 6	over 6 to 10	over 10 to 30	over 30 to 60	over 60 to 100	over 100 to 160	over 160 to	to 10	over 10 to 100	over 100 to
tolerance	±0.20	±0.30	±0.50	±0.70	±1.00	±1.30	±1.60	0.10	0.30	0.60

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES		HOLES	
.X	± .10	Ø.X	±.10
.XX	± .020	Ø.XX	±.015
.XXX	± .015	Ø.XXX	±.010

DRAWN	AY	11/26/18
CHECKED	AC	11/26/18
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN PERMISSION FROM ADAM TECH

ADAM TECH
909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE: TERMINAL BLOCK, .630 [16.00] PITCH W/ SNAP ON CLEAR COVER

SIZE	PART NO.	REV.
X	TBU-XX-W3-CC	A

REF: S00067C | SCALE: NTS | SHEET 1 OF 1

Downloaded from Arrow.com.