


HONEYWELL PART NUMBER
21SM366
PRODUCT CODE TXL9900

REV	DOCUMENT	CHANGED BY	CHECK
5	0038111	PK 20MAY08	ASD



NOTE—

- ▲-MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375±.002 CENTERS
- 2-TERMINALS ARE PLATED FOR SOLDERING
- 3-SWITCH WILL WITHSTAND TEMPERATURE OF 250°
- 4-MATING CONTACT SURFACES ARE 24 K SOLID GOLD OVERLAY

RELEASE NO.	PR - 8090
REPLACES	-

CHARACTERISTICS	ELECTRICAL DATA			DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± TWO PLACE .XX ± THREE PLACE .XXX ± FOUR PLACE .XXXX ± ANGLES ±			DRAWN	VK	18OCT07	Honeywell				
OPERATING FORCE — — — — 3 OZ MAX	CONTACT ARRANGEMENT SPDT						CHECK	RJ	18OCT07					
RELEASE FORCE— — — — 1 OZ MIN	30 VOLTS DC RATING			0.030 0.015 0.005			THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE SWITCH - BASIC				
DIFFERENTIAL TRAVEL— — — .002 MAX		SEA LEVEL	50,000 FT											
OVERTRAVEL — — — — — .005 MIN	INDUCTIVE	1/2 AMP	1/2 AMP	THIRD ANGLE PROJECTION 			INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			SIZE	TYPE	DRAWING NAME		REV
	RESISTIVE	1 AMP	1 AMP							B	I	21SM366		5
						RASTER			SCALE	-	WEIGHT .006 LB MAX	SHEET 1 OF 1		
APPROVALS			KEMA, CE 1A, 250V ~ T85 1E4  											
			UL, CSA 1A, 125 VAC   BRAND L 22											