



8 7 6 5 4 3 2 1

THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON ARE CONFIDENTIAL AND THE PROPERTY OF BEL/STEWART/TRP CONNECTOR AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT THE WRITTEN CONSENT OF TRP CONNECTOR.

PRODUCT MAY BE PROTECTED BY ONE OR MORE OF THE FOLLOWING US PATENTS:
5736910 5939955 6425781 6428361 6554638 6840817 7123117
7429195 7717749 7808751 6217391 6149050 7924130

REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN APVD
7		SEE LAST SHEET	13JAN2015	RL TY



1. MATERIALS
- HOUSING: THERMOPLASTIC, FLAMMABILITY RATING UL 94V-0.
 - SHIELD: BRASS 0.20mm THICK, PREPLATED WITH 0.76um MIN SEMI-BRIGHT NICKEL. SOLDER TABS POST DIPPED WITH 2.54um MIN SAC SOLDER.
 - CONTACTS: PHOSPHOR BRONZE 0.46mm X 0.30mm, PHOSPHOR BRONZE, 1.27um MIN NICKEL UNDERPLATE, WITH 1.27um MIN GOLD PLATING AT MATING INTERFACE AND 2.54um MIN MATTE TIN ON SOLDER TAILS,
 - SOLDER TAILS: 0.25mmTHICK, PHOSPHOR BRONZE, 1.27um MIN OVERALL NICKEL UNDERPLATE, 3um TIN PLATE
 - LIGHT EMITTING DIODE (LED): DIFFUSED EPOXY LENS, 0.5mm X 0.5mm CARBON STEEL WIREFRAME LEADS PREPLATED WITH 2.03um MIN. SILVER PLATE OVER 1.02um MIN. NICKEL OVER 1.02um MIN. COPPER UNDERPLATE; LEADS POST-PLATED WITH 3.05um MIN. MATTE TIN, TIP TIN DIPPING.
2. RJ45 JACK CAVITY CONFORMS TO FCC RULES AND REGULATIONS PART 68 SUB PART F.
3. MAGNETICS
- APPLICATION: 10/100/1000 BASE-T
 - IMPEDANCE: 100 OHMS
 - TURNS RATIO (CHIP:CABLE): 1:1 ALL FOUR PAIRS
 - OPEN CIRCUIT INDUCTANCE (OCL): 350uH MIN. @100kHz, 0.1VRMS, 8mADC BIAS FROM 0°C TO 70°C, ALL FOUR PAIRS
 - ALL FOUR PAIRS BI-DIRECTIONAL
 - PERFORMANCE @ 25°C:
 - INSERTION LOSS (IL): 1.1dB MAX. FROM 0.5MHz TO 100MHz
 - RETURN LOSS (RL): 18dB MIN FROM 0.5MHz TO 40MHz
 - 12-20LOG(f/80)dB MIN. FROM 40.1MHz TO 100MHz
 - CROSSTALK ATTENUATION: 35dB MIN. FROM 0.5MHz TO 40MHz
 - 33-20LOG(f/50)dB MIN. FROM 40.1MHz TO 100MHz
 - COMMON MODE REJECTION RATIO (CMRR):30dB MIN. FROM 0.5MHz TO 100MHz
 - ISOLATION VOLTAGE: 2250VDC FOR 60 SECONDS WITH A RISE TIME OF 500 V/SEC

4. OPERATING TEMPERATURE: FROM 0°C TO +70°C.

5. INDICATED MAGNETIC CONNECTIONS ARE SYMMETRICAL TO SUPPORT AUTO-MDI/MDIX.





6. THE 250 OHM LED RESISTORS ARE OPTIONAL, PLEASE SEE CHART FOR PRESENCE OR ABSENCE OF RESISTORS. IF LEDS WITHOUT 250 OHM RESISTORS. LEDS ARE DRIVEN WITH CONSTANT CURRENT AT APPROX 20mA

LED COLOR: DOMINATE WAVELENGTH (λD): GREEN 568 nm TYP. AT IF = 20mA
FORWARD VOLTAGE (VF): GREEN 2.2V TYP. at IF = 20mA
DOMINATE WAVELENGTH (λD): YELLOW 588 nm TYP. AT IF = 20mA
FORWARD VOLTAGE (VF): YELLOW 2.1V TYP. at IF = 20mA
DOMINATE WAVELENGTH (λD): AMBER 590±3 nm AT IF = 20mA
FORWARD VOLTAGE (VF): AMBER 2.1V at IF = 20mA
DOMINATE WAVELENGTH (λD): ORANGE 605 nm TYP. AT IF = 20mA
FORWARD VOLTAGE (VF): ORANGE 2.1V TYP. at IF = 20mA
DOMINATE WAVELENGTH (λD): ULTRA LOW WAVELENGTH GREEN (ULWG) 525 nm TYP. AT IF = 20mA
FORWARD VOLTAGE (VF): ULTRA LOW WAVELENGTH GREEN (ULWG) 2.8V TYP. at IF = 20mA
BUILT-IN 250 OHM RESISTORS. LEDS ARE DRIVEN WITH 5V VOLTAGE AND THE MAX OPERATING CURRENT IS 20mA

LED COLOR: DOMINATE WAVELENGTH (λD): GREEN 568 nm TYP. @ VF=5V
FORWARD CURRENT (IF): GREEN 12mA TYP @ VF = 5V
DOMINATE WAVELENGTH (λD): YELLOW 588 nm TYP. @ VF=5V
FORWARD CURRENT (IF): YELLOW 13mA TYP @ VF = 5V

7. TRP CONNECTOR LOGO, PART NUMBER, DATE CODE, COUNTRY OF ORIGIN AND AGENCY APPROVAL MARKING IN APPROXIMATE LOCATION SHOWN.



8. THESE PARTS ARE RECOMMENDED FOR WAVE SOLDERING PROCESS,PREHEAT TEMPERATURE IS 120°C TO 160°C, 120 SECONDS TO 180 SECONDS, PEAK WAVE SOLDERING TEMPERATURE IS 260°C MAX,10 SECONDS MAX.



SUGGESTED PANEL CUTOUT
SCALE 4:1

HIGH TEMPERATURE	3.43	3.68	GREEN	-	NO	YELLOW	-	NO	1-2250022-2
NORMAL TEMPERATURE	3.43	3.68	GREEN	-	NO	GREEN	-	NO	1-2250022-1
NORMAL TEMPERATURE	3.43	3.68	ULWG	AMBER	NO	ULWG	AMBER	NO	1-2250022-0
NORMAL TEMPERATURE	3.43	2.30	GREEN	YELLOW	NO	GREEN	-	YES	2250022-9
NORMAL TEMPERATURE	3.43	3.68	GREEN	-	NO	YELLOW	-	NO	2250022-8
NORMAL TEMPERATURE	3.43	2.30	GREEN	YELLOW	NO	GREEN	-	NO	2250022-7
HIGH TEMPERATURE	3.43	2.30	GREEN	YELLOW	NO	GREEN	YELLOW	NO	2250022-6
HIGH TEMPERATURE	3.43	3.68	GREEN	-	YES	GREEN	-	YES	2250022-5
NORMAL TEMPERATURE	3.43	3.68	GREEN	YELLOW	NO	GREEN	YELLOW	NO	2250022-4
NORMAL TEMPERATURE	3.43	2.30	GREEN	ORANGE	NO	YELLOW	-	NO	2250022-3
NORMAL TEMPERATURE	3.43	2.30	GREEN	-	YES	GREEN	-	YES	2250022-2
NORMAL TEMPERATURE	3.43	2.30	GREEN	YELLOW	NO	GREEN	YELLOW	NO	2250022-1
HOUSING TEMPERATURE	DIM B	DIM A	11-12	12-11	250 OHMS RESISTOR	13-14	14-13	250 OHMS RESISTOR	PART NUMBER
			LED 1			LED 2			

THIS DRAWING IS A CONTROLLED DOCUMENT. DIMENSIONS: mm TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.25 1 PLC ±0.25 2 PLC ±0.25 3 PLC ± 4 PLC ± ANGLES PRODUCT SPEC 108-104004 APPLICATION SPEC -		DWN ROY LIU 20MAY2013 CHK TOWER YU/FRANK LIU 20MAY2013 APVD TONY YUAN 20MAY2013 MODEL NAME MAGJACK SINGLE Non-PoE CUSTOMER DRAWING	DESC IXL 4G46PI GIGABIT TAB DOWN W/ LED SIZE A1 CAGE CODE DRAWING NO C=2250022 RESTRICTED TO -	DONGGUAN CHINA
SCALE 4:1		SHEET 1 OF 3	REV 7	

4G46P1 GIGABIT CIRCUIT 35

C1=1000pF, 2kV, CAPACITOR
R1-R4=75 Ohms, RESISTORS
C2-C5=0.1uF, 50V CAPACITOR

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN ROY LIU		20MAY2013		 trp a bel group CONNECTOR		DONGGUAN CHINA	
DIMENSIONS:		CWN TOWER YU/FRANK LIU		20MAY2013					
mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD TONY YUAN		DESC			
		0 PLC ±0.25 1 PLC ±0.25 2 PLC ±0.25 3 PLC ± 4 PLC ± ANGLES ± *		MODEL NAME MAGJACK		IXI 4G46PI GIGABIT TAB DOWN W/ LED			
PRODUCT SPEC		APPLICATION SPEC		SIZE		CAGE CODE		DRAWING NO	
108-104004		-		SINGLE Non-PoE		A1		C=2250022	
CUSTOMER DRAWING						SCALE		REV	
						4:1		2 of 3	
								9	

C_2250022					STOCK DISPOSITION			
					A: CONTINUE AS IS B: REWORK C: SCRAP		D: USE OLD FIRST E: PARTS TO CONFORM F: OTHER	
REVISION HISTORY								
DATE	REV	CHANGES	REASON	APPROVAL	INVENTORY (A,B,C,D,E,F)	WORK IN PROCESS (A,B,C,F)	SUPPLIER ORDERS (A,E,F)	OPEN CUST ORDERS (A,E,F)
20MAY2013	1	-	INITIAL RELEASE	TONY YUAN	-	-	-	-
07JUN2013	2	DELETE DASH NUMBER 2250022-9	MARKET REQUIREMENT	TONY YUAN	-	-	-	-
24FEB2014	3	ADD DASH NUMBER 2250022-9	MARKET REQUIREMENT	TONY YUAN	-	-	-	-
06MAR2014	4	ADD DASH NUMBER 1-2250022-0	MARKET REQUIREMENT	TONY YUAN	-	-	-	-
01SEP2014	5	ADD DASH NUMBER 1-2250022-1 BASED ON 2250022-5 (REMOVE RESISTORS FROM LEDS, HOUSING BECOME NORMAL TEMP) ADD DASH NUMBER 1-2250022-2 BASED ON 2250022-8 (CHANGE PLASTIC TO HIGH TEMPERATURE)	MARKET REQUIREMENT	TONY YUAN	-	-	-	-
11OCT2014	6	NOTE 6: ADD AMBER LED SPEC PART LIST: 1-2250022-0, CHANGE ULWG/YELLOW TO ULWG/AMBER	MARKET REQUIREMENT	TONY YUAN	-	-	-	-
13JAN2015	7	1.EC-1411035 COMPANY LOGO CHANGE 2.CHANGE DIM A OF 1-2250022-0 FROM 4.19 TO 3.68	MARKET REQUIREMENT	TONY YUAN	-	-	-	-

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN
ROY LIU
20MAY2013

CHK
TOWER YU/FRANK LIU
20MAY2013

APVD
TONY YUAN
20MAY2013

DIMENSIONS:

mm

0 PLC ±0.25

1 PLC ±0.25

2 PLC ±0.25

3 PLC ±

4 PLC ±

ANGLES

APPLICATION SPEC

PRODUCT SPEC

108-104004

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

±0.25

±0.25

±

±

±

±

MODEL NAME

MAGJACK

DESC

SINGLE Non-PoE

SIZE

A1

CAGE CODE

DRAWING NO

C=2250022

RESTRICTED TO

-

CUSTOMER DRAWING

SCALE 4:1

SHEET 3 OF 3

REV 7

trp CONNECTOR

DONGGUAN CHINA

Downloaded from [Arrow.com](#)