



Part Number : [1720650212](#)
Product Description : Mega-Fit Slim Vertical Header, Through Hole, 5.70mm Pitch, Dual Row, 12 Circuits, 0.38µm Gold (Au) Plating, Glow-Wire Capable, Black
Series Number : 172065
Status : Active
Product Category : PCB Headers and Receptacles



Documents & Resources


Drawings
[1720650212_sd.pdf](#)
[768291100-000.pdf](#)

3D Models and Design Files
[1720650212_stp.zip](#)

Specifications
[768232000-AS-000.pdf](#)
[AS-76823-100-001.pdf](#)
[1720631000-PS-000.pdf](#)
[510651000-PS-CHI-000.pdf](#)
[510651000-PS-JAP-000.pdf](#)
[510651000-PS-KOR-000.pdf](#)
[510651000-PS-SPA-000.pdf](#)
[PS-76823-100-001.pdf](#)
[1720631000-TS-000.pdf](#)
[TS-76823-100-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 33; 44; 34
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)

EU RoHS	Compliant per EU 2015/863
---------	---------------------------

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	172065
Description	Mega-Fit Slim Vertical Header, Through Hole, 5.70mm Pitch, Dual Row, 12 Circuits, 0.38µm Gold (Au) Plating, Glow-Wire Capable, Black
Application	Power, Wire-to-Board
Component Type	PCB Header
Product Name	Mega-Fit
UPC	889056897235

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	23.5A
Voltage - Maximum	600V AC (RMS)/DC

Physical

Breakaway	No
Circuits (Loaded)	12

Circuits (maximum)	12
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Mated Height	16.78mm
Material - Metal	High Conductivity Copper
Material - Plating Mating	Gold
Material - Plating Termination	Matte Tin
Material - Resin	Liquid Crystal Polymer
Net Weight	6.631/g
Number of Rows	2
Orientation	Vertical
Packaging Type	Tray
PC Tail Length	3.73mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.58mm
Pitch - Mating Interface	5.70mm
Pitch - Termination Interface	5.70mm
Plating min - Mating	0.381µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Yes
Temperature Range - Operating	-40° to +120°C
Termination Interface Style	Through Hole
Unmated Height	14.80mm

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mega-Fit Dual Row Receptacle Housings	<u>170001</u>
Mega-Fit Dual Row Receptacle Housings	<u>171692</u>

This document was generated on Apr 05, 2025