
Part Number : 1731071939
Product Description : FCT Mixed Layout D-Sub Connector, Male, Straight, PCB Through Hole, Gold Plating, Tin-plated Shell with Dimples, 6.60mm Snap-in Bolt, 9 Circuits Loaded (4 High Power, 5 Signal), Green Insulator
Series Number : 173107
Status : Active
Product Category : D-Sub Connectors
Engineering Part Number : FM9W4P1-1410



Documents and Resources

Drawings

1731071939_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Symbol and Footprint (Multi-Format)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Downloaded from Arrow.com.

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	D-Sub Connectors
Series	173107
Description	FCT Mixed Layout D-Sub Connector, Male, Straight, PCB Through Hole, Gold Plating, Tin-plated Shell with Dimples, 6.60mm Snap-in Bolt, 9 Circuits Loaded (4 High Power, 5 Signal), Green Insulator
IP Rating	IP20
Magnetic	Yes
Product Name	FCT Products
Type	Mixed Layout
UPC	193264773893

Electrical

Current - Maximum per Contact	20.0A
Shielded	Yes

Physical

Circuits (Loaded)	9
Circuits (maximum)	9
Color - Resin	Green

Downloaded from Arrow.com.

Durability (mating cycles min)	500
Gender	Male
Material - Contact	Copper Alloy
Material - Resin	Polybutylene Terephthalate (PBT)
Material - Shell	Steel
Net Weight	16.000/g
Number of Rows	2
Orientation	Straight
Packaging Type	Carton
Panel Mount	Rear
Panel Mount Method	Thread-In
PCB Locator	No
PCB Retention	No
PCB Thickness - Recommended	1.60mm
PC Tail Length	10.20mm
Pitch - Mating Interface	2.84mm
Pitch - Termination Interface	2.84mm
Plating - Contact	Gold over Nickel
Plating - Shell	Tin
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	1
Shell Size	3
Temperature Range - Operating	-55° to +130°C
Termination Style	Through Hole
Waterproof / Dustproof	No
Waterproof / Dustproof Type	IP20

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	FCT Mixed Layout D-Sub, Size 3, 9W4, Socket

Downloaded from Arrow.com.

This document was generated on Jun 03, 2026

Downloaded from Arrow.com.