
This document was generated on 05/31/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 1201130014
Status: Active
Overview: Brad® Nano-Change® (M8) Products
Description: Nano-Change® Molded Junction Box, Top Mount with Molded Cable, End Entry, 8 Ports, 5.0m Cable



Series image - Reference only

Documents:
Drawing (PDF)
RoHS Certificate of Compliance (PDF)
Packaging Specification 1921-00000-00039 (PDF)

General

Product Family	Passive Distribution Boxes
Series	120113
IP Rating	IP67
NEMA Rating	NEMA 6
Overview	Brad® Nano-Change® (M8) Products
Product Name	Nano-Change® (M8)
UPC	78678834073

Physical

Bus I/O	Nano-Change® (M8)
Cable Connector Orientation	Straight
Cable Length	5.0m
Home Run Cable Length	5.0m
Home Run Connector	N/A
Home Run Interface	N/A
Keyway	None
LED Indicator	No
Material - Cable Jacket	PUR
Material - Housing	PBT
Material - Metal	Copper Alloy
Material - Plating Mating	Gold over Nickel
Net Weight	837.235/g
Orientation	Top Mount
Poles	3
Poles (wired)	3
Ports	8
Temperature Range - Operating	-25°C to +90°C
Wiring Configuration	Single I/O per Port

Electrical

Current - Maximum per Contact	2.0A per port
Functional Wiring	PNP
Voltage - Maximum	10-30V DC

Material Info

Old Part Number	BEY801P-FBP-05

Reference - Drawing Numbers

Packaging Specification	1921-00000-00039
Sales Drawing	SD-120113-003, SD-120113-016

EU ELV
Not Relevant

EU RoHS **China RoHS**
Not Reviewed
REACH SVHC
Not Reviewed
Halogen-Free Status
Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the Contact Us section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Relevant

Search Parts in this Series
120113 Series

This document was generated on 05/31/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Downloaded from Arrow.com.