




Wire & Cable > Hook Up Wire > Modified-Crosslinked, Lightweight Wire



Cable Type: **MIL-DTL-22759**

Operating Voltage: **600 V**

Wire & Cable Insulation Material: **Modified Radiation Cross-linked ETFE Polymer**

Conductor Material: **Silver-Coated Copper**

Wire Size: **20 AWG**

[All Modified-Crosslinked, Lightweight Wire \(266\)](#)

Features

Product Type Features

Cable Style	Primary
-------------	---------

Configuration Features

Number of Strands	19
Number of Conductors	1

Electrical Characteristics

Operating Voltage	600 V
-------------------	-------

Body Features

Wire & Cable Insulation Material	Modified Radiation Cross-linked ETFE Polymer
Conductor Material	Silver-Coated Copper
Wire Color (Base)	Black

Dimensions

Strand Size	32 AWG
Outside Cable Diameter	1.27 mm[.05 in]
Conductor Diameter Range	.99 mm[.039 in]
Wire Size	20 AWG

Usage Conditions



Cable Type	MIL-DTL-22759
Operating Temperature Range	-65 – 200 °C
Other	
Product Source	US

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Out of Scope - excluded from Halogen requirements
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # A36675-000  
D-200-83

Customers Also Bought






TE Part #NB-PTCO-006  
Pt1000, 2.0x2.3, Class B, PTCF102B1G0




TE Part #33459  
TERMINAL,SOLIS R 12-10 5/16




TE Part #1-1617754-9  
FCA-410-1621M=M83536/16-021M



TE Part #1-1617110-7  
JMGST-5L = M28776/7-001L




TE Part #2-1617749-0  
FCA-210-1023M=M83536/10-023M



TE Part #5-1617791-1  
FCA-125-3702L=M83536/37-002L



TE Part #CAT-AS22759-32  
Modified-Crosslinked, Lightweight Wire



TE Part #640024-1  
058 PIN REC 010TP

Documents

Product Drawings  
22759/44-20-0

English