





REV.	DATE	ECR NO.	DESCRIPTION
A	07/26/99	—	REFORMAT — CHANGE TO NEXCOTE FINISH
B	05/24/00	—	MODIFY PLATING / ADD INSULATOR
C	07/08/04	—	UPDATE CABLE STRIPPING DIMS.
D	07/22/11	2205	CHANGE THE TOTAL LENGTH TO 20 REF



RECOMMENDED
CABLE STRIPPING DIM'S



1. CRIMPED CONTACT PIN
HEX. CRIMP SIZE .068"

4	CONTACT PIN	BRASS	GOLD	1
3	INSULATOR	PTFE	NATURAL	1
2	BODY	BRASS	GOLD	1
1	SHELL	BRASS	NICKEL	1
	DESCRIPTION	MATERIAL	FINISH	QTY

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.
UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm
UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020"
DO NOT SCALE DRAWING

APPROVALS	DATE
DRAWN M.ZHANG	07/22/11
CHECKED	
ISSUED	
SHEET 1 OF 1	
CAD FILE C:/CONNEX/112551.DWG	

Amphenol Connex			
PART DESCRIPTION BNC DIRECT SOLDER PLUG (FOR .141" SEMI RIGID CABLE)			
PART NO. 112551			
DWG. NO.	112551.DWG	REV. D	SCALE NA