

FDR844P

P-Channel 1.8V Specified PowerTrench® MOSFET

General Description



This P-Channel 1.8V specified MOSFET uses Fairchild's advanced low voltage PowerTrench process. It has been optimized for battery power management applications.

Applications

- Power management
- Load switch
- Battery protection

Features

- -10 A, -20 V. $R_{DS(ON)} = 11 \text{ m}\Omega$ @ $V_{GS} = -4.5 \text{ V}$
- $R_{DS(ON)} = 14 \text{ m}\Omega$ @ $V_{GS} = -2.5 \text{ V}$
- $R_{DS(ON)} = 20 \text{ m}\Omega$ @ $V_{GS} = -1.8 \text{ V}$
- Fast switching speed
- High performance trench technology for extremely low $R_{DS(ON)}$
- High power and current handling capability



Absolute Maximum Ratings

$T_A=25^\circ\text{C}$ unless otherwise noted

Symbol	Parameter	Ratings	Units
V_{DSS}	Drain-Source Voltage	-20	V
V_{GSS}	Gate-Source Voltage	± 8	V
I_D	Drain Current – Continuous	-10	A
	– Pulsed	-50	
P_D	Power Dissipation for Single Operation	1.8	W
	(Note 1a)		
	(Note 1b)	1.0	
	(Note 1c)	0.9	
T_J, T_{STG}	Operating and Storage Junction Temperature Range	-55 to +150	°C

Thermal Characteristics

$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient	(Note 1a)	70	°C/W
$R_{\theta JC}$	Thermal Resistance, Junction-to-Case	(Note 1)	20	°C/W

Package Marking and Ordering Information

Device Marking	Device	Reel Size	Tape width	Quantity
.844P	FDR844P	13"	12mm	2500 units


Electrical Characteristics

$T_A = 25^\circ\text{C}$ unless otherwise noted


Symbol	Parameter	Test Conditions	Min	Typ	Max	Units
Off Characteristics						
BV_{DSS}	Drain-Source Breakdown Voltage	$V_{\text{GS}} = 0 \text{ V}$, $I_D = -250 \mu\text{A}$	-20			V
$\frac{\Delta \text{BV}_{\text{DSS}}}{\Delta T_J}$	Breakdown Voltage Temperature Coefficient	$I_D = -250 \mu\text{A}$, Referenced to 25°C		-13		mV°C
I_{DSS}	Zero Gate Voltage Drain Current	$V_{\text{DS}} = -16 \text{ V}$, $V_{\text{GS}} = 0 \text{ V}$		-1		μA
I_{GSSF}	Gate-Body Leakage, Forward	$V_{\text{GS}} = 8 \text{ V}$, $V_{\text{DS}} = 0 \text{ V}$		100		nA
I_{GSSR}	Gate-Body Leakage, Reverse	$V_{\text{GS}} = -8 \text{ V}$, $V_{\text{DS}} = 0 \text{ V}$		-100		nA
On Characteristics (Note 2)						
$V_{\text{GS(th)}}$	Gate Threshold Voltage	$V_{\text{DS}} = V_{\text{GS}}$, $I_D = -250 \mu\text{A}$	-0.4	-0.7	-1.5	V
$\frac{\Delta V_{\text{GS(th)}}}{\Delta T_J}$	Gate Threshold Voltage Temperature Coefficient	$I_D = -250 \mu\text{A}$, Referenced to 25°C		3		mV°C
$R_{\text{DS(on)}}$	Static Drain-Source On-Resistance	$V_{\text{GS}} = -4.5 \text{ V}$, $I_D = -10 \text{ A}$ $V_{\text{GS}} = -2.5 \text{ V}$, $I_D = -9 \text{ A}$ $V_{\text{GS}} = -1.8 \text{ V}$, $I_D = -7.5 \text{ A}$ $V_{\text{GS}} = -4.5 \text{ V}$, $I_D = -10 \text{ A}$, $T_J = 125^\circ\text{C}$		7 9.5 13 9.5	11 14 20 15	$\text{m}\Omega$
$I_{\text{D(on)}}$	On-State Drain Current	$V_{\text{GS}} = -4.5 \text{ V}$, $V_{\text{DS}} = -5 \text{ V}$	-50			A
g_{FS}	Forward Transconductance	$V_{\text{DS}} = -10 \text{ V}$, $I_D = -10 \text{ A}$		57		S
Dynamic Characteristics						
C_{iss}	Input Capacitance	$V_{\text{DS}} = -10 \text{ V}$, $V_{\text{GS}} = 0 \text{ V}$, $f = 1.0 \text{ MHz}$		4951		pF
C_{oss}	Output Capacitance			884		pF
C_{rss}	Reverse Transfer Capacitance			451		pF
Switching Characteristics (Note 2)						
$t_{\text{d(on)}}$	Turn-On Delay Time	$V_{\text{DD}} = -10 \text{ V}$, $I_D = -1 \text{ A}$, $V_{\text{GS}} = -4.5 \text{ V}$, $R_{\text{GEN}} = 6 \Omega$		16	29	ns
t_r	Turn-On Rise Time			9	18	ns
$t_{\text{d(off)}}$	Turn-Off Delay Time			196	314	ns
t_f	Turn-Off Fall Time			78	125	ns
Q_g	Total Gate Charge	$V_{\text{DS}} = -10 \text{ V}$, $I_D = -10 \text{ A}$, $V_{\text{GS}} = -4.5 \text{ V}$		53	74	nC
Q_{gs}	Gate-Source Charge			6		nC
Q_{gd}	Gate-Drain Charge			12		nC
Drain-Source Diode Characteristics and Maximum Ratings						
I_s	Maximum Continuous Drain-Source Diode Forward Current				-1.5	A
V_{SD}	Drain-Source Diode Forward Voltage	$V_{\text{GS}} = 0 \text{ V}$, $I_s = -1.5 \text{ A}$ (Note 2)		-0.56	-1.2	V

Notes:


- R_{JJA} is the sum of the junction-to-case and case-to-ambient thermal resistance where the case thermal reference is defined as the solder mounting surface of the drain pins. R_{JJC} is guaranteed by design while R_{JCA} is determined by the user's board design.



a) 70°C/W when mounted on a 1in^2 pad of 2 oz copper



b) 125°C/W when mounted on a $.04 \text{ in}^2$ pad of 2 oz copper



c) 135°C/W when mounted on a minimum pad.

Scale 1 : 1 on letter size paper

2. Pulse Test: Pulse Width $< 300\mu\text{s}$, Duty Cycle $< 2.0\%$

Typical Characteristics




Figure 1. On-Region Characteristics.




Figure 2. On-Resistance Variation with Drain Current and Gate Voltage.




Figure 3. On-Resistance Variation with Temperature.




Figure 4. On-Resistance Variation with Gate-to-Source Voltage.




Figure 5. Transfer Characteristics.




Figure 6. Body Diode Forward Voltage Variation with Source Current and Temperature.

Typical Characteristics




Figure 7. Gate Charge Characteristics.




Figure 8. Capacitance Characteristics.




Figure 9. Maximum Safe Operating Area.




Figure 10. Single Pulse Maximum Power Dissipation.




Figure 11. Transient Thermal Response Curve.

Thermal characterization performed using the conditions described in Note 1c.
Transient thermal response will change depending on the circuit board design.

TRADEMARKS

The following are registered and unregistered trademarks Fairchild Semiconductor owns or is authorized to use and is not intended to be an exhaustive list of all such trademarks.

ACE TM	FAST [®]	OPTOLOGIC TM	SMART START TM	VCX TM
Bottomless TM	FASTR TM	OPTOPLANAR TM	STAR*POWER TM	
CoolFET TM	FRFET TM	PACMAN TM	Stealth TM	
CROSSVOLT TM	GlobalOptoisolator TM	POP TM	SuperSOT TM -3	
DenseTrench TM	GTOT TM	Power247 TM	SuperSOT TM -6	
DOME TM	HiSeC TM	PowerTrench [®]	SuperSOT TM -8	
EcoSPARK TM	ISOPLANAR TM	QFET TM	SyncFET TM	
E ² CMOS TM	LittleFET TM	QS TM	TinyLogic TM	
EnSigna TM	MicroFET TM	QT Optoelectronics TM	TruTranslation TM	
FACT TM	MicroPak TM	Quiet Series TM	UHC TM	
FACT Quiet Series TM	MICROWIRE TM	SILENT SWITCHER [®]	UltraFET [®]	

STAR*POWER is used under license

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, or (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.
2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

PRODUCT STATUS DEFINITIONS

Definition of Terms

Datasheet Identification	Product Status	Definition
Advance Information	Formative or In Design	This datasheet contains the design specifications for product development. Specifications may change in any manner without notice.
Preliminary	First Production	This datasheet contains preliminary data, and supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
No Identification Needed	Full Production	This datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
Obsolete	Not In Production	This datasheet contains specifications on a product that has been discontinued by Fairchild semiconductor. The datasheet is printed for reference information only.

Rev. H4