


LOC	DIST	REVISIONS					
A1	2	P	LTR	DESCRIPTION	DATE	DWN	APVD
			B6	REVISED PER ECR-17-014951	16OCT2017	BDA	KR
			B7	REVISED PER ECR-24-224610	10MAR2025	AK	BR



- 1 MATES WITH APPROPRIATE UNIVERSAL MATE-N-LOK CAP OR HEADER
- 2 SMALL NICKS ARE PERMITTED ON THE CIRCUIT TOWERS WHICH COULD INCREASE THE INITIAL HOUSING MATING FORCE BY UP TO 4.4 NEWTONS. NO INDIVIDUAL NICKED TOWER SHALL INCREASE THIS FORCE BY OVER 5.5 NEWTONS.
- 3 DIMENSIONS SHOWN REPRESENT PRODUCT IN DRY, AS MOLDED, CONDITION. ADDITIONAL 2% GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR AND SHOULD BE ACCOUNTED FOR.
- 4 UNDERWRITERS RECOGNIZED COMPONENT LOGO AND CSA CERTIFICATION LOGO TO BE LOCATED ONCE ON ANY SIDE OF HOUSING
- 5 POSITION #1 LOCATOR FEATURE MAY BE ROUND OR OBLONG (AS DEPICTED)
- 6 MATERIAL CORRESPONDING TO THE REQUIREMENTS OF IEC 60335 (INCL. GLOW WIRE TEST 750 ° C, WITHOUT FLAME)
- 7 PRELIMINARY PART NOT RELEASED FOR PRODUCTION
- 8 NO LATCH WINDOW PRESENT.
- 9 LATCH WINDOW PRESENT.

OBSOLETE		1-1703061-3	1	PA66 UL94 V0 GW T 750 °C	NATURAL
		1-1703061-2	A	PA66 UL94 V0 GW T 750 °C	NATURAL
		1-1703061-1	1	PA6 UL94 V0	NATURAL
		1703061-4	A	PA6 UL94 V2 GW T 750 °C	BLACK
		1703061-3	A	PA6 UL94 V2 GW T 750 °C	RED
		1703061-2	A	PA6 UL94 V2 GW T 750 °C	BLUE
		1703061-1	A	PA6 UL94 V2 GW T 750 °C	NATURAL
	REMARK	PN	REV	MATERIAL	COLOUR

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 17OCT2008 MAHNKE, B.		 TE Connectivity				
		CHK Z1TZ, A. 26APR2004						
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME PLUG, 2 CIRCUIT, UNIVERSAL MATE-N-LOK -				
mm		APVD 27APR2004 BLEICHER, M.						
		PRODUCT SPEC 108-1031						
		APPLICATION SPEC 114-1010						
MATERIAL		FINISH		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
SEE TABLE		0 PLC ± 1 PLC ± 2 PLC ±0.13 3 PLC ± 4 PLC ± ANGLES ±40°30'		WEIGHT 2.422 g	A2	00779	©-1703061	
CUSTOMER DRAWING						SCALE 4:1	SHEET 1 OF 1	REV B7